

8961726 TEXAS INSTR (OPTO)

62C 36752 D


T-33-19

TIP30, TIP30A, TIP30B, TIP30C,
TIP30D, TIP30E, TIP30F
P-N-P SILICON POWER TRANSISTORS


JULY 1968 - REVISED OCTOBER 1984

- Designed for Complementary Use With TIP29 series
- 30 W at 25°C Case Temperature
- 1 A Continuous Collector Current
- 3 A Peak Collector Current
- Minimum f_T of 3 MHz at 10 V, 0.2 A
- Customer Specified Selections Available
- Designed for Power Amplifier and High-Speed Switching Applications

device schematic



TO-220AB PACKAGE



absolute maximum ratings at 25°C case temperature (unless otherwise noted)

	TIP30	TIP30A	TIP30B	TIP30C
Collector-base voltage	- 80 V	- 100 V	- 120 V	- 140 V
Collector-emitter voltage ($I_B = 0$)	- 40 V	- 60 V	- 80 V	- 100 V
Emitter-base voltage	- 5 V			
Continuous collector current	- 1 A			
Peak collector current (see Note 1)	- 3 A			
Continuous base current	- 0.4 A			
Safe operating area at 25°C case temperature	See Figure 4			
Continuous device dissipation at 25°C case temperature (see Note 2)	30 W			
Continuous device dissipation at (or below) 25°C free-air temperature (see Note 3)	2 W			
Unclamped inductive load energy (see Note 4)	32 mJ			
Operating collector junction and storage temperature range	- 65°C to 150°C			
Lead temperature 3,2 mm (0.125 inch) from case for 10 seconds	250°C			

NOTES: 1. This value applies for $t_W \leq 0.3$ ms, duty cycle $\leq 10\%$.
 2. Derate linearly to 150°C case temperature at the rate of 0.24 W/°C.
 3. Derate linearly to 150°C free-air temperature at the rate of 16mW/°C.
 4. This rating is based on the capability of the transistor to operate safely in the circuit in Figure 2.

8961726 TEXAS INSTR (OPTO)

62C 36753 D

TIP30, TIP30A, TIP30B, TIP30C,
TIP30D, TIP30E, TIP30F
P-N-P SILICON POWER TRANSISTORS

T-33-19

absolute maximum ratings at 25°C case temperature (unless otherwise noted)

	TIP30D	TIP30E	TIP30F
Collector-base voltage	-160 V	-180 V	-200 V
Collector-emitter voltage ($I_B = 0$)	-120 V	-140 V	-160 V
Emitter-base voltage	-5 V		
Continuous collector current	-1 A		
Peak collector current (see Note 1)	-3 A		
Continuous base current	-0.4 A		
Safe operating area at 25°C case temperature	See Figure 4		
Continuous device dissipation at 25°C case temperature (see Note 2)	30 W		
Continuous device dissipation at (or below) 25°C free-air temperature (see Note 3)	2 W		
Unclamped inductive load energy (see Note 4)	32 mJ		
Operating collector junction and storage temperature range	-65°C to 150°C		
Lead temperature 3,2 mm (0.125 inch) from case for 10 seconds	250°C		

- NOTES: 1. This value applies for $t_W \leq 0.3$ ms, duty cycle $\leq 10\%$.
 2. Derate linearly to 150°C case temperature at the rates of 0.24 W/°C.
 3. Derate linearly to 150°C free-air temperature at the rate of 16 mW/°C.
 4. This rating is based on the capability of the transistor to operate safely in the circuit in Figure 2.

electrical characteristics at 25°C case temperature

PARAMETER	TEST CONDITIONS	TIP30			TIP30A			TIP30B			TIP30C			UNIT
		MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	MIN	TYP	MAX	
$V_{(BR)CEO}$	$I_C = -30$ mA, $I_B = 0$, See Note 5	-40			-60			-80			-100			V
I_{CEO}	$V_{CE} = -30$ V, $I_B = 0$		-0.3			-0.3						-0.3		mA
	$V_{CE} = -60$ V, $I_B = 0$							-0.3					-0.3	
I_{CES}	$V_{CE} = -80$ V, $V_{BE} = 0$		-0.2											mA
	$V_{CE} = -100$ V, $V_{BE} = 0$				-0.2									
	$V_{CE} = -120$ V, $V_{BE} = 0$							-0.2						
	$V_{CE} = -140$ V, $V_{BE} = 0$											-0.2		
I_{EBO}	$V_{EB} = -5$ V, $I_C = 0$		-1		-1			-1			-1			mA
h_{FE}	$V_{CE} = -4$ V, $I_C = -0.2$ A, See Notes 5 and 6	20			20			20			20			
	$V_{CE} = -4$ V, $I_C = -1$ A, See Notes 5 and 6	15	75		15	75		15	75		15	75		
V_{BE}	$V_{CE} = -4$ V, $I_C = -1$ A, See Notes 5 and 6		-1.3		-1.3			-1.3			-1.3			V
$V_{CE(sat)}$	$I_B = -125$ mA, $I_C = -1$ A, See Notes 5 and 6		-0.7		-0.7			-0.7			-0.7			V
h_{fe}	$V_{CE} = -10$ V, $I_C = -0.2$ A, $f = 1$ kHz	20			20			20			20			
$ h_{fe} $	$V_{CE} = -10$ V, $I_C = -0.2$ A, $f = 1$ MHz	3			3			3			3			

- NOTES 5. These parameters must be measured using pulse techniques, $t_W = 300 \mu s$, duty cycle $\leq 2\%$.
 6. These parameters are measured using voltage-sensing contacts separate from the current-carrying contacts.

TIP Devices

8961726 TEXAS INSTR (OPTO)

62C 36754 D

TIP30, TIP30A, TIP30B, TIP30C,
TIP30D, TIP30E, TIP30F
P-N-P SILICON POWER TRANSISTORS

electrical characteristics at 25°C case temperature

T-33-19

PARAMETER	TEST CONDITIONS	TIP30D	TIP30E	TIP30F	UNIT
		MIN TYP MAX	MIN TYP MAX	MIN TYP MAX	
$V_{(BR)CEO}$	$I_C = -30 \text{ mA}$, See Note 5	-120	-140	-160	V
I_{CEO}	$V_{CE} = -90 \text{ V}$, $I_B = 0$	-0.3	-0.3	-0.3	mA
I_{CES}	$V_{CE} = -90 \text{ V}$, $V_{BE} = 0$	-0.2			mA
	$V_{CE} = -180 \text{ V}$, $V_{BE} = 0$		-0.2		
	$V_{CE} = -200 \text{ V}$, $V_{BE} = 0$			-0.2	
I_{EBO}	$V_{EB} = -5 \text{ V}$, $I_C = 0$	-1	-1	-1	mA
h_{FE}	$V_{CE} = -4 \text{ V}$, $I_C = -0.2 \text{ A}$, See Notes 5 and 6	40	40	40	
	$V_{CE} = -4 \text{ V}$, $I_C = -1 \text{ A}$, See Notes 5 and 6	15	15	15	
V_{BE}	$V_{CE} = -4 \text{ V}$, $I_C = -1 \text{ A}$, See Notes 5 and 6	-1.3	-1.3	-1.3	V
$V_{CE(sat)}$	$I_B = -125 \text{ mA}$, $I_C = -1 \text{ A}$, See Notes 5 and 6	-0.7	-0.7	-0.7	V
h_{fe}	$V_{CE} = -10 \text{ V}$, $I_C = -0.2 \text{ A}$, $f = 1 \text{ kHz}$	20	20	20	
$ h_{fe} $	$V_{CE} = -10 \text{ V}$, $I_C = -0.2 \text{ A}$, $f = 1 \text{ MHz}$	3	3		

NOTES: 5. These parameters must be measured using pulse techniques, $t_W = 300 \mu\text{s}$, duty cycle $\leq 2\%$.

6. These parameters are measured with voltage-sensing contact separate from the current-carrying contacts.

thermal characteristics

PARAMETER	MIN	TYP	MAX	UNIT
$R_{\theta JC}$		4.17		°C/W
$R_{\theta JA}$		62.5		

resistive-load switching characteristics at 25°C case temperature

PARAMETER	TEST CONDITIONS†			MIN	TYP	MAX	UNIT
t _{on}	I _C = -1 A,	I _{B1} = -0.1 A,	I _{B2} = 0.1 A,	0.3			μs
t _{off}	V _{BE(off)} = 4.3 V,	R _L = 30 Ω,	See Figure 1	1			

† Voltage and current values shown are nominal; exact values vary slightly with transistor parameters.

5

TIP Devices


8961726 TEXAS INSTR (OPTO)

62C 36755 D


TIP30, TIP30A, TIP30B, TIP30C,
TIP30D, TIP30E, TIP30F
P-N-P SILICON POWER TRANSISTORS

T-33-19

PARAMETER MEASUREMENT INFORMATION



TEST CIRCUIT



VOLTAGE WAVEFORMS

- NOTES: A. V_{gen} is a 30-V pulse into a 50 Ω termination.
B. The V_{gen} waveform is supplied by the following characteristics: $t_r \leq 15$ ns, $t_f \leq 15$ ns, $Z_{out} = 50 \Omega$, $t_w = 20 \mu$ s, duty cycle $\leq 2\%$.
C. Waveforms are monitored on an oscilloscope with the following characteristics: $t_r \leq 15$ ns, $R_{in} \geq 10$ M Ω , $C_{in} \leq 11.5$ pF.
D. Resistors must be noninductive types.
E. The d-c power supplies may require additional bypassing in order to minimize ringing.

FIGURE 1. RESISTIVE-LOAD SWITCHING

TIP Devices


8961726 TEXAS INSTR (OPTO)

62C 36756 D


TIP30, TIP30A, TIP30B, TIP30C,
TIP30D, TIP30E, TIP30F
P-N-P SILICON POWER TRANSISTORS

PARAMETER MEASUREMENT INFORMATION

T-33-19



TEST CIRCUIT



VOLTAGE AND CURRENT WAVEFORMS

NOTES: A. L1 and L2 are 10 mH, 0.11 Ω , Chicago Standard Transformer Corporation C-2688, or equivalent.
B. Input pulse duration is increased until $I_{CM} = -1.8$ A

FIGURE 2. INDUCTIVE-LOAD SWITCHING

5

TIP Devices

8961726 TEXAS INSTR (OPTO)

62C 36757 D

TIP30, TIP30A, TIP30B, TIP30C,
TIP30D, TIP30E, TIP30F
P-N-P SILICON POWER TRANSISTORS

T-33-19

TYPICAL CHARACTERISTICS

STATIC FORWARD CURRENT TRANSFER RATIO
vs
COLLECTOR CURRENT




FIGURE 3

NOTES: 5. These parameters must be measured using pulse techniques, $t_w = 300 \mu s$, duty cycle $\leq 2\%$.

6. These parameters are measured with voltage-sensing contacts separate from the current-carrying contacts.

MAXIMUM SAFE OPERATING AREA

FORWARD-BIAS SAFE OPERATING AREA




FIGURE 4

NOTE 7: This combination of maximum voltage and current values may be achieved only when switching from saturation to cutoff with a clamped inductive load.

TIP Devices

8961726 TEXAS INSTR (OPTO)

62C 36758 D

TIP30, TIP30A, TIP30B, TIP30C,
TIP30D, TIP30E, TIP30F
P-N-P SILICON POWER TRANSISTORS

THERMAL INFORMATION

T-33-19




FIGURE 5



TIP Devices