

## TE Series 1200VA Tower Line-Interactive 120V UPS with serial port

MODEL NUMBER: **TE1200**



### Highlights

- 6 outlets
- Automatic Voltage Regulation (AVR) corrects brownouts and overvoltages
- Larger scale battery produces significantly longer runtimes
- Serial port works with software to facilitate unattended shutdown
- \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Package Includes

- TE1200 UPS System
- Warranty information
- Instruction manual

### Description

Tripp Lite's TE1200 UPS System provides line-interactive voltage regulation and long lasting battery support for mid-size business telephone systems, voicemail systems, personal computers and other communications, network and telecom applications. 1200VA power handling capacity and large capacity battery system maintains continuous operation through power interruptions with over 2 hours runtime for many phone systems and over 1 hour for larger systems. Line interactive voltage regulation maintains normal 120 volt output levels during brownouts as low as 75V and overvoltages as high as 147V, saving battery reserves for use only during complete power failures. Includes 6 outlets, diagnostic LEDs and a built-in serial port that works with Free PowerAlert Software and cabling to provide automatic unattended shutdown of network and PC applications. \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- Provides connected equipment with continuous power during short and long duration loss of commercial power
- Line-interactive voltage regulation corrects brownouts and overvoltages from 75 to 147 volts back to usable 120V output levels, without using battery power
- Supports loads up to 1200VA/940 watts
- 16 minutes half load runtime (600VA/470 watts), 7 minutes full load runtime (1200VA/940 watts)
- 6 protected outlets; 6-ft. cord
- DB9 network interface
- Complete surge protection and EMI/RFI noise filtering
- \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- 5 diagnostic LEDs indicate AC present, on battery, voltage correction, overload & battery low/replace
- Battery replacement door

## Specifications

### OUTPUT



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Output Volt Amp Capacity (VA)	1200
Output kVA Capacity (kVA)	1.2
Output Watt Capacity (Watts)	940
Nominal Output Voltage(s) Supported	115V; 120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	115V (+/- 5%)
UPS Output Receptacles	6 5-15R outlet(s)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
<b>INPUT</b>	
Rated input current (Maximum Load)	8.25A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
<b>BATTERY</b>	
Full Load Runtime (min.)	7 min. (940w)
Half Load Runtime (min.)	16 min. (470w)
DC System Voltage (VDC)	36
Battery Recharge Rate (Included Batteries)	Less than 8 hours from 10% to 90%
Internal UPS Replacement Battery Cartridge	<a href="#">RBC53</a>
Battery Access	Battery access door
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 93 and 107 are boosted by 14%
Severe Undervoltage Correction	Input voltages between 75 and 92 are boosted by 30%



LEDS ALARMS & SWITCHES	
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (UPSWM - tower mounting kit)
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	12.8 x 7.5 x 9.2
UPS Power Module Dimensions (hwd, cm)	32.4 x 19 x 23.5
UPS Power Module Weight (lbs.)	38
UPS Power Module Weight (kg)	17.3
UPS Shipping Dimensions (hwd / in.)	18.2 x 12 x 13.8
UPS Shipping Dimensions (hwd / cm)	46.4 x 30.5 x 34.9
Shipping Weight (lbs.)	42
Shipping Weight (kg)	19.1
UPS Housing Material	PVC
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	204
Battery Mode BTU / Hr. (Full Load)	277.9



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

AC Mode Efficiency Rating (100% Load)	94%
<b>COMMUNICATIONS</b>	
Communications Interface	DB9 Serial; Contact closure
PowerAlert Software	Free download from <a href="http://www.tripplite.com">www.tripplite.com</a>
Communications Cable	DB9 cable included
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 <a href="#">Ultimate Lifetime Insurance</a>

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.