




C	ZINC DIECAST BODY AND HEAD WITH STEEL COVER, BODY AND COVER FINISHED IN RED EPOXY PAINT HEAD FINISHED IN BLACK EPOXY PAINT
D	RED GLASS FILLED POLYESTER HOUSING AND COVER, ZINC DIECAST HEAD FINISHED IN BLACK EPOXY PAINT
E	ZINC DIECAST BODY AND HEAD WITH STEEL COVER, BODY AND COVER FINISHED IN RED EPOXY PAINT, HEAD FINISHED IN BLACK EPOXY PAINT 3 - CONDUIT

A	1/2" NPT X 1/4 CONDUIT THREAD ADAPTER REQUIRED FOR GSD AND GSE PRODUCT
	1/2" NPT X 1/4 CONDUIT THREAD GSA PRODUCT
	PG 13.5 CONDUIT THREAD NO ADAPTER REQUIRED
	M20 X 1.5 CONDUIT THREAD ADAPTER REQUIRED WITH GSD PRODUCT ONLY
B	PF 1/2 CONDUIT THREAD ADAPTER REQUIRED WITH GSD PRODUCT ONLY

AVAILABLE IN GSC, GSD, AND GSE		AVAILABLE IN GSE ONLY	
01	SNAP-ACTION CONTACTS	40	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
07	SNAP-ACTION CONTACTS (GOLD PLATED CONTACTS)	41	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
03	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)	42	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
33	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)	43	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
06	SLOW-ACTION CONTACTS (2 NORMALLY CLOSED)	44	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
36	SLOW-ACTION CONTACTS (2 NORMALLY CLOSED) (GOLD PLATED CONTACTS)	45	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
46	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)	47	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)



NOTES:

1 - MAXIMUM OPERATING TORQUE - 12 Nm/ 1.1 in-lb

2 - MAXIMUM DISCONNECT TORQUE - 16 Nm/ 1.5 in-lb

3 - MAXIMUM TIGHTENING TORQUE FOR FIXING SCREW - 0.5Nm/4.4in-lb (GSC & GSE PRODUCTS)

4 - 0.339Nm/3 in-lb (GSD PRODUCTS)

5 - IP66/IP67 NEMA 1,4X(INDOOR USE ONLY),12,13 FOR GSD PRODUCTS


ELECTRICAL RATING - 11h = 10A					ENVIRONMENTAL	APPROVALS
SILVER CONTACTS				GOLD PLATED CONTACTS	IP66 NEMA 1, 4, 12, 13  TEMP RANGE: -40°C TO +85°C -40°F TO +185°F STORAGE: -40°C TO +85°C -40°F TO +185°F SHOCK: 50G PER IEC 68-2-27 VIBRATION: 100G PER IEC 68-2-6	  IEC 947-5-1 EN50047
AC FOR SWITCH CODES 01, 07, 03, 33	AC FOR SWITCH CODES 06, 36	AC FOR SWITCH CODES 40,41,42,43,44,45,46,47	DC			
A600 AC15 Ue Ie	A500 AC15 Ue Ie	A300 AC15 Ue Ie	Q300 DC13 Ue Ie			
VOLTS AMPS 120 6 240 3 380 1.9 480 1.5 500 1.4 600 1.2	VOLTS AMPS 120 6 240 3 380 1.9 480 1.5 500 1.4	VOLTS AMPS 120 6 240 3	VOLTS AMPS 125 0.55 250 0.27			
				1V 10uA MIN 50V 100mA MAX		

CONTACT CLOSED


CONTACT OPEN

** POSITIVE OPENING TO IEC 947-5-1


M	GS SERIES CHART 2
----------	--------------------------




ACTUATOR CODE 2




ACTUATOR CODE 3



ACTUATOR CODE 3



THIRD ANGLE PROJECTION			
			
SCALE		FULL	
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DIMENSION UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 1			
DIM. NO PLACES ONE PLACE TWO PLACES THREE PLACES ANGLES		TOL. UNLESS NOTED 0.47, 0.1 0.47, 0.1 0.13, 0.006	
		DIM. NO PLACES ONE PLACE TWO PLACES THREE PLACES ANGLES	
		TOL. UNLESS NOTED 0.47, 0.1 0.47, 0.1 0.13, 0.006	
SI METRIC ☒		US CUSTOMARY ☐	
DESIGN UNITS		TBD	
WEIGHT		TBD	