









RECOMMENDED PANEL MOUNT
OPENING, MAXIMUM PANEL
THICKNESS .080/2.03



NOTES:

1. MATERIALS:
HOUSING: POLYESTER (PBT), GLASS FILLED, UL94 V-0,
COLOR: BLACK
TERMINALS: COPPER ALLOY
GASKET: EPDM RUBBER
2. PRODUCT SPECIFICATION: PS-19432-001
3. PACKAGING SPECIFICATION: PK-19436-001
GASKETS, IF REQUIRED FOR THE ASSEMBLIES, ARE BULK PACKAGED IN A SEPARATE BAG.
4. USE WITH MALE CRIMP TERMINAL SERIES 19431.
5. MATES WITH 19432 SERIES RECEPTACLE ASSEMBLIES.
6. RECOMMENDED MOUNTING HARDWARE: (2) #10 X .62/15.8 LONG PLASTIC THREAD CUTTING SCREWS. RECOMMENDED TORQUE 15-17 IN-LBS. SUGGESTED SOURCE: ITW SHAKEPROOF INDUSTRIAL BOSSCREW OR EQUIVALENT.
7. ASSEMBLY IS ROHS COMPLIANT.

19436-0414	8	NO
19436-0413	12-10	
19436-0412	8	
19436-0411	12-10	YES
MATERIAL NUMBER	WIRE AWG	PANEL GASKET

UPDATE GASKET MATL & GASKET PKG EC NO: IPG2012-0303 2012/02/20 DRWN:WLEUNG CHKD: APPR:DTITUS 2012/02/28	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
		 =0  =0		mm	INCH	DRAWN BY DMYRICK	DATE 2007/4/23	TITLE 4 WAY SEALED PLUG PANEL MOUNT ASSEMBLY, 12-10 & 8 AWG		
			4 PLACES	± ---	± ---	CHECKED BY JPWLICKI	DATE 2007/4/23	 MOLEX INCORPORATED		
			3 PLACES	± ---	± .015					
			2 PLACES	± 0.38	± ---	APPROVED BY DTITUS	DATE 2009/10/22			DOCUMENT NO. SD-19436-002
			1 PLACE	± ---	± ---					SHEET NO. 1 OF 1
		ANGULAR ± 1 °								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						