






Part No. & Date code Printing




ORDERING INFORMATION

SERIES	D B P V 25 P O 64 C T X XXX LF	LEAD FREE
SHELL SIZE	E,A,B,C,D	APPLICABLE ONLY FOR DP SERIES
CHARACTERISATION	M-DM SERIES P-DP SERIES	SPECIAL CODE
OPTIONS	BLANK-STANDARD F-FLOAT MOUNTING L-CLINCH NUT (M3) O-CLINCH NUT (UNC) V-FEM. SCREW LOCK HEX. (UNC) N-THR FEM. SCREW LOCK M3	DIMPLES - OPTIONAL X-ON MALE DP CONNECTORS ONLY
NO.OF CONTACTS	09,15,25,37,50	SHELL PLATING
CONTACTS	P - PIN S - SOCKET	BLANK-ZINC for DP/CADMIUM for DM T-STD (Only for DP). TIN over Cu or Zinc Cr 3
TERMINATION TYPE	O-SOLDER BUCKET	OPTIONS
		BLANK-STANDARD H-SHIELDING TERMINATION FINGERS (Only for DP) N- OBLIGATORY FOR DM
		CONTACT PLATING
		64 - 200 MATING CYCLES 65 - 500 MATING CYCLES 32 - 1.27µ Au

"This LF product meets European Union Directives and other country regulations as described in GS-47-0004"


Packaging as per GS-14-920

WITH SHIELDING TERMINATION FINGERS




OPTION: H


MALE LEVER LOCK

ORD CODE 8630-3427(EABC)
,, 8630-3428(D)

FEMALE LEVER LOCK


ORD CODE 8630-3425(EABC)
,, 8630-3426(D)

FEMALE SCREW LOCK



8630-01	M3	M3
8630-01A	M3	4-40 UNC 2
8630-01B	4-40 UNC 2A	4-40 UNC 2B
ORD-CODE	EXTERNAL THREAD	INTERNAL THREAD

FEMALE SCREW LOCK EXTEND TYPE



ORD CODE 8630-01-061

TECHNICAL SPECIFICATIONS

SHELLS	: TIN/CADMIUM/ZINC PLATED STEEL
INSULATOR MATERIAL	: SELF EXTINGUISHING THERMOPLASTIC- TO UL CLASS 94 V0 HOUSING WILL WITHSTAND EXPOSURE TO 260-265°C IF USE PROTECTIVE ADHESIVE (type Kapton or Teflon) OR PROTECTIVE METALLIC DEVICE
CONTACT DIA ON ACTIVE AREA:	Ø1 MM.
CONTACTS MATERIAL	: COPPER ALLOY
CONTACT PLATING	: GXT / GOLD OVER NICKEL
OPERATING TEMPERATURE	: -55°C +125°C
OPERATING CURRENT	: 7.5 A PER CONTACT
CONTACT RESISTANCE	: ≤7.3 mΩ
INSULATION RESISTANCE	: ≥5000 MΩ
MAXIMUM VOLTAGE	: 1000 V.r.m.s
MECHANICAL ENDURANCE	: 500 MATINGS FOR CODE 65 & 32 : 200 MATINGS FOR CODE 64
DAMP HEAT	: 56 DAYS FOR CODE 65 & 32 : 21 DAYS FOR CODE 64

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title D-SUB S/B CONNECTOR (DP&DM SERIES WITH ASSEMBLY OPTIONS)			
N	ELX-I-25321	GREGAR	2016-14-11	angles	linear		dwg no			
				1'±x'		scale NTS	sheet 1 of 1			
				dr	MINI K VANDANATH	1999-03-20	size			
				engr	MITHUN PAUL	2016-14-11	C-DSUB-0068			
				chr	GREGAR MATHEW	2016-14-11	A3			
				appd	BIJU K PAUL	2016-14-11	type Product Customer Drawing			
sheet index	revision	1								
	sheet	1								