

Adapters, Between-Series

Type N / SMA, Economy, DC - 6 GHz

SPECIFICATIONS:

Models: 5061, 5062, 5063, 5064




Electrical:

Frequency Range DC - 6.0 GHz
VSWR 1.25:1 Max.
Impedance 50 Ohms
Operating Temp Range -45°C to +120°C


Mechanical:

Connectors Plated Brass
Conductors Gold Plated Brass or Beryllium Copper


Model Number: 5061
Type N Male /SMA Male




Model Number: 5062
Type N Female /SMA Male



Model Number: 5063
Type N Male /SMA Female



Model Number: 5064
Type N Female /SMA Female



Note: Dimensions in Brackets are Expressed in Millimeters and are for Reference Only.
Design specifications are subject to change without notice.
Contact factory for technical specifications before purchasing or use.

5061: REV E



Aeroflex / Inmet, Inc. • 300 Dino Drive, Ann Arbor, MI 48103 • U.S.A.
888-244-6638 or 734-426-5553 • FAX: 734-426-5557
www.aeroflex.com/inmet • inmetsales@aeroflex.com