

Electrical and Acoustical Parameter

Rated voltage (VDC)	12/24*
Operating voltage (VDC)	9 to 15 / 18 to 28
Current consumption (mA@rated voltage)	110 / 68
Light output (l)	0.7
Flash frequency (Hz)	1
Sound Output (dB(A))	103 / 101
Tones (versions are available with user selectable tones)	Pre-set to tone 5 (12v) Pre-set to tone 3 (24v)
Volume Control (dB)	20
Monitoring	Reverse polarity
Remark:	AUTOMATIC SOUNDER SYNCHRONISATION * 110 to 230Vac with powered base

Mechanical, Environmental Parameter


Contact	screw contact
Operating temperature (°C)	-10 to +55
Storage temperature (°C)	-10 to +55
Material housing	FR ABS + PC (lens)
Colour Housing	Red + withe
Lens Colour	Red, amber, blue, green or clear
IP rating	54(s), 65(d)
Component weight (g)	330
Packaging	box
Remark:	(s) shallow base, (d) deep base

Approval

RoHs	<input checked="" type="checkbox"/>
UL	<input type="checkbox"/>

Designed by	KH	03.08.2011	Dimensions without tolerance ±0.3mm	Index: 00	Current date
Released by	WK	03.08.2011	Drawing number	110803.1SFF	03.08.2011
Changed by					Page 1 of 3







































Drawing of Component



Designed by	KH	03.08.2011	Dimensions without tolerance $\pm 0.3\text{mm}$	Index: 00	Current date
Released by	WK	03.08.2011	Drawing number	03.08.2011	
Changed by			110803.1SFF		Page 2 of 3

Schematic Diagrams and Characteristics

Tone table

TONE DESCRIPTION						
1st TONE	2nd TONE	TYPE	FREQUENCIES	TEMPORAL PATTERN		TYPICAL APPLICATION
1	14	Alternating	800 & 970	2Hz (250ms-250ms)		BS Fire tone
2	14	Sweep	800 to 970	7Hz (7/s)		BS Fire tone
3	14	Sweep	800 to 970	1Hz (1/s)		BS Fire tone
4	14	Continuous	2850	Steady		General purpose
5	4	Sweep	2400 to 2850	7Hz		General purpose
6	4	Sweep	2400 to 2850	1Hz		General purpose
7	14	Slow whoop	500 to 1200	3.5s sweep, 0.5 s silence, then repeat		Dutch tone (NEN 2575)
8	14	Sweep	1200 to 500	1Hz		Din tone (33 404)
9	4	Alternating	2400 & 2850	2Hz (250ms-250ms)		General purpose
10	14	Intermittent	970	0.5Hz (1s On/1s Off)		PFEER alert
11	14	Alternating	800 & 970	1Hz (500ms-500ms)		BS Fire tone
12	4	Intermittent	2850	0.5Hz (1s On/1s Off)		General purpose
13	14	Intermittent	970	0.8Hz (250ms On/1s Off)		General purpose
14	14	Continuous	970	Steady		PFEER Toxic-gas
15	14	Alternating	554 & 440	100ms-400ms		French fire tone
16	16	Intermittent	660	3.3Hz (150ms On/150ms Off)		Swedish (Air raid)
17	17	Intermittent	660	0.28Hz (1.8s On/1.8s Off)		Swedish (Local warning)
18	18	Intermittent	660	0.05Hz (13s Off / 6.5Hz On)		Swedish (Pre-mess)
19	19	Continuous	660	Steady		Swedish (All clear)
20	20	Alternating	554 & 440	0.5Hz (1s On/1s Off)		Swedish (Turn out)
21	21	Intermittent	660	1Hz (500ms-500ms)		Swedish tone
22	14	Intermittent	2850	4Hz (150ms On/100ms Off)		Pelican crossing
23	14	Sweep	800 to 970	50Hz		BS Fire tone
24	4	Sweep	2400 to 2850	50Hz		General purpose
25	25	Intermittent	970	3 x 500ms pulses followed by 1.5s silence then repeat		ISO 8201 / Australia
26	26	Intermittent (I)	800 to 970	3 x 500ms pulsed sweep followed by 1.5s silence then repeat		ISO 8201 / Australia
27	27	Intermittent (I)	970 & 800	3 x 500ms pulsed two tone followed by 1.5s silence then repeat		ISO 8201 / Australia
28	10	Alternating	800 & 970	2Hz (250ms-250ms)		BS Fire tone
29	33	Alternating	990 & 650	2Hz (250ms-250ms) (Symphoni tones)		BS Fire tone
30	35	Alternating	510 & 610	2Hz (250ms-250ms) (Squashni Micro tones)		BS Fire tone
31	14	Sweep	300 to 1200	1Hz		General purpose
32	35	Alternating	510 & 610	1 Hz (500ms-500ms)		BS Fire tone
33	(1)	Continuous	990	Steady		BS Fire tone
34	(1)	Intermittent	990	1Hz (500ms On/500ms Off)		BS Fire tone
35	(1)	Continuous	510	Steady		BS Fire tone
36	(1)	Intermittent	510	1Hz (500ms On/500ms Off)		BS Fire tone
37	(1)	Continuous	850	Steady		BS Fire tone
38	(1)	Continuous	2650	Steady		General purpose

Reliability test

n.a.

Packaging Information

n.a.

Designed by	KH	03.08.2011	Dimensions without tolerance ±0.3mm	Index: 00	Current date
Released by	WK	03.08.2011	Drawing number 110803.1SFF		03.08.2011
Changed by					Page 3 of 3