


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0876313047](#)
Status: **Active**
Overview: [EXTreme PowerPlus™ \(SSI\)](#)
Description: 6.35mm Pitch Power, 3.18mm, 2.54mm Pitch Signal, EXTreme PowerPlus™ P-S-P Header, Through Hole, Right Angle, Long Contacts, 28 Circuits, Power Alpha 2, Signal 24, Power Beta 2, Recessed Signal Pins at A6, B6, C6, D6, Lead-Free

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-87631-006 \(PDF\)](#)
[Application Specification AS-87631-018 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19980
General	
Product Family	PCB Headers
Series	87631
Application	Board-to-Board, Power
Comments	Long Contacts Recessed Signal Pins: A6, B6, C6, D6
Overview	EXTreme PowerPlus™ (SSI)
Product Name	EXTreme PowerPlus™
UPC	822350815628
Physical	
(p)ower-(s)ignal Configuration	2p - 24s - 2p
Breakaway	No
Circuits (Loaded)	28
Circuits (maximum)	28
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	Yes
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	19.880/g
Number of Rows	4
Orientation	Right Angle
PC Tail Length	3.43mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm, 6.35mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No



Series image - Reference only

EU ELV
Not Relevant

EU RoHS
Compliant
REACH SVHC
Not Contained Per -
ED/21/2016 (20 June
2016)
Halogen-Free
Status
Low-Halogen
**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[87631](#) Series

Mates With
[87633](#) Vertical Press-Fit Receptacle, [87622](#)
Vertical Through Hole Receptacle, [87632](#)
Right Angle Through Hole Receptacle

Temperature Range - Operating	-20°C to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	2.5A, 30.0A, 50.0A
Voltage - Maximum	250V DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-87631-018
Product Specification	PS-87631-006
Sales Drawing	SD-87631-013

This document was generated on 10/21/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION