

EMI FILTER & TVS ARRAY**APPLICATIONS**

- ✓ Cellular Phones
- ✓ SMART Cards
- ✓ Notebooks & Handheld Devices
- ✓ Personal Digital Assistants (PDAs)
- ✓ Ground Positioning Systems (GPS)

IEC COMPATIBILITY (EN61000-4)



- ✓ 61000-4-2 (ESD): Air - 15kV, Contact - 8kV
- ✓ 61000-4-4 (EFT): 40A - 5/50ns

FEATURES

- ✓ ESD Protection > 25 kilovolts
- ✓ 175 Watts Peak Pulse Power per Line (8/20μs)
- ✓ Bidirectional EMI Filtering
- ✓ Low Insertion Loss: Up to 10MHz, -3db Roll-Off @ 50MHz
- ✓ Protects Up to Two (2) Data Lines

MECHANICAL CHARACTERISTICS

- ✓ Molded JEDEC SC-70-5L
- ✓ Weight 0.1 grams (Approximate)
- ✓ Flammability Rating UL 94V-0
- ✓ 8mm Tape and Reel Per EIA Standard 481-1-A
- ✓ Device Marking: Marking Code



**PIN CONFIGURATION****CIRCUIT DIAGRAM**

DEVICE CHARACTERISTICS





MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power ($t_p = 8/20\mu s$) - See Figure 1	P_{PP}	175	Watts
Operating Temperature	T_J	-55°C to 150°C	°C
Storage Temperature	T_{STG}	-55°C to 150°C	°C
Typical Series Resistance per Line	R	50	Ohms

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified							
PART NUMBER	DEVICE MARKING	RATED STAND-OFF VOLTAGE	MINIMUM BREAKDOWN VOLTAGE	MAXIMUM REVERSE LEAKAGE CURRENT	MAXIMUM REVERSE LEAKAGE CURRENT	TYPICAL CAPACITOR (PER LINE)	MAXIMUM CAPACITANCE (See Note 1)
		V_{WM} VOLTS	@ 1mA $V_{(BR)}$ VOLTS	$V_{WM} = 5V$ I_D μA	$V_{WM} = 3.3V$ I_D μA	0V @ 1MHZ C_J pF	0V @ 1 MHz C_{TOT} pF
STF701	05F	5.0	6.0	5.0	1.0	40	160

Note 1: Capacitance measured between input and output, per line.



GRAPHS



PACKAGE OUTLINE & DIMENSIONS

PACKAGE OUTLINE

Top view dimensions: A (total width), B (body width), C (lead width), D (lead thickness), E (lead height), F (lead pitch), G (lead spacing), H (lead length), I (lead width), J (lead angle), K (body height), L (lead angle), M (lead length).

Side view dimensions: A (total width), B (body width), C (lead width), D (lead thickness), E (lead height), F (lead pitch), G (lead spacing), H (lead length), I (lead width), J (lead angle), K (body height), L (lead angle), M (lead length).

Side view dimensions: A (total width), B (body width), C (lead width), D (lead thickness), E (lead height), F (lead pitch), G (lead spacing), H (lead length), I (lead width), J (lead angle), K (body height), L (lead angle), M (lead length).

SC 70-5L

PACKAGEDIMENSIONS

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	1.90	2.15	0.074	0.084
B	1.15	1.35	0.045	0.055
C	0.80	1.00	0.031	0.040
D	0.15	0.30	0.006	0.012
E	0.65 BSC	-	0.0255 BSC	-
F	1.30 BSC	-	0.0512 BSC	-
G	0.80	1.10	0.031	0.043
J	0.08	0.25	0.003	0.010
K	2.00	2.20	0.078	0.086
L	0	0.10	0	0.004
M	0.26	0.46	0.010	0.018

MOUNTING PAD

TYPICAL		
DIM	Millimeters	Inches
1	0.50	0.020
2	1.30	0.051
3	0.65	0.026
4	2.40	0.094
5	0.60	0.024
6	0.70	0.028
7	2.50	0.098

Mounting pad dimensions: 1 (pad width), 2 (pad length), 3 (pad thickness), 4 (pad width), 5 (pad length), 6 (pad thickness), 7 (pad width).


NOTES:

1. Dimensioning and tolerances per ANSI Y14.5M, 1985.
2. Controlling Dimension: Inches
3. Dimensions are exclusive of mold flash and metal burrs.

06005 Rev 0 - 11/01

MOUNTING PAD

TYPICAL		
DIM	Millimeters	Inches
1	0.50	0.020
2	1.30	0.051
3	0.65	0.026
4	2.40	0.094
5	0.60	0.024
6	0.70	0.028
7	2.50	0.098



NOTES:

1. Dimensioning and tolerances per ANSI Y14.5M, 1985.
2. Controlling Dimension: Inches
3. Dimensions are exclusive of mold flash and metal burrs.

06005 Rev 0 - 11/01

TAPE & REEL PACKAGING:

Surface mount product is taped and reeled in accordance with EIA-481, reel quantities and sizes are as follows:

7 Inch Reel - 3,000 pieces per reel; 13 Inch Reel - Not Available

ProTek Devices

2929 South Fair Lane, Tempe, AZ 85282

Tel: 602-431-8101 Fax: 602-431-2288

E-Mail: sales@protekdevices.com

Web Site: www.protekdevices.com

COPYRIGHT © ProTek Devices 2001

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.