



July 2016

Chip beads

For power line

High GHz noise countermeasure (high-speed signal line)

MPZ-V series

MPZ1005-V Type

MPZ1005-V 1005[0402 inch]*

* Dimensions code JIS[EIA]

Reminders for using these products

Before using these products, be sure to request the delivery specifications.

Safety reminders

Please pay sufficient attention to the warnings for safe designing when using this products.

Reminders

- The storage period is less than 12 months. Be sure to follow the storage conditions (temperature:5 to 40°C, humidity:10 to 75% RH or less).
If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
- Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- Before soldering, be sure to preheat components.
The preheating temperature should be set so that the temperature difference between the solder temperature and chip temperature does not exceed 150°C.
- Soldering corrections after mounting should be within the range of the conditions determined in the specifications.
If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
- When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
- Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
- Carefully lay out the coil for the circuit board design of the non-magnetic shield type.
A malfunction may occur due to magnetic interference.
- Use a wrist band to discharge static electricity in your body through the grounding wire.
- Do not expose the products to magnets or magnetic fields.
- Do not use for a purpose outside of the contents regulated in the delivery specifications.
- The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.
The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.
If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us.

| | |
|-------------------------------------------------------------------|------------------------------------------------------------------------------|
| (1) Aerospace/aviation equipment | (8) Public information-processing equipment |
| (2) Transportation equipment (cars, electric trains, ships, etc.) | (9) Military equipment |
| (3) Medical equipment | (10) Electric heating apparatus, burning equipment |
| (4) Power-generation control equipment | (11) Disaster prevention/crime prevention equipment |
| (5) Atomic energy-related equipment | (12) Safety equipment |
| (6) Seabed equipment | (13) Other applications that are not considered general-purpose applications |
| (7) Transportation control equipment | |

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.

Chip beads

Product compatible with RoHS directive
Halogen-free
Compatible with lead-free solders

For power line

High GHz noise countermeasure (high-speed signal line)

Overview of MPZ1005-V type

■ FEATURES

- 1005 shape type noise reduction component for power line.
- Compared to the MPZ-E series, it can attain high impedance at GHz bands.
- Exerts an excellent noise reduction effect against noise interfering at several GHz such as LTE or Wi-Fi, or against high-frequency noise.
- Achieves particularly high impedances in the range from 0.7GHz to 5GHz, enabling a reduction of noise that could not be reduced using the conventional MPZ-E series.
- Highly reliable monolithic structure with multilayer integration.

■ APPLICATION

- Ensuring communication sensitivity of wireless communication using high-speed signals such as LTE or Wi-Fi
- Noise removal for mobile devices such as smartphones and tablet terminals, and various modules.
- Noise removal for PCs and recorders, household appliances such as STBs, smart grids, and industrial equipment.

■ PART NUMBER CONSTRUCTION


| | | | | | | |
|-------------|-----------------------|---------------|-------------------------|---------------------|-----------------|---------------|
| MPZ | 1005 | AFZ | 150 | V | T | 000 |
| Series name | LxWxT dimensions (mm) | Material name | Impedance (Ω) at 100MHz | Characteristic type | Packaging style | Internal code |
| 1005 | 1.0x0.5x0.5 | AFZ | 150 | 15 | T Taping | 000 |

■ OPERATING TEMPERATURE RANGE, PACKAGE QUANTITY, PRODUCT WEIGHT

| Type | Temperature ranges | | Package quantity | Individual weight |
|-----------|----------------------------|---------------------------|------------------|-------------------|
| | Operating temperature (°C) | Storage temperature* (°C) | (pieces/reel) | (mg) |
| MPZ1005-V | -55 to +125 | -55 to +125 | 10,000 | 1 |


* The storage temperature range is for after the circuit board is mounted.

- RoHS Directive Compliant Product: See the following for more details.<https://product.tdk.com/info/en/environment/rohs/index.html>
- Halogen-free: indicates that Cl content is less than 900ppm, Br content is less than 900ppm, and that the total Cl and Br content is less than 1500ppm.

 Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use.
Please note that the contents may change without any prior notice due to reasons such as upgrading.

MPZ1005-V type

■ RECOMMENDED REFLOW PROFILE




| Preheating | | | Soldering | | Peak | |
|-------------|-------------|------------------|-------------|-----------------|--------------------|-----------|
| Temp. | Time | | Temp. | Time | Temp. | Time |
| T1 150°C | T2 180°C | t1 60 to 120s | T3 230°C | t2 30 to 60s | T4 250 to 260°C | t3 10s |


⚠ Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use.
Please note that the contents may change without any prior notice due to reasons such as upgrading.

MPZ1005-V type

■ SHAPE & DIMENSIONS



■ RECOMMENDED LAND PATTERN



MPZ1005-V type

■ ELECTRICAL CHARACTERISTICS

□ CHARACTERISTICS SPECIFICATION TABLE


| Impedance | | DC resistance | | Rated current | Part No. |
|-----------------|---------------|---------------|---------|---------------|--------------------|
| [100MHz] (Ω) | [1GHz] (Ω) | Tolerance | (Ω)max. | (A)max. | |
| 15 | 80 | ±40% | 0.300 | 0.80 | MPZ1005AFZ150VT000 |
| 30 | 170 | ±40% | 0.450 | 0.60 | MPZ1005AFZ300VT000 |

Measurement equipment

| Measurement item | Product No. | Manufacturer |
|------------------|---------------|-----------------------|
| Impedance | E4991A+16192A | Keysight Technologies |
| DC resistance | Type-7556 | Yokogawa |

* Equivalent measurement equipment may be used.

Rated current vs. temperature characteristics (derating)




MPZ1005-V type

■ ELECTRICAL CHARACTERISTICS

Z VS. FREQUENCY CHARACTERISTICS (BY SERIES)

MPZ1005AFZ-V series




MPZ1005-V type


■ ELECTRICAL CHARACTERISTICS

□ Z, X, R VS. FREQUENCY CHARACTERISTICS

MPZ1005AFZ150VT000




MPZ1005AFZ300VT000



MPZ1005-V type


■ PACKAGING STYLE

□ REEL DIMENSIONS




Dimensions in mm

□ TAPE DIMENSIONS



Dimensions in mm

| Type | A | B | P1 | K |
|-----------|----------|----------|----------|---------|
| MPZ1005-V | 0.65±0.1 | 1.15±0.1 | 2.0±0.05 | 0.8max. |



Dimensions in mm

⚠ Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use.
Please note that the contents may change without any prior notice due to reasons such as upgrading.