


120 Watts AA20140 Series

Total Power: 70-120 Watts
Input Voltage: 85-264 VAC
of Outputs: Quad



Special Features

- Active power factor correction
- EN61000-3-2 compliance
- Remote sense on outputs one and two
- Industry-standard 4.25" x 7" footprint
- Adjustable main outputs
- Built-in Class B EMI filter
- Overvoltage protection
- Overload protection
- Thermal overload protection

Environmental

Operating temperature: 0° to 50°C ambient; derate each output at 2.5% per degree from 50° to 70°C

Electromagnetic susceptibility: Designed to meet EN61000-4, -2, -3, -4, -5, -6, Level 3

Humidity: Operating; non-condensing
20% to 90%

Vibration: 5-32 Hz sinewave .02" double amplitude
32-2 kHz sinewave 1 G peak

Storage temperature: -40° to 85°C

Temperature coefficient: $\pm 0.04\%$ per °C

MTBF per mil std 217E: >200,000 hours at full load and 30°C ambient conditions and full load

Electrical Specs

Input

Input range	90-264 VAC
Frequency	47-63 Hz
Inrush current	40 A max., cold start @ 25°C
Efficiency	65% typical at full load
EMI filter	FCC Class B conducted and radiated, CISPR 22 Class B conducted and radiated, EN55022 Class B conducted and radiated, VDE 0878 PT3 Class B conducted and radiated.
Power factor	0.99 typical
Safety ground	
Leakage current	<2 mA @ 50/60 Hz, 254 VAC input

Output

Maximum power	70 W convection; 120 W with 30 CFM forced air
Adjustment range	$\pm 5\%$ minimum on 3.3 V and 5 V outputs
Hold-up time	15 ms @ 120 W load, 115 VAC input
Overload protection	Short circuit protection on all outputs. Case overload protected @ 110-145% above peak rating
Overvoltage protection	3.3 V output: 4.25 V ± 0.25 V 5 V output: 6.25 V ± 0.75 V, 20-35% above nominal output. Latching type recycle AC to reset.
Remote sense	Compensates for 0.5 V lead drop min. Will operate without remote sense connected.

Safety

TUV	EN60950	9837006
UL	UL1950	E186249
CUL	CSA 22.2-234 Level 3	E186249
CB	Certificate and report	DE2-002056
CE	Mark (LVD)	

AMERICAS

5810 Van Allen Way
Carlsbad, CA 92008
Telephone: 760-930-4600
Facsimile: 760-930-0698

EUROPE

Astec House, Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX, UK
Telephone: 44 (1384) 842-211
Facsimile: 44 (1384) 843-355

ASIA

Units 2111-2116, Level 21
Tower1, Metroplaza
223, Hing Fong Road
Fwai Fong, New Territories
Hong Kong
Telephone: 852-2437-9662
Facsimile: 852-2402-4426



Ordering Information

Model Number	Output Voltage	Minimum Load	Maximum Load with Convection Cooling	Maximum Load with 30 CFM Forced Air	Peak Load ¹	Regulation ²	Ripple P/P (PARD) ³
AA20140	+3.3 V	0 A	8 A	16 A	18 A	±2%	50 mV
	+5 V	1 A	10 A	20 A	22 A	±3%	50 mV
	+12 V	0.2 A	1 A	2 A	3 A	±5%	120 mV
	-12 V	0 A	0.5 A	0.5 A	1 A	±10%	120 mV

1. Peak current lasting <30 seconds with a maximum 10% duty cycle.
2. At 25°C including initial tolerance, line voltage, load currents and output voltages adjusted to factory settings.
3. Peak-to-peak with 20 MHz bandwidth and 10 μ F in parallel with a 0.1 μ F capacitor at rated line voltage and load ranges.
4. Minimum loads are required.

Pin Assignments

Connector

SK1	PIN 1	Neutral
	PIN 3	Live
SK2	PIN 1-10	Common
	PIN 11	+5 Sense
	PIN 12	+3.3 V Sense
	PIN 13	+12 V
	PIN 14-17	5 V
	PIN 18-22	3.3 V
	PIN 23	Return Sense
	PIN 24	-12 V

Mating Connectors


(SK1) AC Input: Molex: 09-50-8031 (USA)
Molex: 09-91-03500 (UK)
PINS: 08-58-0111

(SK2) DC Output: Molex: Right angle
39-30-1240 or
39-29-1248
or
Vertical
39-28-1243

Astec Connector Kit #70-841-013, includes all of the above.

Notes:

1. Specifications subject to change without notice.
2. All dimensions in inches (mm), tolerance $\pm .02$ ".
3. Warranty: 1 year
4. Weight: 1.38 lb. / .63 kg



Height is 1.6"