




Single Port PoE Gigabit Switch Powered by IEEE802.3at Extends Ethernet Data and PoE to 200 Meters

IEEE802.3at Midspan



Features

- IEEE802.3af Class 4
- 0-55C Operating Temperature Range
- Gigabit Compatible
- Extends Ethernet to 200 meters
- Powered by IEEE802.3at with Layer 1
- Detects 25K signature resistance
- Boost Circuit to Compensate for Wire Drops
- 1 Year Warranty

Applications

- IP Cameras
- Access Controls
- Wireless Access Points

Safety Approvals

- CE

Mechanical Characteristics

- Length: 120mm (4.72in)
- Width: 60mm (2.36in)
- Height: 32mm (1.26in)
- Weight: 0.6Kg (1.3lb)

Output Specifications

Model	DC Output Voltage			Output Current		Output Power
	Min.	Typ.	Max.	Min.	Max.	
POE16S-1AFG	54V	56V	57V	10mA	330mA	19W

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

INPUT:**Input Source**

Receives power from IEEE802.3at Midspan

Input Detection

25K Detection IEEE802.3at compliance

DC Input Voltage Range

45VDC to 57VDC

DC Input Current

1.0A at 45VDC and maximum load

2.0A at 50VDC and maximum load

0.8A at 57VDC and maximum load

OUTPUT:**Total Output Power**

19W with 33.6W PoE Input

Ripple and Noise (Vp-p)

250mV maximum

Output Detection

25K Detection IEEE802.3af compliance

Efficiency

75% minimum at maximum load

ENVIRONMENTALOperating Temperature 0 to 40°C
(gigabit data rates)Operating Temperature 0 to 55°C
(10Mb and 100Mb data rates)Storage Temperature -25 to +65°C
Humidity 5 to 90%**EMI**

EN55022 Class A, FCC part 15 Class A

Warranty

1 Year

Immunity

ESD EN61000-4-2 Level 3

RS EN61000-4-3 Level 3

Surge EN61000-4-5 Level 2

Isolation (HI-POT)

2121VDC for 1 min, 10mA

Insulation Resistance

Input to Ground: >10M OHM 500VDC

Output to Ground: >10M OHM 500VDC

FEATURES**Over Current Protection**

For PoE Class 0-3 Detection on Output: 450mA maximum

For PoE Class 4 Detection on Output: 650mA maximum

Short Circuit ProtectionOutputs equipped with short circuit protection
The output can be shorted permanently without damage**Indicators**

Ethernet – IN/OUT	Green LED1 and LED2 - 10Mb Activity
	Green LED1 – 100Mb Activity
	Green LED2 – 1Gb Activity
	Orange LED3 – Link Activity

POE

Blinking GREEN – Unit is ON Active with No Load
Solid GREEN – Unit has detected a valid IEEE802.3af load
Blinking RED/GREEN – unit has detected an invalid load
Solid RED – unit is in over-load condition

Input/Output Connectors


RJ45

Input Connection

Pins: 1,2 7,8 GND / Pins: 3,6 4,5 +VIN

Output Connection

Pins: 1,2 GND / Pins: 3,6 +VIN



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phihong:](#)

[POE16S-1AFG-R](#)