




HZ0402A152R-10

UNCONTROLLED
DOCUMENT

PHYSICAL DIMENSIONS:

A	1.00 [.040]	+	0.15 [.006]
B	0.50 [.020]	+	0.15 [.006]
C	0.50 [.020]	+	0.15 [.006]
D	0.30 [.012]	MAX.	



AGILENT E4991A RF Impedance/Material Analyzer
HP 16194A Test Fixture. TEST REF. 6231




ELECTRICAL CHARACTERISTICS:

Z @ 100MHz (Ω)	DCR (Ω)	Rated Current
Nominal	1500	
Minimum	1125	
Maximum	1875	2.00 50 mA

NOTES: UNLESS OTHERWISE SPECIFIED


1. TAPED AND REELED per CURRENT EIA SPECIFICATIONS 7" REELS, 10,000 PCS/REEL, PAPER TAPE.
2. TERMINATION FINISH IS 100% TIN.
3. COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.

LAND PATTERNS FOR REFLow SOLDERING



(For wave soldering, add 0.763 [.030] to this dimension.)

RECOMMENDED SOLDERING CONDITIONS



DIMENSIONS ARE IN mm [INCHES].

This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
PROJECT/PART NUMBER:	HZ0402A152R-10	REV	B
DATE:	07/24/07	SCALE:	NTS
CAD #	HZ0402A152R-10-B	TOOL #	-
REV	INT	DESCRIPTION	DATE
REV	INT	DESCRIPTION	DATE

Laird
TECHNOLOGIES

2 of 2