


DASH NO.	M CODE	MADE FROM
----------	--------	-----------



GSD

M55339/25-00606

REVISIONS	
ISSUE	CHANGES
3	CN 23170E MA 18 MAR 82
4	CN 28988A AMD 15 JUN 87
5	CN 29305 A LI. 70CT87
6	CN 32904 C KH 18 MAR 91
7	CN 34182 C KH 28 OCT 92
8	CN 35618 D ME 10 JAN 95
9	CN 36030 C KH 31 JAN 95

GSD

NOTES:

1. MATERIALS:

LOCKWASHER — PHOSPHOR BRONZE, ASTM-B-103
 CENTER CONTACT — BER. COPPER, ASTM-B-196
 INSULATORS — TEFLON, ASTM-D-4894
 C-RING — HARD DRAWN COPPER WIRE, PER, QQ-W-336.
 O-RING — SYNTHETIC RUBBER, PER MIL-P-25732.
 O-RINGS — PARKER COMPOUND, S-317-0.
 ALL OTHER METAL PARTS — BRASS, ASTM-B16

2. FINISHES

CENTER CONTACT — HARD GOLD PER
 MIL-G-45204.
 ALL OTHER METAL PARTS — SILVER
 PLT PER, QQ-S-365.

3. ELECTRICAL CHARACTERISTICS:

NOMINAL IMPEDANCE — 50 Ω.
 WORKING VOLTAGE — 500 VOLTS RMS.
 FREQUENCY RANGE — DC TO 10 GHz.

4. ENVIRONMENTAL:

SEAL — 30 PSI

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES, FRACTIONS & 2 PLACE DECIMALS ± .010
 3 PLACE DECIMALS ± .004 ANGLES ± 0°30'
 T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY
 NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.

2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
 3. NO FILLETS PERMITTED.
 4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
 5. ALL DIMENSIONS PRIOR TO PLATING.
 6. ALL PLATING IN ACCORDANCE WITH KER 10004.

SCALE	
APPROX SURFACE AREA	
1209-17	
USED ON	
REF	
PRESSURIZED BULKHEAD ADAPTER BNC(F)-N(F)	
DRAWN CT	DATE 8NOV80
APPR	DATE
APPR	DATE
M55339/25-00606	