





NOTES

1 - SILVER PLATED TERMINALS
2 - TESTED TO SHOW COMPLIANCE WITH UL 858 OVEN LATCH REQUIREMENTS
UNDER THE FOLLOWING PARAMETERS: ELECTRICAL ENDURANCE FOR 100K
OPERATIONS AT 200°C FOR 250 HOURS MINIMUM WHILE CONTROLLING AN
INDUCTIVE LOAD OF 6A, 277VAC

CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:		DRAWN	TSM	5FEB02	Honeywell					
OPERATING FORCE----- 66 GRAMS MAX		CONTACT ARRANGEMENT S P N O		NO PLACE X ±.040 ±1		CHECK	SAV	5FEB02						
RELEASE FORCE----- 5 GRAMS MIN				ONE PLACE .X ±.030 ±0,4		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH, BASIC					
DIFFERENTIAL TRAVEL----- .027 MAX		L278		TWO PLACE .XX ±.015 ±0,15										
OVERTRAVEL----- .068 MIN		6A, 1/8HP 125, <u>250</u> OR 277 VAC		THREE PLACE .XXX ±.005 ±		DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED			SIZE DWG TYPE DRAWING NAME REV B I V7-1X2AE9-295 4					
RELEASE TRAVEL----- .016 MIN		(P) 		ANGLES ± ±										
				THIRD ANGLE PROJECTION		PTC 2D ASME Y14.5M-1994			SCALE 2 : 1 WEIGHT SHEET 1 OF 1					
														

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-1X2AE9-295](#)