





1


PRODUCT NUMBER	DIM.	LENGTH FORMULAS
SEE NOTE 1	DIM A	.100/2.54 X NO. OF COLUMNS + 1.150/29.2
	DIM B	.100/2.54 X NO. OF COLUMNS + .850/21.59
	DIM C	.100/2.54 X NO. OF COLUMNS DIVIDED BY 2 - .100/2.54




SECTION U-U



SECTION X-X



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100 [2.54] GRID
UNLESS OTHERWISE SPECIFIED)



SECTION W-W

NOTES:

- PRODUCT NUMBERING CODE:
50273 - X YYY Z
TAIL LENGTH (NOTE 5)
NO. OF POSITIONS (NOTE 2)
PLATING (NOTE 4)
BASE NUMBER
- THIS PRODUCT IS CONFIGURED IN SIZES OF 20 THRU 122 COLUMNS IN INCREMENTS OF TWO.
i.e.: 20,22,24,26.....118,120,122.
- HOUSING MATERIAL: GLASS AND MINERAL FILLED HIGH TEMP. THERMOPLASTIC. FLAME RETARDANT PER UL94V-0. COLOR: BLACK.
CONTACT MATERIAL: BeCu
- PLATING CONTACT AREA OPTIONS:
1 = 30u"/.76u GOLD
3 = 50u"/1.27u GOLD
5 = 30u"/.76u GXT
ALL SOLDER TAILS TIN/LEAD
- TAIL LENGTH OPTIONS:
E = .125±.010 / 3.18±.25
F = .145±.010 / 3.68±.25
H = .180±.010 / 4.57±.25
- MANUFACTURERS NAME, PART NUMBER AND LOT CODE TO APPEAR ON THIS SURFACE PER BUS-12-108.
- FOR DOCUMENTATION MENU, SEE SPEC. BUS-01-057.

mat'l. code	surface	tolerance	projection	product family
-	ISO 1302 ✓	ISO 406 ISO 1101	INCH/MM	HPC
ltr	ecn	no	dr	date
F				
	angles	linear		
	0°±2'	.XX ±.01/.3 .XXX ±.005/.13 .XXXX ±.0020/.051	scale 1:1	
dr	D. SHEAFFER	4/15/92		
enr	S. CLARK	4/22/92		
chr	S. CLARK	4/22/92		
appd	S. CLARK	4/22/92		
sheet	revision			
index	sheet			



title
4 ROW R/A RECEPTACLE
S.T.B., 1 OFFSET GUIDE

dwg no 50273 sheet 2 of 2 size A3

type Product Customer Drawing