

(2.00 mm) .0787"

YTW-12-10-S-6-300-215

YTW-26-02-T-5-250-050

YTW-20-03-G-Q-400-085

YTW SERIES

HIGH-DENSITY BOARD STACKER

SPECIFICATIONS

For complete specifications see www.samtec.com/YTW

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Operating Temp Range:

-55 °C to +105 °C with Tin;

-55 °C to +125 °C with Gold

Plating:

Sn or Au over

50 μ " (1.27 μ m) Ni

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only

RECOGNITIONS


For complete scope of recognitions see www.samtec.com/quality




FILE NO. E111594

Mates with:
YTQ, YTS, YTE

OTHER SOLUTIONS



Paste In Hole (PIH) processing.
Contact Samtec ASP Group.



Choice of 4, 5 or 6 row

(2.00 mm)
.0787" pitch

YTW	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	STACKER HEIGHT	TAIL SPEC
	02 thru 50	Specify LEAD STYLE from chart below.	-G = 20 μ " (0.51 μ m) Gold contact area, Gold flash on tail -S = 30 μ " (0.76 μ m) Gold contact area, Tin on tail (Style -01 & -02 not available) -L = 10 μ " (0.25 μ m) Gold contact area, Tin on tail -T = Tin	-Q = Four Row -5 = Five Row -6 = Six Row	-"XXX" = Stacker Height In inches (0.13 mm) .005" increments Example: -250 = (6.35 mm) .250"	-"XXX" = Tail Length In inches (0.13 mm) .005" increments Example: -150 = (3.81 mm) .150" -"XXX" = Polarized Position

LEAD STYLE	OAL
-01	(8.20) .323
-02	(9.60) .377
-03	(13.60) .535
-04	(14.10) .555
-05	(15.10) .594
-06	(17.10) .673
-07	(19.10) .751
-09	(11.60) .456
-10	(15.60) .614
-11	(10.08) .397

ROW OPTION	STACKER HEIGHT
-Q	(3.05) .120 MIN
-5 & -6	(4.06) .160 MIN

Note:
This Series is non-standard,
non-returnable.

WWW.SAMTEC.COM

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.