





LOC	DIST	REVISIONS			
AJ	16	F	LTR	DESCRIPTION	DATE
		D	OBS	-3 PER 0020-0072-01	16APR01



RECOMMENDED PC BOARD LAYOUTS
SCALE 4:1



RECOMMENDED PANEL CUTOUT
SCALE 4:1



1. POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-0 RATED, COLOR: BLACK
2. POLYMETHYLPENTENE: GENERAL PURPOSE
3. ZINC DIE-CAST PER QQ-Z-363
4. PHOSPHOR BRONZE PER QQ-B-750
5. BRASS PER ASTM-B-453
6. GOLD PLATE PER MIL-G-45204, 0.76µm [0.000030] MIN THICKNESS
7. NICKEL PLATE PER QQ-N-290, 2.54µm [0.000100] MIN THICKNESS
8. CHROMATE PER QQ-P-416
9. TIN-LEAD PLATE PER MIL-P-81728A
10. RECOMMENDED PANEL MOUNTING
11. CAPACITANCE: 9400pF VOLTAGE: 1500Vdc
12. ESD DEVICE VOLTAGE BREAKDOWN < 2.5kVdc
13. USE INSTRUCTION SHEET 2769
14. GOLD PLATE PER MIL-G-45204, 0.38µm [0.000015] MIN THICKNESS
15. GOLD PLATE PER MIL-G-45204, 0.08µm [0.000003] MIN THICKNESS

- DIELECTRIC
- CONTACT
- SHELL

OBSELETE	15	415657-3
	14	415657-2
SUPSD BY 415657-2	13	415657-1
CONTACT FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE	REVISIONS	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm (INCHES)		DATE	REVISIONS	JACK, RIGHT ANGLE, 50 OHM, DECOUPLED, PCB, BNC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		DATE	REVISIONS	SIZE CASE CODE DRAWING NO	
0 PLC ±		DATE	REVISIONS	A2 00779 C-415657	
1 PLC ±		DATE	REVISIONS	SCALE 5:1 SHEET 1 OF 1 REV 0	
2 PLC ±0.20 (1.008)		DATE	REVISIONS		
3 PLC ±		DATE	REVISIONS		
4 PLC ±		DATE	REVISIONS		
ANGLES ±		DATE	REVISIONS		
MATERIAL SEE NOTES		DATE	REVISIONS		
FINISH SEE NOTES		DATE	REVISIONS		
WEIGHT		DATE	REVISIONS		
CUSTOMER DRAWING		DATE	REVISIONS		