





PRODUCT NUMBER

77315-YXX-XXLF

- RoHS COMPATIBLE
SEE NOTE 7
- TOTAL NB OF POSITIONS 01 TO 36
- PACKAGING, NOTE 3
- PIN STYLE SEE SHEET 2
- PLATING SEE SHEET 2

NOTES:

- HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK
- PIN MATERIAL : PHOSPHOR BRONZE
- PACKAGING:
 - PACKAGING POLYBAG
 - "V" BLIBOX PACK FOR CUSTOMER DEDICATED PART
 - "K" TAPE & REEL PACKAGING WITHOUT PICK UP CAP
- 9N MIN RETENTION IN EITHER DIRECTION
- TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- UNDERPLATING : 1.27µm Ni MIN
- RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
 - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - REFLOW COMPATIBLE
 - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family BERGSTIK
ltr	ecr no	dr	date	tolerances unless otherwise specified		mm	title
AT	F-23187	AMA	16.02.01	angles	.X ±0.3	mm	UNSHR.HEADER
AU	F-23373	AMA	16.02.26	linear	.XX ±0.15	mm	RA SR TMT
AV	F-23462	LMU	16.03.07		.XXX ±0.05	scale 5:1	
AW	F-23551	LMU	16.03.21	dr	D.LE	01.01.24	dwg no
AX	F-24328	AMA	16.06.17	enrg	JM.C	01.01.24	sheet 1 of 2
AY	F-25336	DDE	16.11.15	chr	JM.C	01.01.24	size
BA	F-25361	DDE	16.11.16	appd	JF.N	01.01.24	A3
sheet	revision	BA	AU				type
index	sheet	1	2				CUSTOMER Drawing



FCIconnect.com

Copyright FCI

PRODUCT SPECIFICATIONS

PIN	STYLE	MATING	SOLDER	DIM "C"
01		5.72	2.57	1.5
02		5.72	5.11	1.5
03		5.72	7.65	1.5
07		5.72	5.11	3.9
13		5.72	3.45	1.5
18		5.84	3.05	1.5
22		11.71	3.2	1.5
24		6.75	2.85	1.5
25		8.07	3.05	1.5
26		8.2	12.6	1.5
27		5	3.9	1.5
28		3.1	3.1	1.5
29		9.7	2.90	1.5
30		8.30	4.40	1.5
31		11.70	2.80	1.5
32		8.90	3.05	1.5
33		10.20	3.05	1.5
34		10.00	3.25	1.5
35		5.72	12.73	1.5
36		N/A		
37		N/A		
38		8.51	5.51	1.5
39		9.80	9.30	1.5
40		8.13	2.54	3.90
41		14.20	3.05	1.5
42		9.00	7.20	1.5
43		8.08	2.79	1.5
44		15.70	2.79	1.5
45		8.20	2.35	1.5
46		3.10	9.90	1.5
47		2.30	2.30	1.5
48		3.50	3.05	1.5

PLATING

1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

4 = 3µm-5µm TIN FULL PLATED REFLOW

5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL

G = 0.76µm FULL GXT

S = 0.38µm FULL GXT

- 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

mat'l. code				surface		tolerance		projection	product family		
SEE NOTES				ISO 1302	ISO 406	ISO 1101	ISO 1101		BERGSTIK		
ltr	ecn no	dr	date	tolerances unless otherwise specified				mm	title		
AP	F-23462	LMU	16.03.07	angles	linear	.X ±0.3			UNSHR.HEADER		
AR	F-23551	LMU	16.03.21			.XX ±0.15			RA SR TMT		
AS	F-24328	AMA	16.06.17			.XXX ±0.05		scale 5:1			
AT	F-25336	DDE	16.11.15	dr	D.LE	01.01.24		FCI	dwg no	sheet 2 of 2	size
AU	F-25361	DDE	16.11.16	enr	JM.C	01.01.24			77315		A3
AN	F-23373	AMA	16.02.26	appd	JF.N	01.01.24			type CUSTOMER		Drawing
sheet index	revision sheet										