

## MM74HC273

### Octal D-Type Flip-Flops with Clear

#### General Description

The MM74HC273 edge triggered flip-flops utilize advanced silicon-gate CMOS technology to implement D-type flip-flops. They possess high noise immunity, low power, and speeds comparable to low power Schottky TTL circuits. This device contains 8 master-slave flip-flops with a common clock and common clear. Data on the D input having the specified setup and hold times is transferred to the Q output on the LOW-to-HIGH transition of the CLOCK input. The CLEAR input when LOW, sets all outputs to a low state.

Each output can drive 10 low power Schottky TTL equivalent loads. The MM74HC273 is functionally as well as pin compatible to the 74LS273. All inputs are protected from damage due to static discharge by diodes to  $V_{CC}$  and ground.

#### Features


- Typical propagation delay: 18 ns
- Wide operating voltage range
- Low input current: 1  $\mu$ A maximum
- Low quiescent current: 80  $\mu$ A (74 Series)
- Output drive: 10 LS-TTL loads

#### Ordering Code:

| Order Number | Package Number | Package Description                                                         |
|--------------|----------------|-----------------------------------------------------------------------------|
| MM74HC273WM  | M20B           | 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide  |
| MM74HC273SJ  | M20D           | 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide               |
| MM74HC273MTC | MTC20          | 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide |
| MM74HC273N   | N20A           | 20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide      |

Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

#### Connection Diagram



MM74HC273 Octal D-Type Flip-Flops with Clear

**Truth Table**

(Each Flip-Flop)


| Inputs |       |   | Outputs        |
|--------|-------|---|----------------|
| Clear  | Clock | D | Q              |
| L      | X     | X | L              |
| H      | ↑     | H | H              |
| H      | ↑     | L | L              |
| H      | L     | X | Q <sub>0</sub> |

H = HIGH Level (Steady State)

L = LOW Level (Steady State)

X = Don't Care

↑ = Transition from LOW-to-HIGH level

Q<sub>0</sub> = The level of Q before the indicated steady state input conditions were established**Logic Diagram**

**Absolute Maximum Ratings**(Note 1)

(Note 2)

|                                                  |                         |
|--------------------------------------------------|-------------------------|
| Supply Voltage ( $V_{CC}$ )                      | -0.5 to +7.0V           |
| DC Input Voltage ( $V_{IN}$ )                    | -1.5 to $V_{CC} + 1.5V$ |
| DC Output Voltage ( $V_{OUT}$ )                  | -0.5 to $V_{CC} + 0.5V$ |
| Clamp Diode Current ( $I_{IK}, I_{OK}$ )         | $\pm 20$ mA             |
| DC Output Current, per pin ( $I_{OUT}$ )         | $\pm 25$ mA             |
| DC $V_{CC}$ or GND Current, per pin ( $I_{CC}$ ) | $\pm 50$ mA             |
| Storage Temperature Range ( $T_{STG}$ )          | -65°C to +150°C         |
| Power Dissipation ( $P_D$ )                      |                         |
| (Note 3)                                         | 600 mW                  |
| S.O. Package only                                | 500 mW                  |
| Lead Temperature ( $T_L$ )                       |                         |
| (Soldering 10 seconds)                           | 260°C                   |

**Recommended Operating Conditions**

|                                                            | Min | Max      | Units |
|------------------------------------------------------------|-----|----------|-------|
| Supply Voltage ( $V_{CC}$ )                                | 2   | 6        | V     |
| DC Input or Output Voltage<br>( $V_{IN}, V_{OUT}$ )        | 0   | $V_{CC}$ | V     |
| Operating Temperature Range ( $T_A$ )                      | -40 | +85      | °C    |
| Input Rise or Fall Times<br>( $t_r, t_f$ ) $V_{CC} = 2.0V$ |     | 1000     | ns    |
| $V_{CC} = 4.5V$                                            |     | 500      | ns    |
| $V_{CC} = 6.0V$                                            |     | 400      | ns    |

**Note 1:** Absolute Maximum Ratings are those values beyond which damage to the device may occur.**Note 2:** Unless otherwise specified all voltages are referenced to ground.**Note 3:** Power Dissipation temperature derating — plastic "N" package: - 12 mW/°C from 65°C to 85°C.**DC Electrical Characteristics** (Note 4)

| Symbol          | Parameter                         | Conditions                                                                                                           | V <sub>CC</sub> | T <sub>A</sub> = 25°C |                   | T <sub>A</sub> = -40 to 85°C | T <sub>A</sub> = -55 to 125°C | Units |
|-----------------|-----------------------------------|----------------------------------------------------------------------------------------------------------------------|-----------------|-----------------------|-------------------|------------------------------|-------------------------------|-------|
|                 |                                   |                                                                                                                      |                 | Typ                   | Guaranteed Limits |                              |                               |       |
| V <sub>IH</sub> | Minimum HIGH Level Input Voltage  |                                                                                                                      | 2.0V            |                       | 1.5               | 1.5                          | 1.5                           | V     |
|                 |                                   |                                                                                                                      | 4.5V            |                       | 3.15              | 3.15                         | 3.15                          | V     |
|                 |                                   |                                                                                                                      | 6.0V            |                       | 4.2               | 4.2                          | 4.2                           | V     |
| V <sub>IL</sub> | Maximum LOW Level Input Voltage   |                                                                                                                      | 2.0V            |                       | 0.5               | 0.5                          | 0.5                           | V     |
|                 |                                   |                                                                                                                      | 4.5V            |                       | 1.35              | 1.35                         | 1.35                          | V     |
|                 |                                   |                                                                                                                      | 6.0V            |                       | 1.8               | 1.8                          | 1.8                           | V     |
| V <sub>OH</sub> | Minimum HIGH Level Output Voltage | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 20 μA                                  | 2.0V            | 2.0                   | 1.9               | 1.9                          | 1.9                           | V     |
|                 |                                   |                                                                                                                      | 4.5V            | 4.5                   | 4.4               | 4.4                          | 4.4                           | V     |
|                 |                                   |                                                                                                                      | 6.0V            | 6.0                   | 5.9               | 5.9                          | 5.9                           | V     |
|                 |                                   | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 4.0 mA<br> I <sub>OUT</sub>   ≤ 5.2 mA | 4.5V            | 4.2                   | 3.98              | 3.84                         | 3.7                           | V     |
|                 |                                   |                                                                                                                      | 6.0V            | 5.7                   | 5.48              | 5.34                         | 5.2                           | V     |
|                 |                                   |                                                                                                                      |                 |                       |                   |                              |                               |       |
| V <sub>OL</sub> | Maximum LOW Level Output Voltage  | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 20 μA                                  | 2.0V            | 0                     | 0.1               | 0.1                          | 0.1                           | V     |
|                 |                                   |                                                                                                                      | 4.5V            | 0                     | 0.1               | 0.1                          | 0.1                           | V     |
|                 |                                   |                                                                                                                      | 6.0V            | 0                     | 0.1               | 0.1                          | 0.1                           | V     |
|                 |                                   | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 4 mA<br> I <sub>OUT</sub>   ≤ 5.2 mA   | 4.5V            | 0.2                   | 0.26              | 0.33                         | 0.4                           | V     |
|                 |                                   |                                                                                                                      | 6.0V            | 0.2                   | 0.26              | 0.33                         | 0.4                           | V     |
|                 |                                   |                                                                                                                      |                 |                       |                   |                              |                               |       |
| I <sub>IN</sub> | Maximum Input Current             | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                             | 6.0V            |                       | ±0.1              | ±1.0                         | ±1.0                          | μA    |
| I <sub>CC</sub> | Maximum Quiescent Supply Current  | V <sub>IN</sub> = V <sub>CC</sub> or GND<br>I <sub>OUT</sub> = 0 μA                                                  | 6.0V            |                       | 8                 | 80                           | 160                           | μA    |

**Note 4:** For a power supply of  $5V \pm 10\%$  the worst case output voltages ( $V_{OH}$ , and  $V_{OL}$ ) occur for HC at 4.5V. Thus the 4.5V values should be used when designing with this supply. Worst case  $V_{IH}$  and  $V_{IL}$  occur at  $V_{CC} = 5.5V$  and 4.5V respectively. (The  $V_{IH}$  value at 5.5V is 3.85V.) The worst case leakage current ( $I_{IN}$ ,  $I_{CC}$ , and  $I_{OZ}$ ) occur for CMOS at the higher voltage and so the 6.0V values should be used.

## AC Electrical Characteristics

$V_{CC} = 5V$ ,  $T_A = 25^\circ C$ ,  $C_L = 15\text{ pF}$ ,  $t_r = t_f = 6\text{ ns}$


| Symbol                | Parameter                                  | Conditions | Typ | Guaranteed Limit | Units |
|-----------------------|--------------------------------------------|------------|-----|------------------|-------|
| $f_{MAX}$             | Maximum Operating Frequency                |            | 50  | 30               | MHz   |
| $t_{PHL}$ , $t_{PLH}$ | Maximum Propagation Delay, Clock to Output |            | 18  | 27               | ns    |
| $t_{PHL}$             | Maximum Propagation Delay, Clear to Output |            | 18  | 27               | ns    |
| $t_{REM}$             | Minimum Removal Time, Clear to Clock       |            | 10  | 20               | ns    |
| $t_s$                 | Minimum Setup Time Data to Clock           |            | 10  | 20               | ns    |
| $t_H$                 | Minimum Hold Time Clock to Data            |            | -2  | 0                | ns    |
| $t_W$                 | Minimum Pulse Width Clock or Clear         |            | 10  | 16               | ns    |

## AC Electrical Characteristics

$C_L = 50\text{ pF}$ ,  $t_r = t_f = 6\text{ ns}$  (unless otherwise specified)

| Symbol                              | Parameter                                  | Conditions      | V <sub>CC</sub> | T <sub>A</sub> = 25°C |                   | T <sub>A</sub> = -40 to 85°C | T <sub>A</sub> = -55 to 125°C | Units |
|-------------------------------------|--------------------------------------------|-----------------|-----------------|-----------------------|-------------------|------------------------------|-------------------------------|-------|
|                                     |                                            |                 |                 | Typ                   | Guaranteed Limits |                              |                               |       |
| f <sub>MAX</sub>                    | Maximum Operating Frequency                |                 | 2.0V            | 16                    | 5                 | 4                            | 3                             | MHz   |
|                                     |                                            |                 | 4.5V            | 74                    | 27                | 21                           | 18                            | MHz   |
|                                     |                                            |                 | 6.0V            | 78                    | 31                | 24                           | 20                            | MHz   |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Maximum Propagation Delay, Clock to Output |                 | 2.0V            | 38                    | 135               | 170                          | 205                           | ns    |
|                                     |                                            |                 | 4.5V            | 14                    | 27                | 34                           | 41                            | ns    |
|                                     |                                            |                 | 6.0V            | 12                    | 23                | 29                           | 35                            | ns    |
| t <sub>PHL</sub>                    | Maximum Propagation Delay, Clear to Output |                 | 2.0V            | 42                    | 135               | 170                          | 205                           | ns    |
|                                     |                                            |                 | 4.5V            | 19                    | 27                | 34                           | 41                            | ns    |
|                                     |                                            |                 | 6.0V            | 18                    | 23                | 29                           | 35                            | ns    |
| t <sub>REM</sub>                    | Minimum Removal Time Clear to Clock        |                 | 2.0V            | 0                     | 25                | 32                           | 37                            | ns    |
|                                     |                                            |                 | 4.5V            | 0                     | 5                 | 6                            | 7                             | ns    |
|                                     |                                            |                 | 6.0V            | 0                     | 4                 | 5                            | 6                             | ns    |
| t <sub>S</sub>                      | Minimum Setup Time Data to Clock           |                 | 2.0V            | 26                    | 100               | 125                          | 150                           | ns    |
|                                     |                                            |                 | 4.5V            | 7                     | 20                | 25                           | 30                            | ns    |
|                                     |                                            |                 | 6.0V            | 5                     | 17                | 21                           | 25                            | ns    |
| t <sub>H</sub>                      | Minimum Hold Time Clock to Data            |                 | 2.0V            | -15                   | 0                 | 0                            | 0                             | ns    |
|                                     |                                            |                 | 4.5V            | -6                    | 0                 | 0                            | 0                             | ns    |
|                                     |                                            |                 | 6.0V            | -4                    | 0                 | 0                            | 0                             | ns    |
| t <sub>W</sub>                      | Minimum Pulse Width Clock or Clear         |                 | 2.0V            | 34                    | 80                | 100                          | 120                           | ns    |
|                                     |                                            |                 | 4.5V            | 11                    | 16                | 20                           | 24                            | ns    |
|                                     |                                            |                 | 6.0V            | 10                    | 14                | 18                           | 20                            | ns    |
| t <sub>r</sub> , t <sub>f</sub>     | Maximum Input Rise and Fall Time, Clock    |                 | 2.0V            |                       | 1000              | 1000                         | 1000                          | ns    |
|                                     |                                            |                 | 4.5V            |                       | 500               | 500                          | 500                           | ns    |
|                                     |                                            |                 | 6.0V            |                       | 400               | 400                          | 400                           | ns    |
| t <sub>THL</sub> , t <sub>TLH</sub> | Maximum Output Rise and Fall Time          |                 | 2.0V            | 28                    | 75                | 95                           | 110                           | ns    |
|                                     |                                            |                 | 4.5V            | 11                    | 15                | 19                           | 22                            | ns    |
|                                     |                                            |                 | 6.0V            | 9                     | 13                | 16                           | 19                            | ns    |
| C <sub>PD</sub>                     | Power Dissipation Capacitance (Note 5)     | (per flip-flop) |                 | 45                    |                   |                              |                               | pF    |
| C <sub>IN</sub>                     | Maximum Input Capacitance                  |                 |                 | 7                     | 10                | 10                           | 10                            | pF    |

**Note 5:**  $C_{PD}$  determines the no load dynamic power consumption,  $P_D = C_{PD} V_{CC}^2 f + I_{CC} V_{CC}$ , and the no load dynamic current consumption,  $I_S = C_{PD} V_{CC} f + I_{CC}$ .




**20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide  
Package Number M20B**



LAND PATTERN RECOMMENDATION




DIMENSIONS ARE IN MILLIMETERS



NOTES:



- A. CONFORMS TO EIAJ EDR-7320 REGISTRATION,  
ESTABLISHED IN DECEMBER, 1998.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD  
FLASH, AND TIE BAR EXTRUSIONS.

M20DRevB1





DETAIL A

**20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide  
Package Number M20D**



DIMENSIONS ARE IN MILLIMETERS




DETAIL A

NOTES:

- A. CONFORMS TO JEDEC REGISTRATION MO-153, VARIATION AC,  
REF NOTE 6, DATE 7/93.
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLDS FLASH,  
AND TIE BAR EXTRUSIONS.
- D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.

MTC20REVD1

**20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide  
Package Number MTC20**

**Physical Dimensions** inches (millimeters) unless otherwise noted (Continued)

N20A (REV G)

**20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide  
Package Number N20A**

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

**LIFE SUPPORT POLICY**

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

[www.fairchildsemi.com](http://www.fairchildsemi.com)