

Tyco / Electronics
Raychem Circuit Protection
 308 Constitution Drive
 Menlo Park, CA 94025-1164
 Phone: 800-227-4856
 Fax: 800-227-4866

PolySwitch®
PTC Devices
 Overcurrent Protection Device

PRODUCT: RXEF040

DOCUMENT: SCD 25218
 PCN: 759132
 REV LETTER: C
 REV DATE: APRIL 7, 2005
 PAGE NO.: 1 OF 1

Specification Status: Released

Electrical Rating

Voltage: 72V MAX

Current: 40A MAX

Insulating Material:

Cured, Flame Retardant Epoxy

Polymer

meets UL94 V-0 Requirements

Lead Material:

24 AWG Tin Plated Copper Clad Steel

Marking:

Raychem Logo
 and Voltage

XX 72

XF040 — Part Identification

Lot Identification
 (can be on back)




TABLE I. DIMENSIONS:

	A		B		C		D		E	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:	--	7.6	--	13.5	4.3	5.8	7.6	--	--	3.0
in*:	--	(0.30)	--	(0.53)	(0.17)	(0.23)	(0.30)	--	--	(0.12)

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS :

I HOLD RATED CURRENT	CURRENT RATINGS		INITIAL RESISTANCE VALUES		TIME TO TRIP	ONE HOUR POST-TRIP RESISTANCE STANDARD TRIP	TRIPPED- STATE POWER DISSIPATION
AMPERES AT 20°C	AMPERES AT 20°C		OHMS AT 20°C		SECONDS AT 20°C, 2.0A	OHMS AT 20°C	WATTS AT 20°C
HOLD	HOLD	TRIP	MIN	MAX	MAX	MAX	NOMINAL
0.40	0.40	0.80	0.55	0.86	3.8	1.29	0.56

Agency Recognitions:

UL, CSA, TUV

Approved by UL as a current limiting impedance, per the 1996 NEC, Tables 11 (c) and 11 (b).

Reference Documents:

PS300

Precedence:

This specification takes precedence over documents referenced herein.

Effectivity:

Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION:

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information

ROHS Compliant

ELV Compliant

Pb-Free

Directive 2002/95/EC
 Compliant

Directive 2000/53/EC
 Compliant

