




D4E146 Series Centrifugal Blower

Ø 146mm

- AC dual inlet, forward curved centrifugal blower. Via a bracket, the integrated external-rotor motor is mounted on one side of the housing.
- Direction of rotation is CCW as seen from inlet opposite the cable exit. Insulation class "B".
- Housing and impeller made of galvanised sheet-steel. Forward curved impellers are directly press-fitted onto the rotor of the external-rotor motor.
- Maintenance-free ball bearings.
- UL, CSA, VDE approvals on some models, please contact application engineering.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Capacitor (µF)	Wgt. (lbs)
D4E146-AA25-34	1	450	115	60	128	55	60	Ball	Leads	8	7.69
D4E146-AA07-22	1	450	230	50/60	116	53	60	Ball	Leads	2	7.69



DIMENSIONS - Inches (mm)

PART NUMBER	A	B	C	D	E	F	G	H	I	J
D2E146-AA	8.11 (206)	8.62 (219)	3.82 (97)	3.86 (98)	10.63 (270)	10.0 (254)	5.59 (142)	4.96 (126)	9.13 (232)	4.02 (102)

