




$\phi 0.71 \pm 0.07$
 $\phi 0.30 \times M$



VIEW P

$\phi 0.71 \pm 0.07$
 $\phi 0.30 \times M$



VIEW Q

LEGEND

87758- * * * *

CKT SIZE (SEE SHT 2 TABLE) PLATING (SEE NOTE 2)

NOTES:

1. MATERIAL:

HOUSING: 30% G.F. NYLON 46, 94V-0, COLOR: BLACK
 PIN: 0.50mm SQ. PHOSPHOR BRONZE 510

2. PLATING:

**16 - 0.38um MIN GOLD IN CONTACT AREA.
 TIN IN SOLDER AREA, BOTH OVER
 NICKEL OVERALL.
 **17 - 0.76um MIN GOLD IN CONTACT AREA,
 TIN IN SOLDER AREA, BOTH OVER
 NICKEL OVERALL.
 **18 - 2.54um MIN TIN OVER
 NICKEL OVERALL.

3. 12 CKT USED FOR ILLUSTRATION ONLY

4. PACKED IN POCKET TRAY

5. PIN PUSHOUT FORCE: 1KG MIN IN EITHER DIRECTION

6. CKT 4 AND 6 IS CUT FROM CKT 8 AND 12 RESPECTIVELY.
 CKT 2 ARE CUT FROM ANY LARGER CKT SIZE.ROUGH EDGES
 ARE EXPECTED ALONG THE CUTTING EDGES.

7. PRODUCT SPEC PS-87761-100 APPLIES.

8. RECOMMENDED PCB THICKNESS IS 1.60±0.10

EC NO: S2005-0715 DRAWN:KCHO CHKD:PTLM APPR:SCLOW A2	2005/05/16 2005/05/18 2005/05/19	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
			 =0  =0			DRAWN BY KSEE	DATE 2003/10/30	TITLE SALES DRAWING 2MM DUAL ROW SINGLE WAFER, VERTICAL T/H HDR			
				4 PLACES	$\pm$ ---	$\pm$ ---	CHECKED BY KCLING		DATE 2004/01/05		
				3 PLACES	$\pm$ ---	$\pm$ ---					
				2 PLACES	$\pm$ 0.20	$\pm$ ---					
				1 PLACE	$\pm$ ---	$\pm$ ---	APPROVED BY SKTOH		DATE 2004/01/05		
						ANGULAR $\pm$ 3 °		MATERIAL NO.	DOCUMENT NO.	SHEET NO.	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3	SEE TABLE	SD-87758-107	1 OF 2	
										THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

