







KEY SHOWN IN POSITION "E"



(STAGGERED VIEW SHOWN)



NOTCH DESIGNATES ROW A

UPDATE TOL EC NO: UCP2008-1145 DRAWN BY: BPI/SZCZOR CHKD: 2007/11/19 APPR: JLAURX REV: 2007/11/19	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
					mm	INCH	DRAWN BY	DATE	TITLE					
				4 PLACES	± ---	± ---	BPI/SZCZOR	3/28/06	I-TRAC BACKPLANE 7 ROW					
				3 PLACES	± ---	± ---	CHECKED BY	DATE	GUIDE RIGHT ASSEMBLY					
				2 PLACES	± 0.13	± ---	JLAURX	2007/02/06	SALES DRAWING					
				1 PLACE	± 0.25	± ---	APPROVED BY	DATE	MOLEX INCORPORATED					
				ANGULAR		± 1/2°	CBIXLER	2007/02/06	SD-76015-004					
				DRAFT WHERE APPLICABLE		SEE CHART		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
				MUST REMAIN		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX						
				WITHIN DIMENSIONS		INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

13 12 11 10 9 8 7 6 5 4 3 2 1

76015-****

MODULE TYPE -- TAIL PLATING TYPE

GUIDE RIGHT -- TIN/LEAD = 4

GUIDE RIGHT -- TIN ONLY = 5

GUIDE RIGHT W/END -- TIN/LEAD = 8

GUIDE RIGHT W/END -- TIN ONLY = 9

OF COLUMNS

4 = 4 COL

6 = 6 COL

1 = 10 COL

PIN LENGTH (P)

2 = 3.90

3 = 4.70

4 = 5.70

5 = 4.70 & 5.70

STAGGERED

KEY ORIENTATION

0 = NO KEY

1 = A

2 = B

3 = C

4 = D


5 = E

6 = F


7 = G

8 = H

GUIDE LEFT STYLE



GUIDE LEFT W/END STYLE



MATERIAL NUMBER	# OF COLUMNS	DIM 'A'	DIM 'B'
76015-4**	4	21.1	11.10
76015-6**	6	28.5	18.50
76015-1**	10	43.3	33.30

MATERIAL NUMBER	# OF COLUMNS	DIM 'A'	DIM 'B'
76015-4**	4	22.4	11.10
76015-6**	6	29.8	18.50
76015-1**	10	44.6	33.30

NOTES:

1. MATERIALS: HOUSING - LIQUID CRYSTAL POLYMER (LCP)
GLASS-FILLED, UL94V-0
TERMINALS - HIGH PERFORMANCE COPPER ALLOY
2. FINISH: 30uIN MIN. GOLD IN CONTACT AREA.
SELECTIVE TIN/LEAD OR SELECTIVE TIN
ON PCB TAILS. NICKEL OVERALL.
3. REFER TO MOLEX PRODUCT SPECIFICATION PS-75710-999
FOR PERFORMANCE SPECIFICATIONS.
4. FOR MIXED CONTACT MATING LENGTHS, CONSULT MOLEX
FOR AVAILABILITY.
5. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF
COSMETIC SPEC PS-45499-002.
6. PACKAGE PER: PK-70873-125.
7. GUIDED PARTS TO BE SHIPPED WITH 2-56 UNC B SCREW P/N 73774-1000.
8. FOR GROUNDED GUIDE PINS USE DIA 3.56 +/-0.08 (PTH),
DIA 3.66 (DRILL), AND DIA 6.5 (PAD).
9. REFER TO PCB ROUTING GUIDE FOR ANTI-PAD AND ROUTING RECOMMENDATIONS.

INITIAL RELEASE EC NO: UCP2008-1145 DRAWN BY: SZCZOR CHKD: JLAURX APPR: JLAURX REV: B	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
				mm	INCH	DRAWN BY BPI/SZCZOR	DATE 3/28/06	TITLE I-TRAC BACKPLANE 7 ROW GUIDE RIGHT ASSEMBLY SALES DRAWING					
			4 PLACES	± ---	± ---	CHECKED BY JLAURX	DATE 2007/02/06	MOLEX MOLEX INCORPORATED					
			3 PLACES	± ---	± ---								
			2 PLACES	± 0.13	± ---	APPROVED BY CBIXLER		DATE 2007/02/06					
			1 PLACE	± 0.25	± ---								
			ANGULAR		± 1/2°								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART		DOCUMENT NO. SD-76015-004		SHEET NO. 2 OF 4						
			SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

