

Preliminary

TLP719F


DIGITAL LOGIC GROUND ISOLATION
 LINE RECEIVERS
 MICROPROCESSOR SYSTEM INTERFACES
 SWITCHING POWER SUPPLY FEEDBACK CONTROL
 TRANSISTOR INVERTORS

The TOSHIBA TLP719F consists of a GaAlAs high-output light-emitting diode and a high-speed detector.

This unit is a 6-lead SDIP. The TLP719F is 50% smaller than the 8-pin DIP and meets the reinforced insulation class requirements of international safety standards. Therefore the mounting area can be reduced in equipment requiring safety standard certification.

The TLP719F has a Faraday shield integrated on the photodetector chip to provide an effective common mode noise transient immunity. Therefore this product is suitable for application in noisy environmental conditions.

Maximum ratings and electrical characteristics are the same as The TLP719 technical data sheets.



Weight: 0.26 g (typ.)

- Open collector
- Package type : SDIP6
- Isolation voltage : 5000 Vrms (min)
- Common mode transient immunity : $\pm 10 \text{ kV/us}$ (min) @ $V_{CM} = 400 \text{ V}$
- Switching speed : $t_{pH}/t_{pLH} = 0.8 \mu\text{s}$ (max)
 $\text{@ } I_F = 16 \text{ mA, } V_{CC}$
 $R_L = 1.9 \text{ k}\Omega, \text{Ta} = 25^\circ\text{C}$
- TTL compatible
- Construction mechanical rating

Creepage Distance	8.0 mm (min)
Clearance	8.0 mm (min)
Insulation Thickness	0.4 mm (min)

- UL recognized : UL1577, File No. E67349
- Option (D4) TÜV approved : EN60747-5-2


Certificate No. R50033433

Maximum operating insulation voltage : 1140 Vpk

Highest permissible over voltage : 8000 Vpk


(Note) When a EN60747-5-2 approved type is needed,
 please designate the "Option(D4)"

SCHEMATIC



A 0.1- μF bypass capacitor must be connected between pins 4 and 6.
 (See Note 7.)

PIN CONFIGURATION (Top View)



RESTRICTIONS ON PRODUCT USE

030619EBC

- The information contained herein is subject to change without notice.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA for any infringements of patents or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of TOSHIBA or others.
- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- TOSHIBA products should not be embedded to the downstream products which are prohibited to be produced and sold, under any law and regulations.
- GaAs(Gallium Arsenide) is used in this product. The dust or vapor is harmful to the human body. Do not break, cut, crush or dissolve chemically.