




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AJ	00		B	REVISED PER ECO 06-024121	1/29/2007	DW JL

D

C

B


A



PCB CONFIGURATION

- 1 ZINC PER ASTM B 86.
- 2 BERYLLIUM COPPER PER ASTM B 196.
- 3 PTFE PER ASTM B 1710.
- 4 NICKEL PLATE PER QQ-N-290, 3.81 μ m [.000150] MINIMUM THICK.
- 5 TIN PLATE PER ASTM B 545, 3.04 μ m [.000120] MINIMUM THICK, OVER NICKEL PLATE PER MIL-C-26074, 7.62 μ m [.000300] MINIMUM THICK.
- 6 GOLD PLATE PER ASTM B 488, 1.27 μ m [.000050] MINIMUM THICK.
- 7. INTERFACE PER MIL-C-39012.
- 8 GOLD PLATE PER ASTM B 488, 0.76 μ m [.000030] MINIMUM THICK.
- 9 POLYMETHYLPENTENE: GENERAL PURPOSE.

	4.34 [.171]			5413558-5
	3.33 [.131]			5413558-3
	4.34 [.171]			5413558-2
	4.34 [.171]			5413558-1
FRONT DIELECTRIC MATERIAL	A	CONTACT FINISH	SHELL FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - 22APR2005 DOCK5	 Tyco Electronics Corporation Harrisburg, PA 17105-3608				
		CHK J. HAVENER 22APR2005					
DIMENSIONS: mm [INCHES]		APVD J. LIPPERT 22APR2005	NAME JACK, RIGHT ANGLE, PCB, 75 OHM, SERIES BNC				
		PRODUCT SPEC 108-12078					
		APPLICATION SPEC —					
MATERIAL SEE NOTES 1-3		WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=5413558	RESTRICTED TO —	
FINISH SEE NOTES 4-6, 8-9		CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1	REV B