



This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



- NOTES:
1. SUPPLIED WITH SILVER PLATED HEX NUT.
 2. MOUNTING TORQUE NOT TO EXCEED 2.5 lb-in. [.282 Nm].
 3. TUSONIX STANDARD PART NUMBER: 2425-044-X5W0-502Z. TUSONIX RoHS COMPLIANT PART NUMBER: 2425-044-X5W0-502Z LF. CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
 4. PART MARKING: STANDARD PART: BLACK INK FOR TRADEMARK AND CAP. CODE. RoHS PART: GREEN INK FOR TRADEMARK AND CAP. CODE.

SPECIFICATIONS	
TUSONIX STYLE:	2425-044
CAP. VALUE:	5,000 pF
CAP. TOLERANCE:	+ 80 - 20 %
TEMP. CHARACTERISTIC:	X5W
RATING:	200 VDC @ + 85°C/100 VDC @ +125°C
OPERATING RANGE:	-55°C TO +125°C
IR MIN. @ 100 VDC:	10 G Ω
DWV VDC:	600

REVISION RECORD Original Release C.O. ECO-878	A	--TOLERANCES-- Unless Otherwise Specified		Title MINIATURE BUSHING FEED-THRU	
		DECIMAL ± .031 [0.79]		Drawn L.E. 07-30-09	Scale 4 X
		ANGLES ±		Approved R.L. 07-30-09	
		TUSONIX TUCSON, ARIZONA		A 2425-044-X5W0-502Z	