




ZH-100-1/8-0-SP Product Details

[Share](#) [Print](#) [Email](#)


ZH-100-1/8-0-SP

Heat Shrink Tubing

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Heat Shrinkable Tubing
- Product Name = ZH-100
- Product Source = U.K., U.S.
- Flexible
- Thin Wall Style

[View all Features](#)

TE Internal Number: 5220234001


[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Heat Shrinkable Tubing
- Material = Crosslinked Polyolefin
- Color = Black

Electrical Characteristics:

- Product Source = U.K., U.S.
- [Expanded ID, Min. \(mm \[in\]\)](#) = 3.20 [0.126]
- [Recovered ID, Max. \(mm \[in\]\)](#) = 1.60 [0.063]
- Product Use = Cables, Electronic Components, Harnesses

Body Features:

- [Product Name](#) = ZH-100
- Pliancy = Flexible
- [Wall Style](#) = Thin
- [Wall Type](#) = Single
- [Shrink Ratio](#) = 2:1
- Fluid Type = Brake Fluid, Hydraulic Fluid, Unleaded Gasoline, Water
- Resistant To = Fluids, Mechanical Damage
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 0.51 [0.020]

Housing Features:

- Material Systems = No
- Flammability Rating Type = Flame-Retardant

Industry Standards:

- Government/Industry Qualification = No
- UL Rating = None
- CSA Certified = No
- Approved Standards = BR 1326A, BS 4G 198 Part 3 Type 15, DEF Std 59-97 Issue 3 Type 8
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Fluid Resistance = Splash Protection
- [Operating Temperature \(°C\)](#) = -30 - +105

Conditions for Usage:

- Full Recovery Temperature (°C) = 120
- Shrink Temperature, Min. (°C) = 80
- High Temperature Compatible = No

Operation/Application:

- Application = Insulation and Protection, Low Smoke Emissions, Wire Protection Sleeve
- Emission Free = Yes
- Emission Free Type = Halogen-free

Packaging Features:

- Packaging Method = Spool

Other:

- Brand = Raychem

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

