

Item # LC1D115G7, TeSys D IEC Contactor - 115A - Vac Coil

TeSys D IEC Contactor - 115A - Vac Coil



TeSys D IEC Contactor - 115A - 120Vac Coil

SPECIFICATIONS

|                         |                             |
|-------------------------|-----------------------------|
| Termination Method      | Screw Clamp                 |
| Contact Rating          | 600V / 115A                 |
| Coil Voltage            | 120Vac 50/60 Hz             |
| 50/60 Hz Voltage Code   | G7                          |
| Coil Consumption Inrush | 280 - 350 VA                |
| Coil Consumption Sealed | 2 - 18 VA                   |
| Power Wire Size         | #8 AWG - 250MCM             |
| Power Terminal Torque   | 100 lb-in (12 Nm)           |
| Control Wire Size       | #14 - #18 AWG               |
| Control Terminal Torque | 10 lb-in (1.2 Nm)           |
| Mounting Hardware       | 2 x 35mm DIN Rail, M6 screw |
| Weight                  | 2.5 lb (1.13 kg)            |
| AC1 Resistive Rating    | 175 Amp                     |
| AC3 Inductive Rating    | 115 Amp                     |

|                                  |                 |
|----------------------------------|-----------------|
| AC3 Single Phase 115V            | N/A             |
| AC3 Single Phase 230V            | N/A             |
| AC3 Three Phase 200V             | 30 HP           |
| AC3 Three Phase 230V             | 40 HP           |
| AC3 Three Phase 460V             | 75 HP           |
| AC3 Three Phase 575V             | 100 HP          |
| Control Contact Rating (1NC/0NO) | A600            |
| UL File/CCN                      | E164862 / NLDX  |
| CSA File                         | LR43364 3211 04 |
| Meets Standard                   | IEC 60647-4     |
| CE                               | Yes             |
| RoHS                             | Yes             |