

| LOC | DIST | REVISIONS |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
| AD  | 00   | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
|     |      |           | A1  | REVISED PER ECO-11-004587 | 21MAR11 | RK  | HMR  |

8058 & 8060 Series *Transistor Sockets*



8060-1G11



8060-1G6

FEATURES:

The 8058/8060 family of teflon sockets, with beryllium copper contacts, offers many features which allow them to be utilized in the most severe applications. Low profile for close board spacing, closed sleeve for 100% prevention of solder and flux wicking. A choice of many terminal styles for greater packaging selection and ease of use. Many of these sockets meet or exceed MIL-S-83502/2 and MIL-S-83502/5.

- Two-piece socket terminal - four fingered inner contact and machined outer sleeve
- Low profile for tight space applications
- Sockets accept 0,41/.016 to 0,51/.020 diameter leads
- Printed circuit, solder pocket and turret style terminations available
- Closed entry-design no distortion or damage to contact with misaligned or oversized leads

MATERIAL SPECIFICATIONS:

Insulator ..... Teflon  
Sleeve ..... Brass  
Contact Plating ..... Beryllium copper  
Plating ..... Contact gold, sleeve gold

PERFORMANCE SPECIFICATIONS:

MECHANICAL

Vibration ..... Passed MIL-STD -1344, Method 2005, 15 G's, 10 to 2,000 cycles  
Mechanical Shock ..... Passed MIL-STD -1344, Method 2004, 10 G's, 1 to 9,000 cycles  
Durability ..... 50 Insertions and withdrawals, MIL-S-83502/ 1, Sec. 4.7.12  
Insertion Force ..... 4.0 lb. max., .020 dia. +.0000 probe -.0002  
Withdrawal Force ..... 14 Grams (1/2 oz.) min. .016 dia. +.0002 probe -.0001  
Solderability ..... MIL-STD- 202, Method 208

ELECTRICAL

Bulk Contact  
Resistance ..... 20 Milliohms max. per MIL-S-83502/1  
Current Rating ..... 3 Amp DC, contact rating  
Operating Voltage ..... 500 VDC @ atmospheric pressure  
Dielectric Withstanding  
Voltage ..... 600 VAC per MIL-STD -1344 , Method 3001  
Insulation Resistance .... 2 x 10<sup>6</sup> Megohms, MIL-STD -1344, Method 3003  
Capacitance ..... 2 pF Max., MIL-STD -202, Method 305

ENVIRONMENTAL

Operating Temperature .. -55°C to +125°C  
Corrosive Atmosphere .. 30 milliohms, ammonium polysulfide 10 ppm per MIL-S-83502/1 Sec. 4.7.17  
Moisture Resistance ..... 30 Milliohms max., MIL-STD -202, Method 106  
Thermal Shock ..... MIL-STD -1344, Method 1003

**Thomas & Betts**

Quality & Innovation From **AUGAT**® Name Brand Products

H14

Thomas & Betts  
1555 Lynnfield Road  
Memphis, TN 38119  
(901) 682-8221 FAX (901) 537-8805

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT

|                                        |  |                  |           |                               |        |  |
|----------------------------------------|--|------------------|-----------|-------------------------------|--------|--|
| DIMENSIONS:                            |  | DWN              | 28NOV2006 | MATERIAL                      | FINISH |  |
| INCHES                                 |  | R BROWN          |           |                               |        |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | CHK              | 28NOV2006 | <b>STE</b> TE Connectivity    |        |  |
|                                        |  | K DeBOCK         |           |                               |        |  |
|                                        |  | APVD             | 28NOV2006 |                               |        |  |
|                                        |  | K DeBOCK         |           |                               |        |  |
| 0 PLC ± —                              |  | PRODUCT SPEC     |           | NAME                          |        |  |
| 1 PLC ± —                              |  | —                |           | SOCKET, 8 PIN PRINTED CIRCUIT |        |  |
| 2 PLC ± —                              |  | APPLICATION SPEC |           |                               |        |  |
| 3 PLC ± —                              |  | —                |           |                               |        |  |
| 4 PLC ± —                              |  | WEIGHT           |           |                               |        |  |
| ANGLES ± —                             |  | —                |           |                               |        |  |
|                                        |  | CUSTOMER DRAWING |           | RESTRICTED TO                 |        |  |
|                                        |  | A4               |           | 00779                         |        |  |
|                                        |  | C-1437508-5      |           |                               |        |  |
|                                        |  | SCALE            |           | SHEET                         |        |  |
|                                        |  | NTS              |           | 1 OF 4                        |        |  |
|                                        |  |                  |           | REV                           |        |  |
|                                        |  |                  |           | A1                            |        |  |

|     |      |           |     |             |  |  |  |      |
|-----|------|-----------|-----|-------------|--|--|--|------|
| LOC | DIST | REVISIONS |     |             |  |  |  |      |
| AD  | 00   | P         | LTR | DESCRIPTION |  |  |  | DATE |
|     |      |           | —   | SEE SHEET 1 |  |  |  | DWN  |
|     |      |           |     |             |  |  |  | APVD |

Transistor Sockets 8058 & 8060 Series

PART NUMBER / STANDARD CONFIGURATIONS

| Part Number | Figure | No. of Contacts | Pin Circle | A    | B    | C    | D    | E*   | F Max. | Terminal Style      | Mounting Hole | Transistor Lead Length | Polarization Figure |               |
|-------------|--------|-----------------|------------|------|------|------|------|------|--------|---------------------|---------------|------------------------|---------------------|---------------|
| M8058-45G1  | 1      | 3               | .200       | .200 | .265 | .373 | .410 | .160 | .406   | Turret              | B             | .156/.218              | N                   |               |
| M8058-1G29  | 3      | 3               | .200       | .200 | .270 | .373 | .410 | .140 | .351   | Solder Pocket       |               |                        |                     |               |
| 8058-1G29   | 3      | 3               | .200       | .200 | .270 | .373 | .410 | .140 | .351   |                     |               |                        |                     |               |
| 8058-1G23   | 4      | 3               | .200       | .200 | .270 | .373 | .410 | .302 | .544   | 544 Printed Circuit | —             | .125/.155              | P                   |               |
| M8058-1G23  | 4      | 3               | .200       | .200 | .270 | .373 | .410 | .302 | N/A    |                     |               |                        |                     |               |
| 8058-1G59   | 6      | 3               | .200       | .200 | .165 | N/A  | .410 | .125 | N/A    |                     |               |                        |                     |               |
| 8058-38G6   | 6      | 3               | .200       | .200 | .165 | N/A  | .410 | .315 | N/A    | Wirewrap            | B             | .156/.218              | N                   |               |
| 8058-1G62   | 7      | 3               | .200       | .200 | .270 | .373 | .410 | .500 | .703   |                     |               |                        |                     | Turret        |
| M8058-45G2  | 1      | 4               | .200       | .200 | .265 | .373 | .410 | N/A  | .406   |                     |               |                        |                     | Solder Pocket |
| M8058-1G30  | 3      | 4               | .200       | .200 | .265 | .373 | .410 | .140 | .377   |                     |               |                        |                     |               |
| 8058-1G30   | 3      | 4               | .200       | .200 | .270 | .373 | .410 | .140 | .347   | Printed Circuit     | —             | .125/.155              | N                   |               |
| M8058-1G24  | 4      | 4               | .200       | .200 | .270 | .373 | .410 | .347 | .550   |                     |               |                        |                     |               |
| 8058-1G24   | 4      | 4               | .200       | .200 | .270 | .373 | .410 | .317 | .550   | Wirewrap            | B             | .156/.218              | N                   |               |
| 8058-1G63   | 7      | 4               | .200       | .200 | .270 | .373 | .410 | .500 | .703   |                     |               |                        |                     | Turret        |
| 8058-1G58   | 2      | 5               | .200       | .200 | .270 | .373 | .410 | .094 | .331   |                     |               |                        |                     | Solder Pocket |
| 8058-1G61   | 3      | 5               | .200       | .200 | .270 | .373 | .410 | .094 | .300   | Turret              |               |                        |                     |               |
| M8058-1G39  | 2      | 6 at 45°        | .200       | .200 | .270 | .373 | .410 | .140 | .370   | Solder Pocket       | B             | .156/.218              | N                   |               |
| 8058-1G43   | 3      | 6 at 60°        | .200       | .200 | .270 | .373 | .410 | .140 | .370   |                     |               |                        |                     |               |
| M8058-1G18  | 3      | 6 at 45°        | .200       | .200 | .270 | .373 | .410 | .140 | .370   | Printed Circuit     | —             | .125/.155              | P                   |               |
| 8058-1G42   | 4      | 6 at 60°        | .200       | .200 | .270 | .373 | .410 | .317 | .561   |                     |               |                        |                     |               |
| M8058-1G33  | 4      | 6 at 45°        | .200       | .200 | .270 | .373 | .410 | .317 | .561   |                     |               |                        |                     |               |
| 8058-1G48   | 6      | 6 at 60°        | .200       | .200 | .165 | N/A  | .410 | .125 | N/A    | Turret              | B             | .156/.218              | N                   |               |
| 8058-1G52   | 6      | 6 at 45°        | .200       | .200 | .165 | N/A  | .410 | .125 | N/A    |                     |               |                        |                     |               |
| M8058-1G37  | 2      | 8               | .200       | .200 | .270 | .373 | .410 | .094 | .336   |                     |               |                        |                     |               |
| M8058-1G19  | 3      | 8               | .200       | .200 | .270 | .373 | .410 | .140 | .377   | Solder Pocket       | B             | .156/.218              | N                   |               |
| 8058-1G19   | 3      | 8               | .200       | .200 | .270 | .373 | .410 | .140 | .377   |                     |               |                        |                     |               |
| 8058-1G57   | 3      | 8               | .200       | .200 | .270 | .373 | .410 | .140 | .315   |                     |               |                        |                     |               |
| M8058-1G32  | 4      | 8               | .200       | .200 | .270 | .373 | .410 | .317 | .550   | Printed Circuit     | —             | .125/.155              | P                   |               |
| 8058-1G32   | 4      | 8               | .200       | .200 | .270 | .373 | .410 | .317 | .550   |                     |               |                        |                     |               |
| 8058-39G1   | 5      | 8               | .200       | .330 | .375 | .373 | .410 | .187 | .505   |                     |               |                        |                     |               |
| 8058-39G3   | 5      | 8               | .200       | .380 | .375 | .373 | .410 | .150 | .470   | Printed Circuit     | B             | .156/.218              | N                   |               |
| 8058-39G5   | 5      | 8               | .200       | .380 | .375 | .373 | .410 | .150 | .470   |                     |               |                        |                     |               |
| 8058-1G49   | 6      | 8               | .200       | .200 | .165 | N/A  | .410 | .125 | N/A    |                     |               |                        |                     |               |
| 8058-1G47   | 2      | 8               | .230       | .230 | .270 | .373 | .410 | .094 | .300   | Turret              | B             | .125/.155              | P                   |               |
| 8058-1G46   | 3      | 8               | .230       | .230 | .270 | .373 | .410 | .138 | .346   | Solder Pocket       |               |                        |                     |               |
| 8058-1G45   | 4      | 8               | .230       | .230 | .270 | .373 | .410 | .302 | .534   |                     |               |                        |                     |               |
| 8058-39G4   | 5      | 8               | .230       | .380 | .375 | .373 | .410 | .155 | .467   | Printed Circuit     | —             | .156/.218              | PN                  |               |
| 8058-39G6   | 5      | 8               | .230       | .380 | .375 | .373 | .410 | .150 | .467   |                     |               |                        |                     |               |
| 8058-1G50   | 6      | 8               | .230       | .230 | .165 | N/A  | .410 | .125 | N/A    |                     |               |                        |                     |               |
| M8058-1G38  | 2      | 10              | .230       | .230 | .270 | .373 | .410 | .094 | .331   | Turret              | B             | .125/.165              | P                   |               |
| M8058-1G22  | 3      | 10              | .230       | .230 | .270 | .373 | .410 | .141 | .377   | Solder Pocket       |               |                        |                     |               |
| M8058-1G31  | 4      | 10              | .230       | .230 | .270 | .373 | .410 | .317 | .561   |                     |               |                        |                     |               |
| 8058-1G31   | 4      | 10              | .230       | .230 | .270 | .373 | .410 | .317 | .561   | Printed Circuit     | —             | .156/.218              | N                   |               |
| 8058-24G1   | 5      | 10              | .230       | .380 | .375 | .373 | .410 | .187 | .505   |                     |               |                        |                     |               |
| 8058-1G34   | 6      | 10              | .230       | .230 | .165 | N/A  | .410 | .125 | N/A    |                     |               |                        |                     |               |
| M8058-1G91  | 6      | 10              | .230       | .230 | .165 | N/A  | .410 | .125 | N/A    | Printed Circuit     | —             | .125/.155              | P                   |               |
| 8058-1G55   | 5      | 12              | .250       | .380 | .375 | .373 | .410 | .155 | .467   |                     |               |                        |                     |               |
| 8058-1G51   | 6      | 12              | .280       | .280 | .165 | N/A  | .410 | .125 | N/A    |                     |               |                        |                     |               |

\* Dimension E + .011

\* Dimension E ± .031  
(0,79)

↑  
.155 should be  
.165

Need more technical information?  
Consult your Thomas & Betts  
sales office listed on the back cover

H15

Thomas & Betts  
1555 Lynnfield Road  
Memphis, TN 38119  
(901) 682-8221 FAX (901) 537-8805

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT

|                                        |  |                               |           |                                                                                                       |        |  |
|----------------------------------------|--|-------------------------------|-----------|-------------------------------------------------------------------------------------------------------|--------|--|
| DIMENSIONS:                            |  | DWN                           | 28NOV2006 | MATERIAL                                                                                              | FINISH |  |
| INCHES                                 |  | R BROWN                       |           |                                                                                                       |        |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | CHK                           | 28NOV2006 |  TE Connectivity |        |  |
|                                        |  | K DeBOCK                      |           |                                                                                                       |        |  |
|                                        |  | APVD                          | 28NOV2006 |                                                                                                       |        |  |
|                                        |  | K DeBOCK                      |           |                                                                                                       |        |  |
| PRODUCT SPEC                           |  | NAME                          |           |                                                                                                       |        |  |
| APPLICATION SPEC                       |  | SOCKET, 8 PIN PRINTED CIRCUIT |           |                                                                                                       |        |  |
| WEIGHT                                 |  | RESTRICTED TO                 |           |                                                                                                       |        |  |
| CUSTOMER DRAWING                       |  | SIZE                          | CAGE CODE | DRAWING NO                                                                                            |        |  |
|                                        |  | A4                            | 00779     | C-1437508-5                                                                                           |        |  |
| SCALE                                  |  | SHEET                         |           | REV                                                                                                   |        |  |
| NTS                                    |  | 2 of 4                        |           | A1                                                                                                    |        |  |

|     |      |           |     |             |      |     |      |
|-----|------|-----------|-----|-------------|------|-----|------|
| LOC | DIST | REVISIONS |     |             |      |     |      |
| AD  | 00   | P         | LTR | DESCRIPTION | DATE | DWN | APVD |
|     |      | —         |     | SEE SHEET 1 | —    | —   | —    |

8058 & 8060 Series Transistor Sockets

PART NUMBER / STANDARD CONFIGURATIONS

| Part Number | Figure | Number of Contacts | Pin Circle | A    | B    | C    | D    | E*   | F Max. | Terminal Style  | Mtg. Hole Figure | Transistor Lead Length | Polarization Figure |
|-------------|--------|--------------------|------------|------|------|------|------|------|--------|-----------------|------------------|------------------------|---------------------|
| 8060-1G5    | 3      | 3                  | .100       | .100 | .268 | .227 | .255 | .146 | .350   | Solder Pocket   | A                | .156/.218              | N                   |
| 8060-1G17   | 3      | 3                  | .100       | .100 | .320 | .227 | .255 | .084 | .427   |                 |                  |                        |                     |
| 8060-1G9    | 2      | 3                  | .100       | .100 | .268 | .227 | .255 | .094 | .372   | Turret          |                  |                        |                     |
| 8060-1G11   | 4      | 3                  | .100       | .100 | .330 | .227 | .255 | .240 | .580   | Printed Circuit | —                | .125/.155              | P                   |
| 8060-1G7    | 5      | 3                  | .100       | .200 | .410 | .227 | .255 | .170 | .616   |                 |                  |                        |                     |
| 8060-1G3    | 6      | 3                  | .100       | .150 | .195 | N/A  | .255 | .103 | N/A    |                 |                  |                        |                     |
| 8060-1G13   | 6      | 3                  | .100       | .100 | .195 | N/A  | .255 | .103 | N/A    | Solder Pocket   | A                | .156/.218              | N                   |
| 8060-1G6    | 3      | 4                  | .100       | .100 | .265 | .227 | .255 | .146 | .350   |                 |                  |                        |                     |
| 8060-1G10   | 2      | 4                  | .100       | .100 | .265 | .227 | .255 | .094 | .310   | Turret          |                  |                        |                     |
| 8060-1G12   | 4      | 4                  | .100       | .100 | .330 | .227 | .255 | .240 | .553   | Printed Circuit | —                | .125/.155              | P                   |
| 8060-1G8    | 5      | 4                  | .100       | .200 | .390 | .227 | .255 | .187 | .530   |                 |                  |                        |                     |
| 8060-1G4    | 6      | 4                  | .100       | .150 | .195 | N/A  | .255 | .103 | N/A    |                 |                  |                        |                     |
| 8060-1G22   | 6      | 4                  | .100       | .100 | .195 | N/A  | .255 | .295 | N/A    |                 |                  |                        |                     |

\* Dimension E ± .031  
(0,79)

All part number prefixed with (M) meet MIL-83502/1 or MIL-83502/6.

Thomas & Betts

Quality & Innovation From AUGAT® Name Brand Products

H16


Thomas & Betts  
1555 Lynnfield Road  
Memphis, TN 38119  
(901) 682-8221 FAX (901) 537-8805

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT

|                                                                                                                           |  |                  |           |                                                                                                       |               |  |
|---------------------------------------------------------------------------------------------------------------------------|--|------------------|-----------|-------------------------------------------------------------------------------------------------------|---------------|--|
| DIMENSIONS:                                                                                                               |  | DWN              | 28NOV2006 | MATERIAL                                                                                              | FINISH        |  |
| INCHES                                                                                                                    |  | R BROWN          |           |                                                                                                       |               |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:<br><br>0 PLC ± —<br>1 PLC ± —<br>2 PLC ± —<br>3 PLC ± —<br>4 PLC ± —<br>ANGLES ± — |  | CHK              | 28NOV2006 |  TE Connectivity |               |  |
|                                                                                                                           |  | K DeBOCK         |           |                                                                                                       |               |  |
|                                                                                                                           |  | APVD             | 28NOV2006 |                                                                                                       |               |  |
|                                                                                                                           |  | K DeBOCK         |           | NAME<br>SOCKET, 8 PIN PRINTED CIRCUIT                                                                 |               |  |
|                                                                                                                           |  | PRODUCT SPEC     |           |                                                                                                       |               |  |
| APPLICATION SPEC                                                                                                          |  |                  |           |                                                                                                       |               |  |
|                                                                                                                           |  | SIZE             | CAGE CODE | DRAWING NO                                                                                            | RESTRICTED TO |  |
|                                                                                                                           |  | A4               | 00779     | C-1437508-5                                                                                           | —             |  |
| WEIGHT                                                                                                                    |  | CUSTOMER DRAWING |           |                                                                                                       |               |  |
|                                        |  | SCALE            |           | SHEET                                                                                                 | REV           |  |
|                                                                                                                           |  | NTS              |           | 3 of 4                                                                                                | A1            |  |

| LOC | DIST | REVISIONS |     |             |      |     |      |  |
|-----|------|-----------|-----|-------------|------|-----|------|--|
|     |      | P         | LTR | DESCRIPTION | DATE | DWN | APVD |  |
| AD  | 00   |           | —   | SEE SHEET 1 | —    | —   | —    |  |

Transistor Sockets 8058 & 8060 Series

Figure A  
Recommended Chassis Cutout  
for all 8060 Series panel  
mount applications




Figure B  
Recommended Chassis Cutout  
for all 8058 Series panel  
mount applications







Figure 1




Figure 2




Figure 3




Figure 4




Figure 5




Figure 6




Figure 7

Need more technical information?  
Consult your Thomas & Betts  
sales office listed on the back cover

H17


Thomas & Betts  
1555 Lynnfield Road  
Memphis, TN 38119  
(901) 682-8221 FAX (901) 537-8805

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT

|                                                                                                                              |  |                           |           |                                                                                                                 |  |              |                    |                                           |
|------------------------------------------------------------------------------------------------------------------------------|--|---------------------------|-----------|-----------------------------------------------------------------------------------------------------------------|--|--------------|--------------------|-------------------------------------------|
| DIMENSIONS:<br><br>INCHES                                                                                                    |  | DWN<br>R BROWN            | 28NOV2006 | MATERIAL<br>—                                                                                                   |  | FINISH<br>—  |                    |                                           |
|                                                                                                                              |  | CHK<br>K DeBOCK           | 28NOV2006 | <div>TE Connectivity</div> |  |              |                    |                                           |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br><br>0 PLC ± —<br>1 PLC ± —<br>2 PLC ± —<br>3 PLC ± —<br>4 PLC ± —<br>ANGLES ± — |  | APVD<br>K DeBOCK          | 28NOV2006 |                                                                                                                 |  |              |                    |                                           |
|                                                                                                                              |  | PRODUCT SPEC<br><br>—     |           |                                                                                                                 |  |              |                    | NAME<br><br>SOCKET, 8 PIN PRINTED CIRCUIT |
|                                                                                                                              |  | APPLICATION SPEC<br><br>— |           |                                                                                                                 |  |              |                    |                                           |
|                                                                                                                              |  |                           |           | WEIGHT<br>—                                                                                                     |  | SIZE<br>A4   | CAGE CODE<br>00779 | DRAWING NO<br>C= 1437508-5                |
|                                           |  | CUSTOMER DRAWING          |           |                                                                                                                 |  | SCALE<br>NTS | SHEET<br>4 OF 4    | REV<br>A1                                 |

TE TE Connectivity

SOCKET, 8 PIN PRINTED CIRCUIT

SIZE A4 CAGE CODE 00779 DRAWING NO C-1437508-5

RESTRICTED TO — SCALE NTS SHEET 4 OF 4 REV A1