

CATALOG

➔ Cross Reference

[Competitive Products](#)[Military Spec P/Ns](#)[Tyco Brand P/Ns](#)

- ➔ [Part Number Search](#)
- ➔ [Document Search](#)
- ➔ [Product Type Search](#)
- ➔ [Product Family Search](#)
- ➔ [Alphabetical Search](#)
- ➔ [RoHS/ELV Compliance & Alternates](#)
- ➔ [CAD Model Search](#)
- ➔ [Brand Search](#)
- ➔ [Tool Search](#)
- ➔ [Multiple Part Comparison](#)
- ➔ [Lead Free Solutions](#)
- ➔ [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
click here

Circuit Protection Devices

➔ PolySwitch Resettable Devices

Raychem RUEF900  [Active](#)**Directive 2002/95/EC
Compliant**[RoHS Compliant](#)**(Tyco Electronics P/N: 4-1200578-7)**[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
➤ General Info ➤ Sales Info	➤ Pricing ➤ Product Availability	➤ Tooling

Searchable Features:

Brand:	Raychem
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Wave solder capable to 240° C, Wave solder capable to 265°C
Application:	Radial
Family Name:	RUEF
Construction:	Through Hole
IH (Room Temperature) (Amps.):	9
IT (Room Temperature) (Amps.):	18.00
Operating Temperature (Max.) (° C):	85

Other Properties:

RoHS/ELV Compliance History:	Always was RoHS compliant
Tripped Power Dissipation (Typical) (W):	4.20
Coating:	Coated
Lead Type:	Straight
UL Listed:	File No. E74889
CSA File No.:	78165C
TUV Certificate No.:	R2279286
Packaging Method:	Bulk

Vmax Operating (V):	30
Rmin (Ω):	0.005
Rmax (Ω):	0.010
R1 Max [Post Trip] (Ω):	0.02
UL Rated Current (Amps.):	40

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]