





MOD	LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
5	BD	62				0	RLSE WAS 91-4163-045-01	8-91	-
						A	REV NPR 3794	10/28/91	PR
						B	REVISED ECN B06418	07/28/92	PR
						C	REV PER EC 0020-601-93	10/27/93	PR



ELECTRICAL SCHEMATIC



- 1 SHELL: CARBON STEEL; PIN CONTACT: PHOSPHOR BRONZE; HOUSING: POLYESTER, BLACK; RESISTOR NETWORK: THICK FILM RESISTOR COMPOSITION ON ALUMINA SUBSTRATE. SPRING LATCH: STAINLESS STEEL; COVER: ABS, GRAY, UL 94V-0 RATED.
- 2 RESISTOR TOLERANCE: ±5%.
- 3 5.08µm[.000200] MIN TIN OR TIN-LEAD OVER 1.27µm[.000050] MIN COPPER.
- 4 0.76µm[.000030] MIN GOLD FOR A LENGTH OF 3.35[.132] MIN FROM MATING END OVER 1.27µm[.000050] MIN NICKEL.

					750881-1				
					PART NO				
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.25[.010] 3 PLC DEC ± - ANGLES ± - MATERIAL 1		DR 8-4-91 J McCLINTON		AMP AMP Incorporated Harrisburg, PA 17105-3608					
		CHK 8-5-91 R.STONE							
		APPD 8-7-91 P.RUELVIS					NAME		
		APPD 8-7-91 C.ROHDE							
		PRODUCT SPEC -		PLUG ASSEMBLY, 50 POSITION, .050 SERIES AMPLIMITE™, TERMINATOR					
FINISH SHELL: 3 CONTACTS: 4		APPLICATION SPEC -		SIZE D	CAGE CODE 00779	DRAWING NO 750881			
		WEIGHT -		SCALE 4:1		SHEET 1 OF 1			