

NPN 5 GHz wideband transistor

BFR92AW

FEATURES

- High power gain
- Gold metallization ensures excellent reliability
- SOT323 (S-mini) package.

APPLICATIONS


It is designed for use in RF amplifiers, mixers and oscillators with signal frequencies up to 1 GHz.

DESCRIPTION

Silicon NPN transistor encapsulated in a plastic SOT323 (S-mini) package. The BFR92AW uses the same crystal as the SOT23 version, BFR92A.

PINNING

PIN	DESCRIPTION
1	base
2	emitter
3	collector



QUICK REFERENCE DATA

SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
V_{CBO}	collector-base voltage	open emitter	—	—	20	V
V_{CEO}	collector-emitter voltage	open base	—	—	15	V
I_C	collector current (DC)		—	—	25	mA
P_{tot}	total power dissipation	up to $T_s = 93\text{ °C}$; note 1	—	—	300	mW
h_{FE}	current gain	$I_C = 15\text{ mA}$; $V_{CE} = 10\text{ V}$	40	90	—	
C_{re}	feedback capacitance	$I_C = 0$; $V_{CE} = 10\text{ V}$; $f = 1\text{ MHz}$; $T_{amb} = 25\text{ °C}$	—	0.35	—	pF
f_T	transition frequency	$I_C = 15\text{ mA}$; $V_{CE} = 10\text{ V}$; $f = 500\text{ MHz}$	3.5	5	—	GHz
G_{UM}	maximum unilateral power gain	$I_C = 15\text{ mA}$; $V_{CE} = 10\text{ V}$; $f = 1\text{ GHz}$; $T_{amb} = 25\text{ °C}$	—	14	—	dB
		$I_C = 15\text{ mA}$; $V_{CE} = 10\text{ V}$; $f = 2\text{ GHz}$; $T_{amb} = 25\text{ °C}$	—	8	—	dB
F	noise figure	$I_C = 5\text{ mA}$; $V_{CE} = 10\text{ V}$; $f = 1\text{ GHz}$; $\Gamma_s = \Gamma_{opt}$	—	2	—	dB
T_j	junction temperature		—	—	150	°C

Note

1. T_s is the temperature at the soldering point of the collector pin.

NPN 5 GHz wideband transistor

BFR92AW

LIMITING VALUES

In accordance with the Absolute Maximum System (IEC 134).


SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V_{CBO}	collector-base voltage	open emitter	–	20	V
V_{CEO}	collector-emitter voltage	open base	–	15	V
V_{EBO}	emitter-base voltage	open collector	–	2	V
I_C	collector current (DC)		–	25	mA
P_{tot}	total power dissipation	up to $T_s = 93\text{ }^{\circ}\text{C}$; see Fig.2; note 1	–	300	mW
T_{stg}	storage temperature		–65	+150	$^{\circ}\text{C}$
T_j	junction temperature		–	150	$^{\circ}\text{C}$

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
$R_{th\text{ }j-s}$	thermal resistance from junction to soldering point	up to $T_s = 93\text{ }^{\circ}\text{C}$; note 1	190	K/W

Note to the Limiting values and Thermal characteristics

1. T_s is the temperature at the soldering point of the collector pin.



NPN 5 GHz wideband transistor

BFR92AW

CHARACTERISTICS

$T_j = 25\text{ }^{\circ}\text{C}$ (unless otherwise specified).




SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
I_{CBO}	collector leakage current	$I_E = 0; V_{CB} = 10\text{ V}$	–	–	50	nA
h_{FE}	DC current gain	$I_C = 15\text{ mA}; V_{CE} = 10\text{ V}$	40	90	–	
C_c	collector capacitance	$I_E = I_B = 0; V_{CB} = 10\text{ V}; f = 1\text{ MHz}$	–	0.6	–	pF
C_e	emitter capacitance	$I_C = I_C = 0; V_{EB} = 0.5\text{ V}; f = 1\text{ MHz}$	–	0.9	–	pF
C_{re}	feedback capacitance	$I_C = 0; V_{CE} = 10\text{ V}; f = 1\text{ MHz}$	–	0.35	–	pF
f_T	transition frequency	$I_C = 15\text{ mA}; V_{CE} = 10\text{ V}; f = 500\text{ MHz}$	3.5	5	–	GHz
G_{UM}	maximum unilateral power gain; note 1	$I_C = 15\text{ mA}; V_{CE} = 10\text{ V}; f = 1\text{ GHz}; T_{amb} = 25\text{ }^{\circ}\text{C}$	–	14	–	dB
		$I_C = 15\text{ mA}; V_{CE} = 10\text{ V}; f = 2\text{ GHz}; T_{amb} = 25\text{ }^{\circ}\text{C}$	–	8	–	dB
F	noise figure	$I_C = 5\text{ mA}; V_{CE} = 10\text{ V}; f = 1\text{ GHz}; \Gamma_s = \Gamma_{opt}$	–	2	–	dB
		$I_C = 5\text{ mA}; V_{CE} = 10\text{ V}; f = 2\text{ GHz}; \Gamma_s = \Gamma_{opt}$	–	3	–	dB

Note

1. G_{UM} is the maximum unilateral power gain, assuming s_{12} is zero and $G_{UM} = 10 \log \frac{|s_{21}|^2}{(1 - |s_{11}|^2)(1 - |s_{22}|^2)}$ dB.


NPN 5 GHz wideband transistor

BFR92AW




NPN 5 GHz wideband transistor

BFR92AW




$V_{CE} = 10\text{ V}$; $f = 500\text{ MHz}$.

Fig.6 Gain as a function of collector current; typical values.




$V_{CE} = 10\text{ V}$; $f = 1\text{ GHz}$.

Fig.7 Gain as a function of collector current; typical values.



$V_{CE} = 10\text{ V}$; $I_C = 5\text{ mA}$.

Fig.8 Gain as a function of frequency; typical values.




$V_{CE} = 10\text{ V}$; $I_C = 15\text{ mA}$.

Fig.9 Gain as a function of frequency; typical values.


NPN 5 GHz wideband transistor

BFR92AW




$V_{CE} = 10 \text{ V.}$

Fig.10 Minimum noise figure as a function of collector current; typical values.



$V_{CE} = 10 \text{ V.}$

Fig.11 Minimum noise figure as a function of frequency; typical values.





$f = 500 \text{ MHz; } V_{CE} = 10 \text{ V; } I_C = 5 \text{ mA; } Z_0 = 50 \Omega.$

Fig.12 Common emitter noise figure circles; typical values.


NPN 5 GHz wideband transistor

BFR92AW




NPN 5 GHz wideband transistor

BFR92AW



$V_{CE} = 10\text{ V}$; $I_C = 15\text{ mA}$; $Z_o = 50\ \Omega$.

Fig.15 Common emitter input reflection coefficient (s_{11}); typical values.




$V_{CE} = 10\text{ V}$; $I_C = 15\text{ mA}$.

Fig.16 Common emitter forward transmission coefficient (s_{21}); typical values.


NPN 5 GHz wideband transistor

BFR92AW



$V_{CE} = 10 \text{ V}$; $I_C = 15 \text{ mA}$.

Fig.17 Common emitter reverse transmission coefficient (s_{12}); typical values.




$V_{CE} = 10 \text{ V}$; $I_C = 15 \text{ mA}$; $Z_0 = 50 \Omega$.

Fig.18 Common emitter output reflection coefficient (s_{22}); typical values.

NPN 5 GHz wideband transistor

BFR92AW

PACKAGE OUTLINE



MBC871

Dimensions in mm.

Fig.19 SOT323.