


## Lead (Pb)-Bearing Thick Film, Rectangular High Value Chip Resistor



### FEATURES

**HALOGEN  
FREE**

- High resistance values (up to 470M)
- Suitable for voltage dividers and hybrids
- Lead (Pb)-bearing termination plating on Ni barrier layer
- Metal glaze on high quality ceramic
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

### STANDARD ELECTRICAL SPECIFICATIONS

| MODEL           | CASE SIZE INCH | CASE SIZE METRIC | POWER RATING $P_{70}$ W | LIMITING ELEMENT VOLTAGE $U_{max. AC_{RMS}/DC}$ V | TEMPERATURE COEFFICIENT ppm/K | TOLERANCE % | RESISTANCE RANGE $\Omega$ | SERIES |
|-----------------|----------------|------------------|-------------------------|---------------------------------------------------|-------------------------------|-------------|---------------------------|--------|
| D11/CRCW0603-HR | 0603           | RR 1608M         | 0.10                    | 75                                                | $\pm 500$                     | $\pm 5$     | 11M to 470M               | E24    |
| D12/CRCW0805-HR | 0805           | RR 2012M         | 0.125                   | 150                                               | $\pm 500$                     | $\pm 5$     | 11M to 470M               | E24    |
| D25/CRCW1206-HR | 1206           | RR 3216M         | 0.25                    | 200                                               | $\pm 500$                     | $\pm 5$     | 11M to 470M               | E24    |

### Notes

- These resistors do not feature a limited lifetime when operated within the limits of rated dissipation, permissible operating voltage, and permissible film temperature. However, the resistance typically increase due to the resistor's film temperature over operating time, generally known as drift. The drift may exceed the stability requirements of an individual application circuit and thereby limits the functional time.
- Marking and packaging: See datasheet "Surface Mount Resistor Marking" ([www.vishay.com/doc?20020](http://www.vishay.com/doc?20020))
- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material.

### TECHNICAL SPECIFICATIONS

| PARAMETER                                    | UNIT        | D11/CRCW0603-HR                    | D12/CRCW0805-HR | D25/CRCW1206-HR |
|----------------------------------------------|-------------|------------------------------------|-----------------|-----------------|
| Rated Dissipation at $P_{70}$ <sup>(1)</sup> | W           | 0.1                                | 0.125           | 0.25            |
| Operating Voltage $U_{max. AC_{RMS}/DC}$     | V           | 75                                 | 150             | 200             |
| Voltage Coefficient                          | %/V         | $< 100M: < 0.1$<br>$> 100M: < 0.3$ |                 |                 |
| Insulation Voltage $U_{ins}$ (1 min)         | V           | 100                                | 200             | 300             |
| Insulation Resistance                        | $\Omega$    | $> 10^9$                           |                 |                 |
| Operating Temperature Range                  | $^{\circ}C$ | - 55 to + 155                      |                 |                 |
| Weight                                       | mg          | 2                                  | 5.5             | 10              |

### Note

- <sup>(1)</sup> The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature of 155  $^{\circ}C$  is not exceeded.

**PART NUMBER AND PRODUCT DESCRIPTION**

Part Number: CRCW060316M0JPTBHR

|   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |   |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| C | R | C | W | 0 | 6 | 0 | 3 | 1 | 6 | M | 0 | J | P | T | B | H | R |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|



| MODEL/SIZE                       | RESISTANCE  | TOLERANCE | TCR             | PACKAGING    | SPECIAL                           |
|----------------------------------|-------------|-----------|-----------------|--------------|-----------------------------------|
| CRCW0603<br>CRCW0805<br>CRCW1206 | M = Million | J = ± 5 % | P = ± 500 ppm/K | TA, TB<br>TC | Up to 2 digits<br>HR = High value |

Product Description: CRCW0603-HR 500 16M 5% RT5


|                                           |             |                              |           |                 |
|-------------------------------------------|-------------|------------------------------|-----------|-----------------|
| CRCW0603-HR                               | 500         | 16M                          | J         | RT5             |
| MODEL                                     | TCR         | RESISTANCE                   | TOLERANCE | PACKAGING       |
| CRCW0603-HR<br>CRCW0805-HR<br>CRCW1206-HR | ± 500 ppm/K | 68M = 68 MΩ<br>220M = 220 MΩ | ± 5 %     | RT1, RT5<br>RT6 |

**PACKAGING**

| MODEL       | CODE     | QUANTITY | CARRIER TAPE                                | WIDTH | PITCH | REEL DIAMETER |
|-------------|----------|----------|---------------------------------------------|-------|-------|---------------|
| CRCW0603-HR | TA = RT1 | 5000     | Paper tape acc. to<br>IEC 60068-3<br>Type I | 8 mm  | 4 mm  | 180 mm/7"     |
|             | TB = RT5 | 10 000   |                                             |       |       | 285 mm/11.25" |
|             | TC = RT6 | 20 000   |                                             |       |       | 330 mm/13"    |
| CRCW0805-HR | TA = RT1 | 5000     |                                             | 8 mm  | 4 mm  | 180 mm/7"     |
|             | TB = RT5 | 10 000   |                                             |       |       | 285 mm/11.25" |
|             | TC = RT6 | 20 000   |                                             |       |       | 330 mm/13"    |
| CRCW1206-HR | TA = RT1 | 5000     |                                             | 8 mm  | 4 mm  | 180 mm/7"     |
|             | TB = RT5 | 10 000   |                                             |       |       | 285 mm/11.25" |
|             | TC = RT6 | 20 000   |                                             |       |       | 330 mm/13"    |

**DIMENSIONS**


| SIZE |        | DIMENSIONS in millimeters                |             |             |                                         |           | SOLDER PAD DIMENSIONS in millimeters |     |     |                |     |     |
|------|--------|------------------------------------------|-------------|-------------|-----------------------------------------|-----------|--------------------------------------|-----|-----|----------------|-----|-----|
|      |        |                                          |             |             |                                         |           | REFLOW SOLDERING                     |     |     | WAVE SOLDERING |     |     |
| INCH | METRIC | L                                        | W           | H           | T1                                      | T2        | a                                    | b   | l   | a              | b   | l   |
| 0603 | 1608   | 1.55 <sup>+0.10</sup> / <sub>-0.05</sub> | 0.85 ± 0.1  | 0.45 ± 0.05 | 0.3 ± 0.2                               | 0.3 ± 0.2 | 0.5                                  | 0.9 | 1.0 | 0.9            | 0.9 | 1.0 |
| 0805 | 2012   | 2.0 <sup>+0.20</sup> / <sub>-0.10</sub>  | 1.25 ± 0.15 | 0.45 ± 0.05 | 0.3 <sup>+0.20</sup> / <sub>-0.10</sub> | 0.3 ± 0.2 | 0.7                                  | 1.3 | 1.2 | 0.9            | 1.3 | 1.3 |
| 1206 | 3216   | 3.2 <sup>+0.10</sup> / <sub>-0.20</sub>  | 1.6 ± 0.15  | 0.55 ± 0.05 | 0.45 ± 0.2                              | 0.4 ± 0.2 | 0.9                                  | 1.7 | 2.0 | 1.1            | 1.7 | 2.3 |

**DERATING**

**TEST PROCEDURES AND REQUIREMENTS**

| EN 60115-1<br>CLAUSE                                                 | IEC<br>60068-2<br>TEST<br>METHOD                               | TEST                                                                                                                  | PROCEDURE                                                                                                                                                                                | REQUIREMENTS<br>PERMISSIBLE CHANGE ( $\Delta R$ )                                      |
|----------------------------------------------------------------------|----------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|
|                                                                      |                                                                |                                                                                                                       |                                                                                                                                                                                          | STABILITY CLASS 2 OR BETTER                                                            |
|                                                                      |                                                                |                                                                                                                       | Stability for product types:                                                                                                                                                             | 11 M $\Omega$ to 470 M $\Omega$                                                        |
|                                                                      |                                                                |                                                                                                                       | D/CRCW-HR                                                                                                                                                                                |                                                                                        |
| 4.5                                                                  | —                                                              | Resistance                                                                                                            | -                                                                                                                                                                                        | $\pm 5 \%$                                                                             |
| 4.13                                                                 | —                                                              | Short time overload                                                                                                   | $U = 2.5 \times \sqrt{P_{70} \times R} \leq 2 \times U_{\max.}$ ;<br>Duration acc. to style                                                                                              | $\pm (0.5 \% R + 0.05 \Omega)$                                                         |
| 4.17.2                                                               | 58 (Td)                                                        | Solderability                                                                                                         | Solder bath method;<br>Sn60Pb40                                                                                                                                                          | Good tinning ( $\geq 95 \%$ covered); no visible damage                                |
| 4.8.4.2                                                              | —                                                              | Temperature coefficient                                                                                               | 20 °C/- 55 °C/20 °C and<br>20 °C/125 °/20 °C                                                                                                                                             | $\pm 500$ ppm/K                                                                        |
| 4.32                                                                 | 21 (Uu <sub>3</sub> )                                          | Shear (adhesion)                                                                                                      | RR 1608: 9 N<br>RR 2012 and RR 3216: 45 N                                                                                                                                                | No visible damage                                                                      |
| 4.33                                                                 | 21 (Uu <sub>1</sub> )                                          | Substrate bending                                                                                                     | Depth 2 mm;<br>3 times                                                                                                                                                                   | No visible damage, no open circuit in bent position<br>$\pm (0.25 \% R + 0.05 \Omega)$ |
| 4.19                                                                 | 14 (Na)                                                        | Rapid change of temperature                                                                                           | 30 min. at - 55 °C;<br>30 min. at 125 °C<br><br>5 cycles<br>1000 cycles                                                                                                                  | $\pm (0.5 \% R + 0.05 \Omega)$<br>$\pm (1 \% R + 0.05 \Omega)$                         |
| 4.23<br>4.23.2<br>4.23.3<br><br>4.23.4<br>4.23.5<br>4.23.6<br>4.23.7 | —<br>2 (Ba)<br>30 (Db)<br><br>1 (Aa)<br>13 (M)<br>30 (Db)<br>— | Climatic sequence:<br>Dry Heat<br>Damp heat, cyclic<br><br>Cold<br>Low air pressure<br>Damp heat, cyclic<br>D.C. Load | —<br>125 °C; 16 h<br>55 °C; $\geq 90 \%$ RH;<br>24 h; 1 cycle<br>- 55 °C; 2 h<br>1 kPa; (25 $\pm$ 10) °C; 1 h<br>55 °C; $\geq 90 \%$ RH<br>24 h; 5 cycle<br>$U = \sqrt{P_{70} \times R}$ | $\pm (2 \% R + 0.1 \Omega)$                                                            |
| 4.25.1                                                               | —                                                              | Endurance at<br>70 °C                                                                                                 | $U = \sqrt{P_{70} \times R} \leq U_{\max.}$<br>1.5 h on; 0.5 h off;<br>70 °C; 1000 h<br>70 °C; 8000 h                                                                                    | $\pm (2 \% R + 0.1 \Omega)$<br>$\pm (4 \% R + 0.1 \Omega)$                             |



| TEST PROCEDURES AND REQUIREMENTS |                                  |                                         |                                                           |                                                   |
|----------------------------------|----------------------------------|-----------------------------------------|-----------------------------------------------------------|---------------------------------------------------|
| EN 60115-1<br>CLAUSE             | IEC<br>60068-2<br>TEST<br>METHOD | TEST                                    | PROCEDURE                                                 | REQUIREMENTS<br>PERMISSIBLE CHANGE ( $\Delta R$ ) |
|                                  |                                  |                                         |                                                           | STABILITY CLASS 2 OR BETTER                       |
|                                  |                                  |                                         | Stability for product types:                              | 11 M $\Omega$ to 470 M $\Omega$                   |
|                                  |                                  |                                         | D/CRCW-HR                                                 |                                                   |
| 4.18.2                           | 58 (Td)                          | Resistance to soldering heat            | Solder bath method<br>(260 $\pm$ 5) °C;<br>(10 $\pm$ 1) s | $\pm$ (0.5 % $R$ + 0.05 $\Omega$ )                |
| 4.24                             | 78 (Cab)                         | Damp heat, steady state                 | (40 $\pm$ 2) °C;<br>(93 $\pm$ 3) % RH; 56 days            | $\pm$ (2 % $R$ + 0.1 $\Omega$ )                   |
| 4.25.3                           | —                                | Endurance at upper category temperature | 155 °C; 1000 h                                            | $\pm$ (2 % $R$ + 0.1 $\Omega$ )                   |

All tests are carried out in accordance with the following specifications:

- EN 60115-1, generic specification
- EN 140400, sectional specification
- EN 140401-802, detail specification
- IEC 60068-2-x, variety of environmental test procedures

Packaging of components is done in paper or blister tapes according to IEC 60286-3.



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**