




[+ HARNESSING](#)

CABLE ENTRY SEALS



✓ Active

TE CONNECTIVITY (TE)

CES-3R

[Raychem](#) | [CS](#)

CES-3R
TE Internal Number: CC4331-000

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Seal Type Standard

Material Nylon, Polyolefin

Number of Branches/Legs 1

Expanded Inside Diameter (Min) 28 mm [1.1 in]

Recovered Inside Diameter (Max) 10 mm [.394 in]

[↓](#) **PRODUCT DRAWING**
[English](#)

DOCUMENTATION

Product Drawings

Cable Entry Seals, Right Angle, Standard

PDF

English

Product Specifications

Product Specification

Thermofit Polyolefin Molded Components Flame-Retarded, Semi-Rigid, Heat-Shrinkable

PDF

English

Raychem S1297 And /97 Hot Melt Adhesive

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Thread Size 1-3/8-12
Product Type Heat Shrink Cable Entry Seal
Angle 90°

Configuration Features

Number of Branches/Legs 1

Body Features

Seal Type Standard
Material Nylon, Polyolefin

Dimensions

Expanded Inside Diameter (Min) 28 mm [1.1 in]
Recovered Inside Diameter (Max) 10 mm [.394 in]
Drill Size 1.375
Cable Diameter Range 10.16 – 23.88 mm [.4 – .94 in]
Overall Length (Recovered) 53 mm [2.1 in]
Overall Length (Supplied) 53 mm [2.1 in]

Usage Conditions

Flammability Flame-Retardant

Other

Comment Molded part has hot-melt adhesive preinstalled.

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF