



# Data Sheet

## MI-J00

### DC-DC Converters

### 10 to 50 Watts



#### Features

- Inputs:
  - 28 Vdc per MIL-STD-704D/E/F
  - 155 Vdc per MIL-STD-1399A
  - 270 Vdc per MIL-STD-704D/E/F
- Single output: 2 – 48 Vdc
- Up to 23 W/in<sup>3</sup>
- MIL-STD-810 environments
- Up to 90% efficiency
- Remote sense
- Current limit
- ZCS power architecture
- Low noise FM control
- Size: 2.28" x 2.4" x 0.5" (57,9 x 61,0 x 12,7 mm)

#### Product Highlights

The MI-J00 family of DC-DC converters is designed for applications utilizing distributed power architectures. Based on Vicor's VI-200 / VI-J00 family of zero-current switching, component-level DC-DC converters, the MI-J00 family offers exceptional performance in terms of power density, efficiency, noise, ease of use, and reliability.

The MI-J00 family meets all steady-state, transient and under/overvoltage requirements of MIL-STD-704D/E/F for both 28 Vdc input (MI-J2X) and 270 Vdc input (MI-J6X), and the worst case envelope of MIL-STD-1399A for 155 Vdc input (MI-J5X).

The output voltage can be externally trimmed or programmed from 50% to 110% of nominal output. Current limiting, remote sense, and an inhibit pin all combine to offer a high degree of protection, versatility, and reliability for power systems.

Fully encapsulated in Vicor's industry standard package, the MI-J00 family meets MIL-STD-810 environmental testing requirements for humidity, fungus, salt-fog, explosive atmosphere, acceleration, vibration, and shock.

#### Packaging Options

**Standard:** Slotted baseplate

**SlimMod:** Flangeless baseplate, option suffix: - S  
Example: MI - JXX - XX - S

**FinMod:** Finned heat sink, option suffix:  
- F1, -F2, -F3 and - F4

Examples:

MI - JXX - XX -F1, 0.25" fins, longitudinal  
MI - JXX - XX -F2, 0.50" fins, longitudinal  
MI - JXX - XX -F3, 0.25" fins, transverse  
MI - JXX - XX -F4, 0.50" fins, transverse

#### Converter Selection Chart

### MI-J

Semi-custom modules available, consult factory.

#### Input Voltage

| Nominal   | Range                      | Transient <sup>[a]</sup> | Notes                              |
|-----------|----------------------------|--------------------------|------------------------------------|
| 2 = 28 V  | 18 – 50 V <sup>[b]</sup>   | 60 V                     | 28 Vdc input per MIL-STD 704D/E/F  |
| 5 = 155 V | 100 – 210 V                | 230 V                    | 155 Vdc input per MIL-STD-1399A    |
| 6 = 270 V | 125 – 400 V <sup>[c]</sup> | 475 V                    | 270 Vdc input per MIL-STD-704D/E/F |
| 7 = 165 V | 100 – 310 V                | n/a                      |                                    |

<sup>[a]</sup> Transient voltage for 1 second.

<sup>[b]</sup> 16 V operation at 75% load.

<sup>[c]</sup> These units rated at 75% load from 125 – 150 Vin: MI-J6Z-xY, MI-J6Y-xY, MI-J60-xY

#### Output Voltage

|           |            |
|-----------|------------|
| Z = 2.0 V | 1 = 12 V   |
| Y = 3.3 V | P = 13.8 V |
| 0 = 5.0 V | 2 = 15 V   |
| X = 5.2 V | N = 18.5 V |
| W = 5.5 V | 3 = 24 V   |
| V = 5.8 V | L = 28 V   |
| T = 6.5 V | J = 36 V   |
| R = 7.5 V | K = 40 V   |
| M = 10 V  | 4 = 48 V   |

#### Product Grade Temperatures (°C)

| Operating       | Storage         |
|-----------------|-----------------|
| I = -40 to +100 | I = -55 to +125 |
| M = -55 to +100 | M = -65 to +125 |

#### Output Power/Current Vout

| ≥ 5 V    | < 5 V    |
|----------|----------|
| A = 10 W | A = —    |
| Z = 25 W | Z = 5 A  |
| Y = 50 W | Y = 10 A |

## CONVERTER SPECIFICATIONS

(typical at  $T_{BP} = 25^{\circ}\text{C}$ , nominal line and 75% load, unless otherwise specified)

### ■ INPUT SPECIFICATIONS

| Parameter                           | Min | Typ                                               | Max                  | Units    | Test Conditions         |
|-------------------------------------|-----|---------------------------------------------------|----------------------|----------|-------------------------|
| Inrush charge                       |     | $60 \times 10^{-6}$                               | $100 \times 10^{-6}$ | Coulombs | Nominal line            |
| Input reflected ripple current – pp |     | 10%                                               |                      | $I_{IN}$ | Nominal line, full load |
| Input ripple rejection              |     | $30 + 20 \log\left(\frac{V_{in}}{V_{out}}\right)$ |                      | dB       | 120 Hz, nominal line    |
|                                     |     | $20 + 20 \log\left(\frac{V_{in}}{V_{out}}\right)$ |                      | dB       | 2400 Hz, nominal line   |
| No load power dissipation           |     | 1.35                                              | 2                    | Watts    |                         |

### ■ OUTPUT CHARACTERISTICS

| Parameter                       | Min | Typ  | Max  | Units                  | Test Conditions                          |
|---------------------------------|-----|------|------|------------------------|------------------------------------------|
| Setpoint accuracy               |     | 0.5  | 1    | % $V_{NOM}$            |                                          |
| Load/line regulation            |     | 0.05 | 0.2  | % $V_{NOM}$            | LL to HL, 10% to Full Load               |
|                                 |     | 0.2  | 0.5  | % $V_{NOM}$            | LL to HL, No Load to 10%                 |
| Output temperature drift        |     | 0.01 | 0.02 | % / $^{\circ}\text{C}$ | Over rated temperature                   |
| Long term drift                 |     | 0.02 |      | %/1K hours             |                                          |
| Output ripple – pp              |     | 100  | 150  | mV                     | Whichever is greater<br>20 MHz bandwidth |
|                                 |     | 1.0  | 1.5  | % $V_{NOM}$            |                                          |
| Trim range <sup>[a]</sup>       | 50  |      | 110  | % $V_{NOM}$            |                                          |
| Total remote sense compensation | 0.5 |      |      | Volts                  |                                          |
| Current limit                   | 105 |      | 125  | % $I_{NOM}$            | Automatic restart                        |
| Short circuit current           | 105 |      | 130  | % $I_{NOM}$            |                                          |

<sup>[a]</sup> 10 V, 12 V and 15 V outputs, standard trim range  $\pm 10\%$ . Consult factory for wider trim range.

### ■ CONTROL PIN SPECIFICATIONS

| Parameter              | Min  | Typ  | Max | Units | Test Conditions    |
|------------------------|------|------|-----|-------|--------------------|
| Gate out impedance     |      | 50   |     | -     |                    |
| Gate in impedance      |      | 1000 |     | -     |                    |
| Gate in high threshold |      |      | 6   | Volts | Use open collector |
| Gate in low threshold  | 0.65 |      |     | Volts |                    |
| Gate in low current    |      |      | 6   | mA    |                    |

## CONVERTER SPECIFICATIONS (cont.)

### ■ DIELECTRIC WITHSTAND CHARACTERISTICS

| Parameter                   | Min   | Typ | Max | Units            | Test Conditions   |
|-----------------------------|-------|-----|-----|------------------|-------------------|
| Input to output             | 3,000 |     |     | V <sub>RMS</sub> | Baseplate earthed |
| Output to baseplate         | 500   |     |     | V <sub>RMS</sub> |                   |
| Input to baseplate          | 1,500 |     |     | V <sub>RMS</sub> |                   |
| Input to output capacitance |       | 50  | 75  | pF               |                   |

### ■ THERMAL CHARACTERISTICS

| Parameter         | Min | Typ      | Max | Units   | Test Conditions   |
|-------------------|-----|----------|-----|---------|-------------------|
| Efficiency        |     | 80 – 90% |     |         |                   |
| Baseplate to sink |     | 0.14     |     | °C/Watt | With thermal pads |

### ■ ENVIRONMENTAL – MIL-STD-810D

| Parameter                   | Min    | Typ | Max | Units   | Test Conditions         |
|-----------------------------|--------|-----|-----|---------|-------------------------|
| Altitude - method 500.2     | 70,000 |     |     | feet    | Procedure II            |
| Humidity - method 507.2     | 88/240 |     |     | %/hours | Procedure I, cycle 1    |
| Acceleration - method 513.3 | 9      |     |     | g       | Procedure II            |
| Vibration - method 514.3    | 20     |     |     | g       | Procedure I, category 6 |
| Shock - method 516.3        | 40     |     |     | g       | Procedure I             |

### ■ RELIABILITY - MIL-HDBK-217F (MI-J2L-MY)

| Parameter                                | Min | Typ   | Max | Units       | Test Conditions |
|------------------------------------------|-----|-------|-----|-------------|-----------------|
| 25°C Ground Benign: G.B.                 |     | 3,732 |     | 1,000 hours |                 |
| 50°C Naval Sheltered: N.S.               |     | 672   |     | 1,000 hours |                 |
| 65°C Airborne Inhabited<br>Cargo: A.I.C. |     | 526   |     | 1,000 hours |                 |

### ■ MECHANICAL SPECIFICATIONS

| Parameter | Min        | Typ        | Max        | Units           | Test Conditions |
|-----------|------------|------------|------------|-----------------|-----------------|
| Weight    | 3.5<br>101 | 3.7<br>107 | 3.8<br>109 | Ounces<br>Grams |                 |

## CONVERTER SPECIFICATIONS (cont.)



### ■ PRODUCT GRADE SPECIFICATIONS

| Parameter                                                           | I-Grade                      | M-Grade                      |
|---------------------------------------------------------------------|------------------------------|------------------------------|
| Storage temperature                                                 | -55°C to +125°C              | -65°C to +125°C              |
| Operating temperature (baseplate)                                   | -40°C to +100°C              | -55°C to +100°C              |
| Power cycling burn-in                                               | 12 hours, 29 cycles          | 96 hours, 213 cycles         |
| Temperature cycled with power off<br>17°C per minute rate of change | 12 cycles<br>-65°C to +100°C | 12 cycles<br>-65°C to +100°C |
| Test data supplied at these temperatures <sup>[a]</sup>             | -40°C, +80°C                 | -55°C, +80°C                 |
| Warranty                                                            | 2 years                      | 2 years                      |
| Environmental compliance                                            | MIL-STD-810                  | MIL-STD-810                  |
| Derating                                                            | NAVMAT P-4855-1A             | NAVMAT P-4855-1A             |

<sup>[a]</sup> Test data available for review or download from vicorpower.com

### ■ ENVIRONMENTAL QUALIFICATIONS

| Parameter            | Qualification                                                                                                                                                                                                                          |
|----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Altitude             | MIL-STD-810D, Method 500.2, Procedure III, explosive decompression (40 K ft.).                                                                                                                                                         |
|                      | MIL-STD-810D, Method 500.2, Procedure II, 40,000 ft., 1000 – 1500 ft./min. to 70,000 ft., unit functioning                                                                                                                             |
| Explosive Atmosphere | MIL-STD-810C, Method 511.1, Procedure I                                                                                                                                                                                                |
| Vibration            | MIL-STD-810D, Method 514.3, Procedure I, category 6, helicopter, 20 g                                                                                                                                                                  |
|                      | MIL-STD-810D, Method 514.3 random: 10 – 300 Hz @ 0.02 g <sup>2</sup> /Hz, 2000 Hz @ 0.002 g <sup>2</sup> /Hz, 3.9 total G rms<br>3 hrs/axis. Sine: 30 Hz @ 20 g, 60 Hz @ 10 g, 90 Hz @ 6.6 g, 120 Hz @ 5.0 g, 16.0 total G rms, 3 axes |
|                      | MIL-STD-810E, Method 514.4, Table 514.4-VII, ±6 db/octave, 7.7 G rms, 1hr/axis                                                                                                                                                         |
| Shock                | MIL-STD-810D, Method 516.3, Procedure I, functional shock, 40 g                                                                                                                                                                        |
|                      | MIL-STD-202F, Method 213B, 18 pulses, 60 g, 9 msec                                                                                                                                                                                     |
|                      | MIL-STD-202F, Method 213B, 75 g, 11 ms saw tooth shock                                                                                                                                                                                 |
|                      | MIL-STD-202F, Method 207A, 3 impacts / axis, 1, 3, 5 feet                                                                                                                                                                              |
| Acceleration         | MIL-STD-810D, Method 513.3, Procedure II Operational test, 9 g for 1 minute along 3 mutually perpendicular axes                                                                                                                        |
| Humidity             | MIL-STD-810D, Method 507.2, Procedure I, cycle I, 240 hrs, 88% relative humidity                                                                                                                                                       |
| Solder Test          | MIL-STD-202, Method 208, 8 hr. aging                                                                                                                                                                                                   |
| Fungus               | MIL-STD-810C, Method 508.1                                                                                                                                                                                                             |
| Salt-Fog             | MIL-STD-810C, Method 509.1                                                                                                                                                                                                             |



## **Warranty**

Vicor products are guaranteed for two years from date of shipment against defects in material or workmanship when in normal use and service. This warranty does not extend to products subjected to misuse, accident, or improper application or maintenance. Vicor shall not be liable for collateral or consequential damage. This warranty is extended to the original purchaser only.

EXCEPT FOR THE FOREGOING EXPRESS WARRANTY, VICOR MAKES NO WARRANTY, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, THE WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.

Vicor will repair or replace defective products in accordance with its own best judgement. For service under this warranty, the buyer must contact Vicor to obtain a Return Material Authorization (RMA) number and shipping instructions. Products returned without prior authorization will be returned to the buyer. The buyer will pay all charges incurred in returning the product to the factory. Vicor will pay all reshipment charges if the product was defective within the terms of this warranty.

Information published by Vicor has been carefully checked and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Vicor reserves the right to make changes to any products without further notice to improve reliability, function, or design. Vicor does not assume any liability arising out of the application or use of any product or circuit; neither does it convey any license under its patent rights nor the rights of others. Vicor general policy does not recommend the use of its components in life support applications wherein a failure or malfunction may directly threaten life or injury. Per Vicor Terms and Conditions of Sale, the user of Vicor components in life support applications assumes all risks of such use and indemnifies Vicor against all damages.

## **Vicor's comprehensive line of power solutions includes high density AC-DC and DC-DC modules and accessory components, fully configurable AC-DC and DC-DC power supplies, and complete custom power systems.**

Information furnished by Vicor is believed to be accurate and reliable. However, no responsibility is assumed by Vicor for its use. Vicor components are not designed to be used in applications, such as life support systems, wherein a failure or malfunction could result in injury or death. All sales are subject to Vicor's Terms and Conditions of Sale, which are available upon request.

**Specifications are subject to change without notice.**

## **Intellectual Property Notice**

Vicor and its subsidiaries own Intellectual Property (including issued U.S. and Foreign Patents and pending patent applications) relating to the products described in this data sheet. Interested parties should contact Vicor's Intellectual Property Department.

**Vicor Corporation**  
25 Frontage Road  
Andover, MA, USA 01810  
Tel: 800-735-6200  
Fax: 978-475-6715

### **email**

Customer Service: [custserv@vicorpower.com](mailto:custserv@vicorpower.com)  
Technical Support: [apps@vicorpower.com](mailto:apps@vicorpower.com)