



LOC	DIST	P	F	REVISIONS						
				ZONE	LTR	DESCRIPTION			DATE	APPD
HM	00				B	REV; EC 0B40-0292-00			05JAN01	GG MD



1. DIMENSIONS ARE MAXIMUM.
2. MATERIAL:PRINTED CIRCUIT BOARD-LAMINATED PLASTIC SHEET, 1.57 [.062] THICK.
ADAPTER-ABS MOLDING COMPOUND, SEE TABLE.
PRINTED CIRCUIT FINGERS-0.51μm [.000020] MINIMUM GOLD PLATE OVER
1.27μm [.000050] MINIMUM NICKEL PLATE.
3. THIS INTERCONNECT MEETS THE REQUIREMENTS OF IEC 603-7.
4. THIS INSERT IS DESIGNED TO MATE WITH AMP INC. EDGE CONNECTOR KIT AND WALLBOX KITS.



BLACK	260-6	IVORY	557260-6
BLACK	260-5	WHITE	557260-5
BLACK	260-4	NEMA GRAY	557260-4
WHITE	260-3	BLACK	557260-3
BLACK	260-1	LIGHT ALMOND	557260-1

MARKING COLOR	CODE NO.	ADAPTER COLOR	PART NO
AMP AMP Incorporated Harrisburg, PA 17105-3608			
NAME INSERT ASSEMBLY, DUAL, RJ45, EIA/10BT, CATEGORY 5e, AMP COMMUNICATION OUTLET			
SIZE	CAGE CODE	DRAWING NO	
©	00779	©=557260	
SCALE	2:1	SHEET	1 OF 1

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 3 PLC DEC ± ANGLES ±	DR 7-6-94 D. STRAUSSER	NAME INSERT ASSEMBLY, DUAL, RJ45, EIA/10BT, CATEGORY 5e, AMP COMMUNICATION OUTLET
	CHK 7-13-94 B. FOX	
MATERIAL	APPD 7-13-94 L. HOFFMAN	PRODUCT SPEC
	APPD 7-13-94 M. MILLER	
FINISH	APPLICATION SPEC	SIZE
	-	©
WEIGHT	-	SCALE
	-	2:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.