

4		3		2		1	
© - TE Connectivity. All Rights Reserved.							
		REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
	-	SEE SHEET 1			-	-	-

		99.06	[3.900]	101.60	[4.000]	80	4-147424-0	
		96.52	[3.800]	99.06	[3.900]	78	3-147424-9	
		93.98	[3.700]	96.52	[3.800]	76	3-147424-8	
		91.44	[3.600]	93.98	[3.700]	74	3-147424-7	
		88.90	[3.500]	91.44	[3.600]	72	3-147424-6	
		86.36	[3.400]	88.90	[3.500]	70	3-147424-5	
		83.82	[3.300]	86.36	[3.400]	68	3-147424-4	
		81.28	[3.200]	83.82	[3.300]	66	3-147424-3	
		78.74	[3.100]	81.28	[3.200]	64	3-147424-2	
		76.20	[3.000]	78.74	[3.100]	62	3-147424-1	
		73.66	[2.900]	76.20	[3.000]	60	3-147424-0	
		71.12	[2.800]	73.66	[2.900]	58	2-147424-9	
		68.58	[2.700]	71.12	[2.800]	56	2-147424-8	
		66.04	[2.600]	68.58	[2.700]	54	2-147424-7	
		63.50	[2.500]	66.04	[2.600]	52	2-147424-6	
		60.96	[2.400]	63.50	[2.500]	50	2-147424-5	
SUPERSEDED BY 7-147424-4		58.42	[2.300]	60.96	[2.400]	48	2-147424-4	
		55.88	[2.200]	58.42	[2.300]	46	2-147424-3	
		53.34	[2.100]	55.88	[2.200]	44	2-147424-2	
		50.80	[2.000]	53.34	[2.100]	42	2-147424-1	
SUPERSEDED BY 7-147424-0		48.26	[1.900]	50.80	[2.000]	40	2-147424-0	
		45.72	[1.800]	48.26	[1.900]	38	1-147424-9	
		43.18	[1.700]	45.72	[1.800]	36	1-147424-8	
		40.64	[1.600]	43.18	[1.700]	34	1-147424-7	
SUPERSEDED BY 6-147424-6		38.10	[1.500]	40.64	[1.600]	32	1-147424-6	
SUPERSEDED BY 6-147424-5		35.56	[1.400]	38.10	[1.500]	30	1-147424-5	
		33.02	[1.300]	35.56	[1.400]	28	1-147424-4	
		30.48	[1.200]	33.02	[1.300]	26	1-147424-3	
		27.94	[1.100]	30.48	[1.200]	24	1-147424-2	
		25.40	[1.000]	27.94	[1.100]	22	1-147424-1	
SUPERSEDED BY 6-147424-0		22.86	[.900]	25.40	[1.000]	20	1-147424-0	
		20.32	[.800]	22.86	[.900]	18	147424-9	
		17.78	[.700]	20.32	[.800]	16	147424-8	
		15.24	[.600]	17.78	[.700]	14	147424-7	
		12.70	[.500]	15.24	[.600]	12	147424-6	
			10.16	[.400]	12.70	[.500]	10	147424-5
			7.62	[.300]	10.16	[.400]	8	147424-4
			5.08	[.200]	7.62	[.300]	6	147424-3
			2.54	[.100]	5.08	[.200]	4	147424-2
OBSOLETE				2.54	[.100]	2	147424-1	
	FINISH	B	A	NO OF POSN	PART NUMBER			

		99.06	[3.900]	101.60	[4.000]	80	9-147424-0
		96.52	[3.800]	99.06	[3.900]	78	8-147424-9
		93.98	[3.700]	96.52	[3.800]	76	8-147424-8
		91.44	[3.600]	93.98	[3.700]	74	8-147424-7
		88.90	[3.500]	91.44	[3.600]	72	8-147424-6
		86.36	[3.400]	88.90	[3.500]	70	8-147424-5
		83.82	[3.300]	86.36	[3.400]	68	8-147424-4
		81.28	[3.200]	83.82	[3.300]	66	8-147424-3
		78.74	[3.100]	81.28	[3.200]	64	8-147424-2
		76.20	[3.000]	78.74	[3.100]	62	8-147424-1
		73.66	[2.900]	76.20	[3.000]	60	8-147424-0
		71.12	[2.800]	73.66	[2.900]	58	7-147424-9
		68.58	[2.700]	71.12	[2.800]	56	7-147424-8
		66.04	[2.600]	68.58	[2.700]	54	7-147424-7
		63.50	[2.500]	66.04	[2.600]	52	7-147424-6
		60.96	[2.400]	63.50	[2.500]	50	7-147424-5
		58.42	[2.300]	60.96	[2.400]	48	7-147424-4
		55.88	[2.200]	58.42	[2.300]	46	7-147424-3
		53.34	[2.100]	55.88	[2.200]	44	7-147424-2
		50.80	[2.000]	53.34	[2.100]	42	7-147424-1
		48.26	[1.900]	50.80	[2.000]	40	7-147424-0
		45.72	[1.800]	48.26	[1.900]	38	6-147424-9
		43.18	[1.700]	45.72	[1.800]	36	6-147424-8
		40.64	[1.600]	43.18	[1.700]	34	6-147424-7
		38.10	[1.500]	40.64	[1.600]	32	6-147424-6
		35.56	[1.400]	38.10	[1.500]	30	6-147424-5
		33.02	[1.300]	35.56	[1.400]	28	6-147424-4
		30.48	[1.200]	33.02	[1.300]	26	6-147424-3
		27.94	[1.100]	30.48	[1.200]	24	6-147424-2
		25.40	[1.000]	27.94	[1.100]	22	6-147424-1
		22.86	[.900]	25.40	[1.000]	20	6-147424-0
		20.32	[.800]	22.86	[.900]	18	5-147424-9
		17.78	[.700]	20.32	[.800]	16	5-147424-8
		15.24	[.600]	17.78	[.700]	14	5-147424-7
		12.70	[.500]	15.24	[.600]	12	5-147424-6
		10.16	[.400]	12.70	[.500]	10	5-147424-5
		7.62	[.300]	10.16	[.400]	8	5-147424-4
		5.08	[.200]	7.62	[.300]	6	5-147424-3
		2.54	[.100]	5.08	[.200]	4	5-147424-2
OBSOLETE				2.54	[.100]	2	5-147424-1
	FINISH	B	A	NO OF POSN	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002	TE Connectivity Ltd.				
DIMENSIONS: mm [INCHES]		CHK J.OLSON 06NOV02					
		APVD J.OLSON 06NOV02	NAME				
		PRODUCT SPEC 108-25022		RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, TOP ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU			
MATERIAL 		APPLICATION SPEC 114-25018		SIZE A2	CAGE CODE 00779	DRAWING NO 147424	RESTRICTED TO -
		WEIGHT -		SCALE 1:1			
CUSTOMER DRAWING				SHEET 2 of 2		REV G	