

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		J	REV PER ECO 15-002995	11MAR15	KG	PD

D

C

B


A

D

C

B

A



- 1 WIRE INSULATION: 5.72[.225] – 6.35[.250] DIA
- 2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.

23 GRAMS	9.91 ^{+0.13} [.390 ^{±.005}]	3/8	BODY: COPPER ASTM-B187 ANNEALED TIN PL MIL-T-10727 0.00457[.000150] MIN THK INSERT & FUNNEL: BRASS PER ASTM B36 NICKEL PLATE SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	55832-2
24 GRAMS	6.73 ^{+0.08} [.265 ^{±.003}]	1/4		55832-1
WEIGHT	"A"	"B"	MATERIAL AND FINISH	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHRUM 6/15/92	TE Connectivity
			CHK WJ VOCKROTH 6/16/92	
DIMENSIONS: MM [INCHES]			APVD AJ KAUFMAN 6/16/92	NAME WIRE TERMINAL, COPALUM SEALED, RING TONGUE, WIRE SIZE: 6 AL, 4 COPPER
			PRODUCT SPEC 108-11011	
MATERIAL SEE TABLE			APPLICATION SPEC 114-2134	SIZE A2
			FINISH SEE TABLE	CAGE CODE 00779
CUSTOMER DRAWING			WEIGHT SEE TABLE	DRAWING NO C=55832
			SCALE 4:1	RESTRICTED TO -
			SHEET 1 of 1	REV J