









Copyright FCI.

PRODUCT NUMBER SEE SHEET 2



spec ref				dr	Xie Bob	2013/05/22	projection 	MM 	size	A3	scale	3:2	
tolerance std ASME Y14.5	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Xie Bob	2013/06/03			ecn no				-
				chr	LI- He	2013/06/03			rel level				Released
				appr	Pei-Ming Zheng	2013/06/03			product family				PowerBlade+
surface 	linear	0.X	±0.50		title 32S + 14HP VT STB RECEPTACLE				dwg no	10106130-E008001		rev	A
		0.XX	±0.25										
		0.XXX	±0.10										
	ASME Y14.5	angular	0°	±2°	www.fci.com	cat. no.		Product - Customer Drw				sheet 1 of 3	

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
 - HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
 - SIGNAL CONTACT - COPPER ALLOY.
 - POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.
- 9) THE VOID CORING IN BETWEEN POWER MODULES, SIGNAL
MODULES AND END MODULES ARE OPTIONAL AND THE SHAPE
MAY BE DIFFERENT FOR OPTIMIZE THE MOLDING PROCESS. THE
VOID CORING WILL NOT EFFECT TO PRODUCT FUNCTION.

dr	Xie Bob	2013/05/22	projection 	MM 	size	scale	
eng	Xie Bob	2013/06/03			A3	1:1	
chr	Li- He	2013/06/03			ecn no	-	
appr	Pei-Ming Zheng	2013/06/03	product family	PowerBlade+	rel level	Released	
	title	32S + 14HP VT STB RECEPTACLE			dwg no	10106130-E008001	rev
www.fci.com	cat. no.	Product - Customer Drw				sheet 3 of 3	