




- | | | | | | | | | | | |
|--|---------------------------|--|----|----------------------------|---|--------------------|--|---------------------------|--|--|
| CONVERT TO LEAD-FREE
EC NO: UCP2013-2078
DRAWN BY: IBARRA
CHCKD BY: BAHAM
APPR. MILLER
2012/11/26
2012/12/01
2012/12/31 | QUALITY SYMBOLS | GENERAL TOLERANCES (UNLESS SPECIFIED) | | DIMENSION STYLE
MM ONLY | | SCALE
4:1 | DESIGN UNITS
METRIC | THIRD ANGLE
PROJECTION | | |
| | DESCRIPTION
▽=0
▽=0 | | mm | INCH | DRAWN BY
MSANDBERG | DATE
2007/19/07 | TITLE
IMPACT 4 PAIR HEADER
LEFT GUIDED ASSEMBLY
SALES DRAWING
molex
SD-76155-002 | | | |
| | | 4 PLACES ± | ± | --- | CHECKED BY
JLAURX | DATE
2007/19/07 | | | | |
| | | 3 PLACES ± | ± | --- | APPROVED BY
JLAURX | DATE
2010/11/15 | | | | |
| | | 0 PLACES ± | ± | --- | | | | | | |
| | | ANGULAR ±1/2° | | MATERIAL NO. | | DOCUMENT NO. | | SHEET NO. | | |
| | | DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS | | SEE TABLE | | SD-76155-002 | | 1 OF 3 | | |
| | REVIEW | | | SIZE
D | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | | | | |


PART NUMBER TABLE

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM "A"	DIM "B"	GUIDE LEFT END WALL OPTION
76155-*3**	6	24	19.3	9.50	
76155-*8**	8	32	23.1	13.30	
76155-*1**	10	40	26.9	17.10	
76155-*6**	16	64	38.3	28.50	



GUIDE LEFT
END WALL
OPTION

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM "A"	DIM "B"	GUIDE LEFT OPEN WALL OPTION
76155-*3**	6	24	17.9	9.50	
76155-*8**	8	32	21.7	13.30	
76155-*1**	10	40	25.5	17.10	
76155-*6**	16	64	36.9	28.50	



GUIDE LEFT
OPEN WALL
OPTION

PART NUMBER LOGIC

76155-****


MODULE TYPE
3 = GUIDE LEFT, TIN
7 = GUIDE LEFT END WALL, TIN

PIN LENGTH (P)
3 = 4.50 (SHORT COMPLIANT, 0.46±0.05 PTH)
4 = 4.90 (SHORT COMPLIANT, 0.46±0.05 PTH)
5 = 5.50 (SHORT COMPLIANT, 0.46±0.05 PTH)
6 = 4.50 (MICRO COMPLIANT, 0.39±0.05 PTH)
7 = 4.90 (MICRO COMPLIANT, 0.39±0.05 PTH)
8 = 5.50 (MICRO COMPLIANT, 0.39±0.05 PTH)



OF COLUMNS
1 = 10 COL
3 = 6 COL
6 = 16 COL
8 = 8 COL

KEY ORIENTATION
0 = NO KEY
1 = A
2 = B
3 = C
4 = D
5 = E
6 = F
7 = G
8 = H

SEE SHEET 1 EC NO: UCP2013-2078 DRWN: TIBARRA 2012/11/26 CHKD: J BINGHAM 2012/12/18 APPR: SMILLER 2012/12/31	REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	TITLE		
				MM ONLY		3:1	METRIC						
						DRAWN BY	DATE	IMPACT 4 PAIR HEADER LEFT GUIDED ASSEMBLY SALES DRAWING molex					
						CHECKED BY	DATE						
						APPROVED BY	DATE						
						JLAURX	2010/11/15						
						MATERIAL NO.	DOCUMENT NO.					SHEET NO.	
				ANGULAR ±1/2°		SEE TABLE		SD-76155-002				2 OF 3	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						



IMPACT 4 PAIR
BOARD RELATIONSHIPS



SEE SHEET 1 EC NO: UCP2013-2078 DRWN: TIBARRA 2012/11/26 CHKD: BINGHAM 2012/12/18 APPR: SMILLER 2012/12/31	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE IMPACT 4 PAIR HEADER LEFT GUIDED ASSEMBLY SALES DRAWING molex			
			mm	INCH	DRAWN BY MSANDBERG	DATE 2007/19/07	DOCUMENT NO. SD-76155-002				SHEET NO. 3 OF 3		
			4 PLACES ± ---	± ---	CHECKED BY	DATE							
			3 PLACES ± ---	± ---	JLAURX	2007/19/07							
			2 PLACES ± 0.13	± ---	APPROVED BY	DATE							
			1 PLACE ± 0.25	± ---	JLAURX	2010/11/15							
			0 PLACE ±	±	MATERIAL NO.								
			ANGULAR ±1/2°		SEE TABLE								
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							