


Flash


*One Module*

Single channel, electronic time switch

	Features
Single channel analogue time switch intended for control of heating, lighting, watering, access control etc.	- Simple time setting and programming. - Pivoting protective hood. - Connection by protected cage terminals 2-position manual control, AUTO and override.
Simple programming by unlosable segments of 15 minutes (24 hour model), 105 minutes (7 day model).	

	Functional characteristics	
Cycle	24 Hours	7 Days
Programming in steps of	15 min	1 h 45
Minimum interval between 2 switchings	15 min	1 h 45
Maximum number of switchings per cycle	96	96
Accuracy of switching	2 min 30 sec.	15 min


Dimensions



	Technical characteristics
Supply voltage	230 V +/- 10%
Frequency	50/60 Hz
Power consumption	approx. 0.5 VA
Changeover contacts	resistive load 16 A 250 V
resistive load	inductive load (cos φ = 0.6) 4 A 250 V
Accuracy of operation	1 sec / 24 h.
Operating temperature	-10 °C to +55 °C
Storage temperature	-10 °C to +55 °C
Connection by cage terminals, section of conductors	1 to 4 mm ²
Conformity to standard BS EN 60730	yes
Performance indicated for an ambient temperature of 20 °C	

Electrical Connections

Mounting



Reference	Cycle	Voltage free normal contacts
10002	24 hour	16 (4) A
10702	7 day	16 (4) A

Reference	Accessories
143602	Compatible IP40 enclosure

Sangamo Limited
 Industrial Estate, Port Glasgow, Renfrewshire, PA14 5XG
 Tel: 0845 006 6206 Fax: 01475 744567
 Email : enquiries@sangamo.co.uk Web: www.sangamo.co.uk

DS/DP/0010/A