



0548



0548-0-15-XX-21-XX-10-0

Solder mount in .036 min. mounting hole


8975



8975-0-15-XX-21-XX-10-0

Solder mount in .036 min. mounting hole


3016



3016-0-15-XX-21-XX-10-0

Solder mount in .036 min. mounting hole


9548



9548-0-15-XX-21-XX-10-0

Solder mount in .036 min. mounting hole


8637



8637-0-15-XX-21-XX-10-0

Solder mount in .037 min. mounting hole


1407



1407-0-15-XX-11-XX-10-0

Solder mount in .040 min. mounting hole

0553/8553




X553-X-15-XX-X1-XX-10-0

Hex press-fit in .041 plated thru hole

Basic Part Number	Length L	Depth N
0553-1	.140	.124
0553-2	.170	.154
0553-3	.282	.266
8553-0	.245	.229

0566




0566-X-15-XX-21-XX-10-0

Solder mount in .039 min. mounting hole

Basic Part Number	Length L
0566-1	.083
0566-2	.138


0442



0442-0-15-XX-11-XX-10-0

Solder mount in .040 min. mounting hole

0554



0554-0-15-XX-21-XX-10-0

Solder mount in .040 min. mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - XX - XX - XX - 10 - 0

BASIC PART #

SPECIFY SHELL FINISH:
01 200μ" TIN/LEAD OVER NICKEL
80 200μ" TIN OVER NICKEL
15 10μ" GOLD OVER NICKEL



SPECIFY CONTACT FINISH:
02 100μ" TIN/LEAD OVER NICKEL
84 100μ" TIN OVER NICKEL
27 30μ" GOLD OVER NICKEL

SELECT CONTACT

#11 or #21 CONTACT (DATA ON PAGE 217)