




NOTES:

1. MATERIAL:
HOUSING: PPS, 40% G.F. FILLED; BROWN, UL94V-0 RATED,
TERMINAL: PHOSPHOR BRONZE, TIN LEAD OR PURE MATTE TIN PLATED.
2. FINISH:
120u" MATTE TIN PLATED OVERALL, 50u" NICKEL UNDERPLATED.
3. RECOMMENDED PCB LAYOUT IS SHOWN IN FIG.1.
4. THE "FCI" LOGO IS LOCATED AS SHOWN.
5. COPLANARITY REQUIREMENT:
 - A. CONTACT MUST BE BELOW HOUSING BOTTON SURFACE WITHIN 0.23MM.
 - B. CONTACT SEATING LINE MUST BE WITHIN 0.102MM.
6. THE POSITION OF PIN#1 IN THE CENTER PAD IS AS SHOWN.
7. MANUFACTURING PROCESS COMPATIBILITY: THE HOUSING WILL WITHSTAND EXPOSURE TO 245 DEG SOLER BATH TEMPERATURE FOR 5 SECOND IN A IR REFLOW APPLICATION.
8. PRODUCT SPECIFICATION: GES-12-054.
9. PACKAGING SPECIFICATION: GS-14-783

ORDERING DATA: 56484-

X X X L F
 BLANK: PLATING TIN/LEAD
 L F: PLATING PURE MATTE TIN
 NO OF CONTACTS.
 PACKAGING
 4. TAPE & REEL

Dm No of contact	A	B	C	D	E	F	G	H	I
	± 0.2	± 0.2	± 0.2	± 0.2	± 0.2	± 0.2	± 0.2	± 0.2	± 0.2
32	7.62	16.89	21.34	10.16	19.43	12.68	15.22	12.03	14.57
44	12.70	21.97	26.70	12.70	21.97	17.76	17.76	17.11	17.11

AP PART NO.	MCK PART NO.	PACKAGING
56484-XXLF	PLCC-XXP-T-SMT-TR-SOD	TAPE & REEL

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fcimed.com	
litr	ecn no.	dr	date	.X ± 0.38 .XX ± 0.25 .XXX ± 0.20 0° ± .2°				projection		title	
A	T06-0135	WL	6/23/05					linear		MINI PLCC SMT SOCKET	
B	T06-0177	JH	10/24/06							PLCC-XXO-T-SMT-SOD	
				angles							
				dr JASON HSU 3/27/01				MM ←		product family SOCKET	
				engr JASON HSU 3/27/01						size dwg no	
				chr JASON HSU 3/27/01				scale			
				opd JENN TSKAO 3/27/01				1 : 1		A4	
sheet index	revision		B								
sheet	revision	sheet	1								