


RECOMMENDED P.C.B. LAYOUT  
SCALE 1X






CIRCUIT: 4PDT


| SWITCH FUNCTION      |                       |                       |
|----------------------|-----------------------|-----------------------|
| PDS. 1               | PDS. 2                | PDS. 3                |
|                      |                       |                       |
| ON                   | ON                    | ON                    |
| 2-3,5-6<br>8-9,11-12 | 2-3, 5-4<br>8,9 11-10 | 2-1, 5-4<br>8,7 11-10 |

## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC or 28VDC; 2A @250VAC.
5. CONTACT MATERIAL: Copper Alloy w/Silver Plating.
6. ELECTRICAL LIFE: 50,000 make-and-break cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.



SECTION A-A



**E-SWITCH®**

TITLE

3004P6J1BLKM7QE

SCALE

2:1

DATE

1/15/04

DR

AR

DWG

T346008

REV

A

THE INFORMATION CONTAINED IN THIS DOCUMENT  
IS PROPRIETARY TO E-SWITCH AND IS  
NOT TO BE COPIED OR TRANSFERRED

|      |         |                         |         |      |
|------|---------|-------------------------|---------|------|
| A    | 13704   | RELEASED FOR PRODUCTION | 1/15/04 | AR   |
| REV. | ECN No. | DESCRIPTION             | DATE    | CHKD |