

1VL Detector Switches

Type: **ESE13**




■ Features

- Thin type : Height=1.2 mm
- Highly reliable contact
- SMD type (Embossed taping, Reflow soldering)

■ Recommended Applications

- Detection of media in portable electronic equipment
(Mobile phones / Digital still cameras / Camcorders)

■ Explanation of Part Numbers



■ Specifications

Rating		50 μ A 3 Vdc to 10 mA 5 Vdc (Resistive load)
Contact Resistance		500 m Ω max. (Initial)
Insulation Resistance		100 M Ω min. (100 Vdc)
Dielectric Withstanding Voltage		100 Vac for 1 minute
Operating Force		300 mN max.
Mounting Height		1.2 mm
Poles and Throws		1-pole 1-throw
Full Travel (Pushing distance)		Type V : 2.15 mm (2.15 mm) Type H : 3.05 mm (2.15 mm)
Operating Life		50000 cycles min.
Temperature Range		-10 °C to +60 °C
Heat Resistance		+70 °C for 96 hours
Low Temperature Resistance		-25 °C for 96 hours
Humidity Resistance		+40 °C 90 % to 95 % RH for 96 hours
Minimum Quantity/Packing Unit	ESE13H	5000 pcs. Embossed Taping (Reel Pack)
	ESE13V	3000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton	ESE13H	30000 pcs.
	ESE13V	18000 pcs.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Oct. 2012

■ Dimensions in mm (not to scale)

No. 1 ESE13V J-bent terminals 1-pole 1-throw With boss ESE13V01B Without boss ESE13V01A		
No. 2 ESE13V Straight terminals 1-pole 1-throw With boss ESE13V01D Without boss ESE13V01C		
No. 3 ESE13H J-bent terminals 1-pole 1-throw With boss ESE13H01B Without boss ESE13H01A		

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

No. 4

ESE13H Straight terminals

1-pole 1-throw

With boss
ESE13H01D

Without boss
ESE13H01C

PWB mounting hole for reference
(Pitch tolerance: ±0.05)

1-pole 1-throw (N.O)

Technical drawing of a Taping Reel. The top view shows a circular reel with an outer diameter of $\phi 380.0 \pm 2.0$ and a central hole diameter of $\phi 15.0 \pm 0.1$. The side view shows a thickness of 16.4. The drawing is labeled "Taping Reel".

00 Oct. 2012