

**DESCRIPTION**

The 1N64xx series of transient voltage suppressors are designed to protect military and commercial electronic equipment from overvoltages caused by lightning, ESD, EFT, inductive load switching, and EMP. These devices are constructed using a p-n junction TVS diode in a hermetically sealed, voidless glass package. The hermetically sealed package provides high reliability in harsh environmental conditions. TVS diodes are further characterized by their high surge capability, low operating and clamping voltages, and a theoretically instantaneous response time. This makes them ideal for use as board level protection for sensitive semiconductor components. These devices are DESC QPL qualified to MIL-S-19500/551.

**FEATURES:**

- 500 Watts Peak Pulse Power ( $t_p = 10/1000\mu s$ )
- Voidless hermetically sealed glass package
- Metallurgically bonded
- High surge capacity
- Unidirectional
- Available in **JTX**, and **JTXV** versions per MIL-S-19500/551

**MECHANICAL CHARACTERISTICS:**

- Hermetically sealed glass package
- Tinned copper leads
- Marking : P/N, date code, logo, & cathode band

**APPLICATIONS:**

- Aerospace & Industrial Electronics
- Board Level Protection
- Airborne Systems
- Shipboard Systems
- Ground Systems

**MAXIMUM RATINGS**


| RATING                                            | SYMBOL | VALUE       | UNIT  |
|---------------------------------------------------|--------|-------------|-------|
| Peak Pulse Power ( $t_p = 10 \times 1000\mu s$ )  | Ppk    | 500         | Watts |
| Operating Temperature                             | Tj     | -65 to +175 | °C    |
| Storage Temperature                               | Tstg   | -65 to +175 | °C    |
| Steady-State Power Dissipation @ TL = 75°C (3/8") | PD     | 3           | Watts |

**ELECTRICAL CHARACTERISTICS @ 25°C (unless otherwise specified)**


| DEVICE TYPE | REVERSE STAND-OFF VOLTAGE<br>$V_{RWM}$ | REVERSE LEAKAGE CURRENT<br>$I_R$ | MINIMUM BREAKDOWN VOLTAGE<br>$V_{BR} @ I_T$ | TEST CURRENT<br>$I_T$ | MAXIMUM CLAMPING VOLTAGE<br>$V_C @ I_{pp}$ | PEAK PULSE CURRENT<br>$I_{pp}$<br>$T_p = 1mS$ | PEAK PULSE CURRENT<br>$I_{pp}$<br>$T_p = 20\mu S$ | TEMPERATURE COEFFICIENT<br>OF $V_{BR}$<br>$\alpha V_Z$ |
|-------------|----------------------------------------|----------------------------------|---------------------------------------------|-----------------------|--------------------------------------------|-----------------------------------------------|---------------------------------------------------|--------------------------------------------------------|
|             | (V)                                    | ( $\mu A$ )                      | (V)                                         | (mA)                  | (V)                                        | (A)                                           | (A)                                               | % /°C                                                  |
| 1N6461      | 5                                      | 3000                             | 5.6                                         | 25                    | 9.0                                        | 56                                            | 315                                               | 0.040                                                  |
| 1N6462      | 6                                      | 2500                             | 6.5                                         | 20                    | 11.0                                       | 46                                            | 258                                               | 0.040                                                  |
| 1N6463      | 12                                     | 500                              | 13.6                                        | 5                     | 22.6                                       | 22                                            | 125                                               | 0.050                                                  |
| 1N6464      | 15                                     | 500                              | 16.4                                        | 5                     | 26.5                                       | 19                                            | 107                                               | 0.060                                                  |
| 1N6465      | 24                                     | 50                               | 27.0                                        | 2                     | 41.4                                       | 12                                            | 69                                                | 0.084                                                  |
| 1N6466      | 30.5                                   | 3                                | 33.0                                        | 1                     | 47.5                                       | 11                                            | 63                                                | 0.093                                                  |
| 1N6467      | 40.3                                   | 2                                | 43.7                                        | 1                     | 63.5                                       | 8                                             | 45                                                | 0.094                                                  |
| 1N6468      | 51.6                                   | 2                                | 54.0                                        | 1                     | 78.5                                       | 6                                             | 35                                                | 0.096                                                  |

TEL:805-498-2111 FAX:805-498-3804


#### PEAK PULSE POWER vs. PULSE TIME




#### 10x1000μs IMPULSE WAVEFORM




#### STEADY STATE DERATING CHARACTERISTICS FOR FREE AIR MOUNTING



#### PULSE DERATING CURVE



#### MECHANICAL OUTLINE



| DIMENSIONS       |        |       |       |       |      |
|------------------|--------|-------|-------|-------|------|
| DIM <sup>N</sup> | INCHES |       | MM    |       | NOTE |
|                  | MIN    | MAX   | MIN   | MAX   |      |
| A                | 0.115  | 0.140 | 2.92  | 3.56  |      |
| B                | 0.900  | 1.300 | 22.86 | 33.02 |      |
| C                | 0.150  | 0.300 | 3.81  | 7.62  | 2    |
| D                | 0.037  | 0.042 | 0.94  | 1.07  | 2    |

#### NOTES :

- Controlling dimension is inches.
- Includes uncontrolled area of device leads.

#### SCHEMATIC

