





NOTES:


- 1 MATERIAL: BASE AND COVER: 30% GLASS FILLED POLYESTER FLAME RETARDANT PER UL-94-V0 COLOUR GREY STRAIN RELIEF: UNREINFORCED THERMOPLASTIC FLAME RETARDANT PER UL-94-V0 COLOUR GREY CONTACT: PHOSPHOR BRONZE
- 2 PLATING: - CONTACT AREA 0.76µm GOLD - REMAINDER 1.27µm Ni
- 3 TRIANGLE NOT MOLDED-IN ON 2x2 AND 2x3 POSITIONS WITH CENTRAL KEY
- 4 PRODUCT PACKAGED IN TUBES.
- 5 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008. PACKAGING SPECIFICATION AS PER GS-14-920.

mat'l. code	SEE NOTES	surface	ISO 1302	tolerance	ISO 416	ISO 1101	projection	product family	QUICKIE FEM
lfr	ecn no	dr	date	tolerances unless otherwise specified	angles	Linear	mm	title	QUICKIE III FEM
AB	F06-0274	LMU	06.08.25				scale 5:1	dwg no	71602
V	V11892	DLE	01.08.10					sheet 1 of 2	Az
W	F10566	DLE	01.10.24	dr	P. NIZZI	98.02.08			
X	F03019	DLE	03.01.23	engr	JM PHAMVAN	98.02.08			
Y	F03099	DLE	03.04.24	chr	P. NIZZI	98.02.09			
AA	F06-0274	LMU	06.09.12	appd	JMP	98.02.09		type	CUSTOMER Drawing
sheet	revision	AB	Y						
index	sheet	1	2						


PRODUCT NUMBER	SIZE	DIM "A"	DIM "B"	DIM "C"	DIM "S"	SLOT STYLE
71602-X04LF	2x 2	9.54	2.54	9.46	5.66	NO SLOT
71602-X06LF	2x 3	12.08	5.08	12.00	8.20	RIGHT IF NO KEY
71602-X08LF	2x 4	14.62	7.62	14.54	10.74	RIGHT IF NO KEY
71602-X10LF	2x 5	17.16	10.16	17.08	13.28	RIGHT SLOT
71602-X12LF	2x 6	19.70	12.70	19.62	15.82	RIGHT SLOT
71602-X14LF	2x 7	22.24	15.24	22.16	18.36	RIGHT SLOT
71602-X16LF	2x 8	24.78	17.78	24.70	20.90	2 SLOTS
71602-X18LF	2x 9	27.32	20.32	27.24	23.44	2 SLOTS
71602-X20LF	2x 10	29.86	22.86	29.78	25.98	2 SLOTS
71602-X24LF	2x 12	34.94	27.94	34.85	31.06	2 SLOTS
71602-X26LF	2x 13	37.48	30.48	37.40	33.60	2 SLOTS
71602-X30LF	2x 15	42.56	35.56	42.48	38.68	2 SLOTS
71602-X34LF	2x 17	47.64	40.64	47.56	43.76	2 SLOTS
71602-X40LF	2x 20	55.26	48.26	55.18	51.38	2 SLOTS
71602-X44LF	2x 22	60.34	53.34	60.26	56.46	2 SLOTS
71602-X50LF	2x 25	67.96	60.96	67.88	64.08	2 SLOTS
71602-X60LF	2x 30	80.66	73.66	80.58	76.78	2 SLOTS
71602-X64LF	2x 32	85.74	78.74	85.66	81.86	2 SLOTS




WITHOUT STRAIN RELIEF



WITH LOW PROFILE STRAIN RELIEF



WITH STANDARD STRAIN RELIEF



WITH LATCHING STRAIN RELIEF

AFTER TERMINATION SIDE VIEW OF ASSEMBLY (* LATCHING DIM ON HEADER)

71602-7YYLF		●				●	712 724
71602-6YYLF	●					●	612 624
71602-5YYLF		●			●		504 512 524
71602-4YYLF		●					
71602-3YYLF		●	●				304
71602-2YYLF	●				●		204 212 224
71602-1YYLF	●				●		
71602-0YYLF	●		●				004
PRODUCT NUMBER	WITH CENTRAL KEY	WITHOUT CENTRAL KEY	STANDARD	WITHOUT	LOW PROFILE	LATCHING	DASHES NOT AVAILABLE
			STRAIN RELIEF				

mat'L code				surface	tolerance	projection	product family	
lfr ecn no dr date				ISO 1302	ISO 416 ISO 1001	mm	QKIE FEM	
T FBD615 DLE 98.08.26				tolerances unless otherwise specified	Linear	mm	title	
U V11892 DLE 01.08.10				angles	Linear	mm	QUICKIE III FEM	
V F03019 DLE 03.01.23						scale N/A	0.76µm Au	
W F03099 DLE 03.04.23				dr	P. NIZZI	96.02.09	dwg no	
X F06-Q270 LMU 06.09.12				engr	JM PHAMVAN	96.02.09	sheet 2 of -	
Y F06-Q274 LMU 06.09.25				chr	P. NIZZI	96.02.09	71602	
				appd	JM P	96.02.09	type	
sheet index				revision			CUSTOMER Drawing	
sheet				sheet				