


























E		35.56 [1.400]	14	37.69 [1.484]	30	6-146130-4	
		33.02 [1.300]	13	35.15 [1.384]	28	6-146130-3	
E		30.48 [1.200]	12	32.61 [1.284]	26	6-146130-2	
		27.94 [1.100]	11	30.07 [1.184]	24	6-146130-1	
		25.40 [1.000]	10	27.53 [1.084]	22	6-146130-0	
		22.86 [.900]	9	24.99 [.984]	20	5-146130-9	
		20.32 [.800]	8	22.45 [.884]	18	5-146130-8	
		17.78 [.700]	7	19.91 [.784]	16	5-146130-7	
		15.24 [.600]	6	17.37 [.684]	14	5-146130-6	
		12.70 [.500]	5	14.83 [.584]	12	5-146130-5	
		10.16 [.400]	4	12.29 [.484]	10	5-146130-4	
		7.62 [.300]	3	9.75 [.384]	8	5-146130-3	
		5.08 [.200]	2	7.21 [.284]	6	5-146130-2	
		2.54 [.100]	1	4.67 [.184]	4	5-146130-1	
	E		17.78 [.700]	7	19.91 [.784]	16	1-146130-8
	E		5.08 [.200]	2	7.21 [.284]	6	1-146130-7
	E		35.56 [1.400]	14	37.69 [1.484]	30	1-146130-4
		33.02 [1.300]	13	35.15 [1.384]	28	1-146130-3	
D		30.48 [1.200]	12	32.61 [1.284]	26	1-146130-2	
		27.94 [1.100]	11	30.07 [1.184]	24	1-146130-1	
		25.40 [1.000]	10	27.53 [1.084]	22	1-146130-0	
		22.86 [.900]	9	24.99 [.984]	20	146130-9	
		20.32 [.800]	8	22.45 [.884]	18	146130-8	
		17.78 [.700]	7	19.91 [.784]	16	146130-7	
		15.24 [.600]	6	17.37 [.684]	14	146130-6	
		12.70 [.500]	5	14.83 [.584]	12	146130-5	
		10.16 [.400]	4	12.29 [.484]	10	146130-4	
		7.62 [.300]	3	9.75 [.384]	8	146130-3	
		5.08 [.200]	2	7.21 [.284]	6	146130-2	
		2.54 [.100]	1	4.67 [.184]	4	146130-1	
	PLATING	C	B	A	NO OF POSN	PART NUMBER	

RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL

