


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PACKAGE QTY.	MIN. BUNDLE DIA.	MAX. BUNDLE DIA.	LENGTH L ±.2 [5]
MLT2.7WH-LP	50	2.0" [50]	2.7" [69]	10.2" [259]
MLT4WH-LP	50	2.0" [50]	4" [102]	14.3" [362]
MLT6WH-LP	50	2.0" [50]	6" [152]	20.5" [521]
MLT8WH-LP	50	2.0" [50]	8" [203]	26.8" [679]
MLT10WH-LP	50	2.0" [50]	10" [254]	33.0" [838]
MLT2.7WH-TL	250	2.0" [50]	2.7" [69]	10.2" [259]
MLT4WH-TL	250	2.0" [50]	4" [102]	14.3" [362]
MLT6WH-TL	250	2.0" [50]	6" [152]	20.5" [521]



NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 450 LBS (2000 NEWTONS)
WHEN TESTED ON A 3" MANDREL EXCEPT MLT2.7WH-LP WHEN
TESTED ON A 1 1/2" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE
SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = ±.010 [.25] .XX = ±.02 [.5]
.X = ±.03 [.8] ANGLES = ±2°
5. MATERIAL: 304 STAINLESS STEEL



					PANDUIT CORP. TINLEY PARK, ILLINOIS			
05A	2/12	MIM	RGRO	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	METAL LOCKING TIE HEAVY SERIES WAVE-TY 304 STAINLESS STEEL CUSTOMER DRAWING			
REV	DATE	BY	CHK	DESCRIPTION	DRAWN BY	CHK'D	SCALE	DRAWING NO.
					JAMB	DPN	2X	N41122BS_DC